

Micrometer heads

Stem with clamping nut, spherical spindle

Mitutoyo

Application:

For installation in measuring instruments and presetters, as a setting and control element on machine tools, for fine adjustment of cross tables

Execution:

- With regular gradation
- With clamping nut
- Rotating spindle



Art. no.	32016 899
Brand	MITUTOYO
Manufacturer Part Number	148-245
Display	Nonius
Min./max. length measuring range	0-5 mm
Scale value	0.004 mm
Measuring surface diameter	2 mm
Measuring arrangement	Spherical (SR1.5)
Clamp in shank diameter	3.5 mm
Clamping shank length	3.2 mm
Measuring spindle increments	0.1 mm
Spindle clamping	No
Design	Metric
Calibration Group	DE
Gross Weight	0.012 kg
Product Group	3MA

EAN

4946368592244