

Workplace mat made of 100% nitrile rubber, ESD design, oil-resistant

Flat structure, height 19 mm – modular assembly system



Application:

Extremely comfortable anti-fatigue mat for heavy-duty work, with diamond-pattern surface. For use both in large areas and individual workplaces. These 45 x 45 cm modular floor tiles are equipped with a universal double locking system on all four sides, designed to enable an extra-firm, seamless connection for fast installation.

Execution:

- This 19-mm thick mat lifts the employee off the hard floor, while balls underneath the mat allow for flexibility with every movement.
- The diamond-pattern surface provides good grip, and allows easy pivoting and freedom of movement when working on dynamic jobs
- Slip resistance R10 in accordance with DIN 51130
- Free of DOP, DMF, ozone-depleting substances, silicone and heavy metals
- Low flammability, fire safety class Bfl-S1 tested to EN 13501-1
- ESD mats, comply with IEC 61340-4-1 (category DIF), measured resistance $R_g 10^6-10^9\Omega$, $R_p 10^6-10^9\Omega$



Advantage:

- The square mats can be assembled to cover any area
- Can be combined with black or yellow edge strip made of nitrile rubber, 91 cm x 15 cm
- The flexible assembly system means that individual mats can be exchanged or adapted to a different environment
- Insulating mat protects against cold, heat, vibration and noise

Art. no.	50225 267
Brand	NOTRAX
Manufacturer Part Number	574S1818BL
Surface structure	Stud plate / closed
Material	Nitrile rubber
Length	450 mm
Width	450 mm
Material thickness	19 mm
Mat design	Individual mat
Resistance against	Oil, Acid (limited), Fats, Petrol, Coolant
Suitable for wet areas	No
Antistatic	Yes
Anti-fatigue	Yes
Non-slip	Yes
Compliant with REACH	Yes
Colour	Black
ESD-capable	Yes
Gross Weight	3.300 kg
Product Group	5AD

EAN

0662641906921