

Large cabinet with easy-view storage bins

Doors with perforated/slotted panels

RasterPlan

Application:


For clearly-arranged storage of small parts in RASTERPLAN easy-view storage bins.

Version:

- Stable steel sheet metal structure with double-walled, warp-resistant hinged doors with inset triple-bolt security cylinder lock, with 2 keys, opening angle more than 200°
- Full-length rod guidance, internal doors equipped with RASTERPLAN perforated slotted panels, double-walled side walls
- Galvanised shelves, adjustable in increments of 10 mm
- Fitted with RASTERPLAN easy-view storage bins made of impact-proof and shock-proof polyethylene, colour coded
- For accessories such as labels, lids see from no. 50638 850-876 in the Workstation chapter.

Delivery:

Without labels



| | |
|--|----------------------------------|
| Art. no. | 50639 313 |
| Model | 12 |
| Door design | Perforated plates/slotted plates |
| Height | 1950 mm |
| Width | 1130 mm |
| Depth | 590 mm |
| Number of shelves, depth 250 mm | 9 |
| Number of shelves, depth 340 mm | 2 |
| Number of bins 85 x 105 x 45 mm | 32 |
| Number of bins 160 x 105 x 75 mm | 90 |
| Number of bins 230 x 140 x 130 mm | 28 |
| Number of bins 290 x 140 x 130 mm | 14 |
| Number of bins 350 x 200 x 150 mm | 5 |
| Load-carrying capacity per shelf | 50 kg |
| Load-carrying capacity per drawer | 50 kg |
| Lock type | Cylinder lock |
| Material | Sheet steel |
| Body colour | Light grey RAL 7035 |
| Colour of front | Light grey RAL 7035 |
| Surface | Plastic-coated |

EAN-Code

4251142219362