

## NC machine reamer, solid carbide with universal shank

for universal use up to 1300N/mm<sup>2</sup>

**ORION**<sup>®</sup>

### Application:

For producing H7 fit tolerances in through holes on NC machines up to 1300 N/mm<sup>2</sup>.

### Execution:

- 7-8° left-hand spiral, type B

### Advantage:

- good bore hole quality (dimensional tolerance, roundness, surface quality)



<b>Art. no.</b>	<b>11727 140</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	11727140
<b>Cutting material</b>	SC
<b>Tolerance of fit</b>	H7
<b>Groove type</b>	Left-hand twist, 7-8°
<b>Tool holding device</b>	HA parallel shank
<b>Surface</b>	Uncoated
<b>Cutting edge diameter</b>	14 mm
<b>Length</b>	160 mm
<b>Cutting edge length</b>	47 mm
<b>Projecting length</b>	110 mm
<b>Shank diameter</b>	14 mm
<b>Number of cutting edges</b>	6 PCS
<b>f steel 1300</b>	0.15 mm/r
<b>DIN</b>	8093
<b>Gross Weight</b>	0.209 kg
<b>Product Group</b>	104

### EAN

4053625174164