



Finish : Reflector

1	0833	2	0833	3	0000	4		5		6		7		8	
SUPERSEDES 9245 877 49100 0833/000 p.190-1 Of 13/10/2011		HALOGEN LAMP INFRARED INDUSTRIAL 14197Z/83 3000W 400V REFL					9245 877 49100 0833/000			06/03/2012					
REF. : PDM IRK 2012-007		DOCUMENTATION		UNIT mm	PROJ. EUROP 	2 SH	SH 190-1	10	1:1	A4					
NAME :		VALIDATION :			DR. FISCHER Europe										
All rights reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner.															

**PRODUCT REQUIREMENT SHEET**

See LV 75-032

<b>MEASURING VOLTAGE</b>	400V (stabilisation 3 min.)
<b>MEASURING POSITION</b>	Horizontal
<b>LIFE TEST POSITION</b>	Horizontal
<b>BURNING POSITION</b>	P15
<b>SWITCHING CYCLE</b>	Continuous
<b>AGEING</b>	1h at rated voltage

	VALUE UNIT	TOLERANCE
<b>WATTAGE</b>	3000W	± 6 %
<b>LIFE</b>	5000 h	average
<b>COLOR TEMPERATURE</b>	Clear lamp Lamp with reflector	2700 K NA ± 100 K
<b>FLUX (HeLeN lamp)</b>	Clear lamp Reduction	NA NA
<b>IRRADIANCE LEVEL</b>	25000 W/m <sup>2</sup>	Mini
<b>WEIGHT</b>	48 g	

1	0833	2	0833	3	0000	4		5		6		7		8	
SUPERSEDES :		HALOGEN LAMP						9245 877 49100			06/03/2012				
9245 877 49100		INFRARED INDUSTRIAL REFLECTOR						0833/000							
0833/000 p. 190-2		14197Z/83 3000W 400V REFL													
Of 10/10/2011		REF. : PDM IRK 2012-007		DOCUMENTATION		UNIT	PROJ EUROP	2	SH	SH	190-2	10		A4	
						mm									
NOM : J.P. CHARLIER		VALIDATION : A. PICHARD						DR. FISCHER Europe							
All rights reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner.															