

5mm × 20mm Glass Fuses Time Delay

multicompPRO





Features

- Time delay (F) IEC60127
- Glass cartridge, nickel plated brass end caps
- Colour coded available
- DC cold resistance: 64 ~ 96m
- Melting : 1.810A2.sec
- Maximum voltage drop (150mV max): 115m
- Break capacity 35A or 10In 250VAC whichever is greater (125mA-16A)

**RoHS
Compliant**

- UL approved (125mA - 8A)
- CSA approved (125mA - 8A)
- CCC approved (100mA - 6.3A)
- S approved (125mA - 8A)
- ⚡ approved (125mA - 6.3A)

Diagram



Dimensions : Millimetres

Part Number Table

Description	Part Number
10A Glass 5mm×20mm time delay fuse	MC000828
800mA Glass 5mm×20mm time delay fuse	MC000862
8A Glass 5mm×20mm time delay fuse	MC000863
630mA Glass 5mm×20mm time delay fuse	MC000864
63mA Glass 5mm×20mm time delay fuse	MC000865
6.3A Glass 5mm×20mm time delay fuse	MC000866
500mA Glass 5mm×20mm time delay fuse	MC000867
50mA Glass 5mm×20mm time delay fuse	MC000868
5A Glass 5mm×20mm time delay fuse	MC000869
400mA Glass 5mm×20mm time delay fuse	MC000870
4A Glass 5mm×20mm time delay fuse	MC000871
315mA Glass 5mm×20mm time delay fuse	MC000872
3.15A Glass 5mm×20mm time delay fuse	MC000873
250mA Glass 5mm×20mm time delay fuse	MC000874
200mA Glass 5mm×20mm time delay fuse	MC000875
2.5A Glass 5mm×20mm time delay fuse	MC000876
2A Glass 5mm×20mm time delay fuse	MC000877
160mA Glass 5mm×20mm time delay fuse	MC000878
125mA Glass 5mm×20mm time delay fuse	MC000879
100mA Glass 5mm×20mm time delay fuse	MC000880
1.6A Glass 5mm×20mm time delay fuse	MC000881
1.25A Glass 5mm×20mm time delay fuse	MC000882
1A Glass 5mm×20mm time delay fuse	MC000883
3.15A Glass 5mm×20mm time delay fuse	MC001011

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO