

# **MCP3201**

# 2.7V 12-Bit A/D Converter with SPI<sup>TM</sup> Serial Interface

#### **Features**

- 12-bit resolution
- ±1 LSB max DNL
- ±1 LSB max INL (MCP3201-B)
- ±2 LSB max INL (MCP3201-C)
- · On-chip sample and hold
- SPI<sup>™</sup> serial interface (modes 0,0 and 1,1)
- Single supply operation: 2.7V 5.5V
- 100ksps max. sampling rate at V<sub>DD</sub> = 5V
- 50ksps max. sampling rate at V<sub>DD</sub> = 2.7V
- Low power CMOS technology
- 500 nA typical standby current, 2 µA max.
- 400 µA max. active current at 5V
- Industrial temp range: -40°C to +85°C
- 8-pin MSOP, PDIP, SOIC and TSSOP packages


#### **Applications**

- · Sensor Interface
- Process Control
- · Data Acquisition
- · Battery Operated Systems


#### Description

The Microchip Technology Inc. MCP3201 is a successive approximation 12-bit Analog-to-Digital (A/D) Converter with on-board sample and hold circuitry. The device provides a single pseudo-differential input. Differential Nonlinearity (DNL) is specified at ±1 LSB, and Integral Nonlinearity (INL) is offered in ±1 LSB (MCP3201-B) and ±2 LSB (MCP3201-C) versions. Communication with the device is done using a simple serial interface compatible with the SPI protocol. The device is capable of sample rates of up to 100 ksps at a clock rate of 1.6 MHz. The MCP3201 operates over a broad voltage range (2.7V - 5.5V). Low current design permits operation with typical standby and active currents of only 500 nA and 300 µA, respectively. The device is offered in 8-pin MSOP, PDIP, TSSOP and 150 mil SOIC packages.

#### **Package Types**



#### **Functional Block Diagram**



# 1.0 ELECTRICAL CHARACTERISTICS

## 1.1 Maximum Ratings\*

V <sub>DD</sub> 7	.0V
All inputs and outputs w.r.t. $V_{SS}$ 0.6V to $V_{DD}$ +0	.6V
Storage temperature65°C to +150	)°C
Ambient temp. with power applied65°C to +125	5°C
ESD protection on all pins (HBM)> 4	kV

\*Notice: Stresses above those listed under "Maximum ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational listings of this specification is not implied. Exposure to maximum rating conditions for extended periods may affect device reliability.

### PIN FUNCTION TABLE

Name	Function	
$V_{DD}$	+2.7V to 5.5V Power Supply	
$V_{SS}$	Ground	
IN+	Positive Analog Input	
IN-	Negative Analog Input	
CLK	Serial Clock	
D <sub>OUT</sub>	Serial Data Out	
CS/SHDN	Chip Select/Shutdown Input	
$V_{REF}$	Reference Voltage Input	

## **ELECTRICAL CHARACTERISTICS**

Parameter	Sym	Min	Тур	Max	Units	Conditions
Conversion Rate:						
Conversion Time	t <sub>CONV</sub>	_		12	clock cycles	
Analog Input Sample Time	t <sub>SAMPLE</sub>		1.5		clock cycles	
Throughput Rate	f <sub>SAMPLE</sub>	_		100 50	ksps ksps	$V_{DD} = V_{REF} = 5V$ $V_{DD} = V_{REF} = 2.7V$
DC Accuracy:						
Resolution			12		bits	
Integral Nonlinearity	INL	_	±0.75 ±1	±1 ±2	LSB LSB	MCP3201-B MCP3201-C
Differential Nonlinearity	DNL	_	±0.5	±1	LSB	No missing codes over temperature
Offset Error		_	±1.25	±3	LSB	
Gain Error		_	±1.25	±5	LSB	
Dynamic Performance:						
Total Harmonic Distortion	THD	_	-82	_	dB	$V_{IN} = 0.1V \text{ to } 4.9V@1 \text{ kHz}$
Signal to Noise and Distortion (SINAD)	SINAD	_	72	_	dB	V <sub>IN</sub> = 0.1V to 4.9V@1 kHz
Spurious Free Dynamic Range	SFDR	_	86	_	dB	$V_{IN} = 0.1V \text{ to } 4.9V@1 \text{ kHz}$
Reference Input:						
Voltage Range		0.25	1	$V_{DD}$	V	Note 2
Current Drain		_	100 .001	150 3	μA μA	$\overline{\text{CS}} = \text{V}_{\text{DD}} = 5\text{V}$
Analog Inputs:						
Input Voltage Range (IN+)	IN+	IN-	_	V <sub>REF</sub> +IN-	V	
Input Voltage Range (IN-)	IN-	V <sub>ss</sub> -100		V <sub>SS</sub> +100	mV	
Leakage Current		_	0.001	±1	μA	
Switch Resistance	R <sub>ss</sub>	_	1K	_	W	See Figure 4-1

- Note 1: This parameter is established by characterization and not 100% tested.
  - 2: See graph that relates linearity performance to V<sub>REF</sub> level.
  - 3: Because the sample cap will eventually lose charge, effective clock rates below 10 kHz can affect linearity performance, especially at elevated temperatures. See Section 6.2 for more information.

# **ELECTRICAL CHARACTERISTICS (CONTINUED)**

unless otherwise noted.	T -					_
Parameter	Sym	Min	Тур	Max	Units	Conditions
Sample Capacitor	C <sub>SAMPLE</sub>	_	20	_	pF	See Figure 4-1
Digital Input/Output:						
Data Coding Format		S	traight Bina	ary		
High Level Input Voltage	V <sub>IH</sub>	0.7 V <sub>DD</sub>	_	_	V	
Low Level Input Voltage	V <sub>IL</sub>	_	_	0.3 V <sub>DD</sub>	V	
High Level Output Voltage	V <sub>OH</sub>	4.1	_	_	V	$I_{OH} = -1 \text{ mA}, V_{DD} = 4.5 \text{V}$
Low Level Output Voltage	V <sub>OL</sub>	_	_	0.4	V	$I_{OL} = 1 \text{ mA}, V_{DD} = 4.5 \text{V}$
Input Leakage Current	ILI	-10	_	10	μΑ	$V_{IN} = V_{SS}$ or $V_{DD}$
Output Leakage Current	I <sub>LO</sub>	-10	_	10	μΑ	$V_{OUT} = V_{SS}$ or $V_{DD}$
Pin Capacitance (all inputs/outputs)	C <sub>IN</sub> , C <sub>OUT</sub>	_		10	pF	$V_{DD} = 5.0V$ (Note 1) $T_{AMB} = 25$ °C, f = 1 MHz
Timing Parameters:						
Clock Frequency	f <sub>CLK</sub>	_	_	1.6 0.8	MHz MHz	V <sub>DD</sub> = 5V (Note 3) V <sub>DD</sub> = 2.7V (Note 3)
Clock High Time	t <sub>HI</sub>	312	_	_	ns	
Clock Low Time	t <sub>LO</sub>	312	_	_	ns	
CS Fall To First Rising CLK Edge	t <sub>sucs</sub>	100	_	_	ns	
CLK Fall To Output Data Valid	t <sub>DO</sub>	_	_	200	ns	See Test Circuits, Figure 1-2
CLK Fall To Output Enable	t <sub>EN</sub>	_	_	200	ns	See Test Circuits, Figure 1-2
CS Rise To Output Disable	t <sub>DIS</sub>	_	_	100	ns	See Test Circuits, Figure 1-2 (Note 1)
CS Disable Time	t <sub>csh</sub>	625	_	_	ns	
D <sub>OUT</sub> Rise Time	t <sub>R</sub>	_	_	100	ns	See Test Circuits, Figure 1-2 (Note 1)
D <sub>OUT</sub> Fall Time	t <sub>F</sub>	_	_	100	ns	See Test Circuits, Figure 1-2 (Note 1)
Power Requirements:						
Operating Voltage	$V_{DD}$	2.7	_	5.5	V	
Operating Current	I <sub>DD</sub>	_	300 210	400 —	μΑ μΑ	$V_{DD}$ = 5.0V, $D_{OUT}$ unloaded $V_{DD}$ = 2.7V, $D_{OUT}$ unloaded
Standby Current	I <sub>DDS</sub>	_	0.5	2	μΑ	$\overline{\text{CS}} = \text{V}_{\text{DD}} = 5.0\text{V}$
Temperature Ranges:	•	•	-	•	-	
Specified Temperature Range	T <sub>A</sub>	-40	_	+85	°C	
Operating Temperature Range	T <sub>A</sub>	-40		+85	°C	
Storage Temperature Range	T <sub>A</sub>	-65		+150	°C	
Thermal Package Resistance:						
Thermal Resistance, 8L-PDIP	$q_{JA}$		85	_	°C/W	
Thermal Resistance, 8L-SOIC	$q_{JA}$	_	163	_	°C/W	
Thermal Resistance, 8L-MSOP	$q_{JA}$	_	206	_	°C/W	
Thermal Resistance, 8L-TSSOP	$q_{JA}$	_	124	_	°C/W	

Note 1: This parameter is established by characterization and not 100% tested.

See graph that relates linearity performance to V<sub>REF</sub> level.
 Because the sample cap will eventually lose charge, effective clock rates below 10 kHz can affect linearity performance, especially at elevated temperatures. See Section 6.2 for more information.




FIGURE 1-1: Serial Timing.






FIGURE 1-2: Test Circuits.

#### 2.0 TYPICAL PERFORMANCE CHARACTERISTICS


**Note:** The graphs provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs, the data presented may be outside the specified operating range (e.g., outside specified power supply range) and therefore outside the warranted range.




**FIGURE 2-1:** Integral Nonlinearity (INL) vs. Sample Rate.




**FIGURE 2-2:** Integral Nonlinearity (INL) vs.  $V_{REF.}$ 




**FIGURE 2-3:** Integral Nonlinearity (INL) vs. Code (Representative Part).




**FIGURE 2-4:** Integral Nonlinearity (INL) vs. Sample Rate ( $V_{DD} = 2.7V$ ).




**FIGURE 2-5:** Integral Nonlinearity (INL) vs.  $V_{REF}$  ( $V_{DD} = 2.7V$ ).




**FIGURE 2-6:** Integral Nonlinearity (INL) vs. Code (Representative Part,  $V_{DD} = 2.7V$ ).




**FIGURE 2-7:** Integral Nonlinearity (INL) vs. Temperature.




**FIGURE 2-8:** Differential Nonlinearity (DNL) vs. Sample Rate.




**FIGURE 2-9:** Differential Nonlinearity (DNL) vs.  $V_{REF}$ .




**FIGURE 2-10:** Integral Nonlinearity (INL) vs. Temperature  $(V_{DD} = 2.7V)$ .




**FIGURE 2-11:** Differential Nonlinearity (DNL) vs. Sample Rate  $(V_{DD} = 2.7V)$ .



**FIGURE 2-12:** Differential Nonlinearity (DNL) vs.  $V_{REF}$  ( $V_{DD} = 2.7V$ ).



**FIGURE 2-13:** Differential Nonlinearity (DNL) vs. Code (Representative Part).



**FIGURE 2-14:** Differential Nonlinearity (DNL) vs. Temperature.






FIGURE 2-15: Gain Error vs. V<sub>REF</sub>.



**FIGURE 2-16:** Differential Nonlinearity (DNL) vs. Code (Representative Part,  $V_{\rm DD} = 2.7V$ ).



**FIGURE 2-17:** Differential Nonlinearity (DNL) vs. Temperature  $(V_{DD} = 2.7V)$ .




FIGURE 2-18: Offset Error vs. V<sub>REF</sub>.






FIGURE 2-19: Gain Error vs. Temperature.



**FIGURE 2-20:** Signal to Noise Ratio (SNR) vs. Input Frequency.



**FIGURE 2-21:** Total Harmonic Distortion (THD) vs. Input Frequency.







FIGURE 2-22: Offset Error vs. Temperature.




**FIGURE 2-23:** Signal to Noise and Distortion (SINAD) vs. Input Frequency.




**FIGURE 2-24:** Signal to Noise and Distortion (SINAD) vs. Input Signal Level.




**FIGURE 2-25:** Effective Number of Bits (ENOB) vs.  $V_{REF}$ .




**FIGURE 2-26:** Spurious Free Dynamic Range (SFDR) vs. Input Frequency.




**FIGURE 2-27:** Frequency Spectrum of 10 kHz input (Representative Part).




**FIGURE 2-28:** Effective Number of Bits (ENOB) vs. Input Frequency.



**FIGURE 2-29:** Power Supply Rejection (PSR) vs. Ripple Frequency.



**FIGURE 2-30:** Frequency Spectrum of 1 kHz input (Representative Part,  $V_{DD} = 2.7V$ ).



**FIGURE 2-31:**  $I_{DD}$  vs.  $V_{DD}$ .






FIGURE 2-32: I<sub>DD</sub> vs. Clock Frequency.



**FIGURE 2-33:**  $I_{DD}$  vs. Temperature.



**FIGURE 2-34:**  $I_{REF}$  vs.  $V_{DD}$ .






FIGURE 2-35: I<sub>REF</sub> vs. Clock Frequency.




**FIGURE 2-36:**  $I_{REF}$  vs. Temperature.


 $\textbf{Note:} \ \, \textbf{Unless otherwise indicated,} \ \, \textbf{V}_{\text{DD}} = \textbf{V}_{\text{REF}} = 5 \\ \textbf{V}, \ \, \textbf{V}_{\text{SS}} = 0 \\ \textbf{V}, \ \, \textbf{f}_{\text{SAMPLE}} = 100 \\ \text{ ksps, } \ \, \textbf{f}_{\text{CLK}} = 16 \\ \textbf{f}_{\text{SAMPLE}}, \\ \textbf{T}_{\text{A}} = 25 \\ \textbf{C} \\ \textbf{C}$ 



**FIGURE 2-37:**  $I_{DDS}$  vs.  $V_{DD}$ .



**FIGURE 2-38:**  $I_{DDS}$  vs. Temperature.



**FIGURE 2-39:** Analog Input Leakage Current vs. Temperature.

### 3.0 PIN DESCRIPTIONS

#### 3.1 IN+

Positive analog input. This input can vary from IN- to  $V_{\rm REF}$  + IN-.

#### 3.2 <u>IN-</u>

Negative analog input. This input can vary  $\pm 100 \ \text{mV}$  from  $V_{SS}$ .

## 3.3 Chip Select/Shutdown (CS/SHDN)

The  $\overline{\text{CS}}/\text{SHDN}$  pin is used to initiate communication with the device when pulled low and will end a conversion and put the device in low power standby when pulled high. The  $\overline{\text{CS}}/\text{SHDN}$  pin must be pulled high between conversions.

#### 3.4 Serial Clock (CLK)

The SPI clock pin is used to initiate a conversion and to clock out each bit of the conversion as it takes place. See Section 6.2 for constraints on clock speed.

#### 3.5 Serial Data Output (DOUT)

The SPI serial data output pin is used to shift out the results of the A/D conversion. Data will always change on the falling edge of each clock as the conversion takes place.

#### 4.0 DEVICE OPERATION

The MCP3201 A/D Converter employs a conventional SAR architecture. With this architecture, a sample is acquired on an internal sample/hold capacitor for 1.5 clock cycles starting on the first rising edge of the serial clock after  $\overline{CS}$  has been pulled low. Following this sample time, the input switch of the converter opens and the device uses the collected charge on the internal sample and hold capacitor to produce a serial 12-bit digital output code. Conversion rates of 100 ksps are possible on the MCP3201. See Section 6.2 for information on minimum clock rates. Communication with the device is done using a 3-wire SPI-compatible interface.

#### 4.1 Analog Inputs

The MCP3201 provides a single pseudo-differential input. The IN+ input can range from IN- to  $V_{\text{REF}}$  ( $V_{\text{REF}}$ +IN-). The IN- input is limited to  $\pm 100$  mV from the  $V_{\text{SS}}$  rail. The IN- input can be used to cancel small signal common-mode noise which is present on both the IN+ and IN- inputs.

For the A/D Converter to meet specification, the charge holding capacitor ( $C_{\text{SAMPLE}}$ ) must be given enough time to acquire a 12-bit accurate voltage level during the 1.5 clock cycle sampling period. The analog input model is shown in Figure 4-1.

In this diagram, it is shown that the source impedance  $(R_S)$  adds to the internal sampling switch  $(R_{SS})$  impedance, directly affecting the time that is required to charge the capacitor  $(C_{SAMPLE})$ . Consequently, a larger source impedance increases the offset, gain, and integral linearity errors of the conversion.

Ideally, the impedance of the signal source should be near zero. This is achievable with an operational amplifier such as the MCP601, which has a closed loop output impedance of tens of ohms. The adverse affects of higher source impedances are shown in Figure 4-2.

If the voltage level of IN+ is equal to or less than IN-, the resultant code will be 000h. If the voltage at IN+ is equal to or greater than  $\{[V_{REF} + (IN-)] - 1 LSB\}$ , then the output code will be FFFh. If the voltage level at IN- is more than 1 LSB below  $V_{SS}$ , then the voltage level at the IN+ input will have to go below  $V_{SS}$  to see the 000h output code. Conversely, if IN- is more than 1 LSB above Vss, then the FFFh code will not be seen unless the IN+ input level goes above  $V_{RFF}$  level.

## 4.2 Reference Input

The reference input  $(V_{REF})$  determines the analog input voltage range and the LSB size, as shown below.

$$LSB \ Size = \frac{V_{REF}}{4096}$$

As the reference input is reduced, the LSB size is reduced accordingly. The theoretical digital output code produced by the A/D Converter is a function of the analog input signal and the reference input as shown below.

Digital Output Code = 
$$\frac{4096*V_{IN}}{V_{REE}}$$

where:

$$V_{IN}$$
 = analog input voltage =  $V(IN+)$  -  $V(IN-)$   
 $V_{REF}$  = reference voltage

When using an external voltage reference device, the system designer should always refer to the manufacturer's recommendations for circuit layout. Any instability in the operation of the reference device will have a direct effect on the operation of the A/D Converter.





FIGURE 4-1: Analog Input Model.



**FIGURE 4-2:** Maximum Clock Frequency vs. Input Resistance ( $R_{\rm S}$ ) to maintain less than a 0.1 LSB deviation in INL from nominal conditions.

#### 5.0 SERIAL COMMUNICATIONS

Communication with the device is done using a standard SPI-compatible serial interface. Initiating communication with the MCP3201 begins with the  $\overline{CS}$  going low. If the device was powered up with the  $\overline{CS}$  pin low, it must be brought high and back low to initiate communication. The device will begin to sample the analog input on the first rising edge after  $\overline{CS}$  goes low. The sample period will end in the falling edge of the second clock, at which time the device will output a low null bit. The next 12 clocks will output the result of the conver-

sion with MSB first, as shown in Figure 5-1. Data is always output from the device on the falling edge of the clock. If all 12 data bits have been transmitted and the device continues to receive clocks while the  $\overline{\text{CS}}$  is held low, the device will output the conversion result LSB first, as shown in Figure 5-2. If more clocks are provided to the device while  $\overline{\text{CS}}$  is still low (after the LSB first data has been transmitted), the device will clock out zeros indefinitely.




FIGURE 5-1: Communication with MCP3201 using MSB first Format.




FIGURE 5-2: Communication with MCP3201 using LSB first Format.

### 6.0 APPLICATIONS INFORMATION

### 6.1 <u>Using the MCP3201 with</u> Microcontroller SPI Ports

With most microcontroller SPI ports, it is required to clock out eight bits at a time. If this is the case, it will be necessary to provide more clocks than are required for the MCP3201. As an example, Figure 6-1 and Figure 6-2 show how the MCP3201 can be interfaced to a microcontroller with a standard SPI port. Since the MCP3201 always clocks data out on the falling edge of clock, the MCU SPI port must be configured to match this operation. SPI Mode 0,0 (clock idles low) and SPI Mode 1.1 (clock idles high) are both compatible with the MCP3201. Figure 6-1 depicts the operation shown in SPI Mode 0,0, which requires that the CLK from the microcontroller idles in the 'low' state. As shown in the diagram, the MSB is clocked out of the A/D Converter on the falling edge of the third clock pulse. After the first eight clocks have been sent to the device, the microcontroller's receive buffer will contain two unknown bits (the output is at high impedance for the first two clocks), the null bit and the highest order five bits of the conversion. After the second eight clocks have been sent to the device, the MCU receive register will contain the lowest order seven bits and the B1 bit repeated as the A/D Converter has begun to shift out LSB first data with the extra clock. Typical procedure would then call for the lower order byte of data to be shifted right by one bit to remove the extra B1 bit. The B7 bit is then transferred from the high order byte to the lower order byte, and then the higher order byte is shifted one bit to the right as well. Easier manipulation of the converted data can be obtained by using this method.

Figure 6-2 shows the same thing in SPI Mode 1,1 which requires that the clock idles in the high state. As with mode 0,0, the A/D Converter outputs data on the falling edge of the clock and the MCU latches data from the A/D Converter in on the rising edge of the clock.




FIGURE 6-1: SPI Communication using 8-bit segments (Mode 0,0: SCLK idles low).




FIGURE 6-2: SPI Communication using 8-bit segments (Mode 1,1: SCLK idles high).


#### 6.2 <u>Maintaining Minimum Clock Speed</u>

When the MCP3201 initiates the sample period, charge is stored on the sample capacitor. When the sample period is complete, the device converts one bit for each clock that is received. It is important for the user to note that a slow clock rate will allow charge to bleed off the sample cap while the conversion is taking place. At 85°C (worst case condition), the part will maintain proper charge on the sample capacitor for at least 1.2 ms after the sample period has ended. This means that the time between the end of the sample period and the time that all 12 data bits have been clocked out must not exceed 1.2 ms (effective clock frequency of 10 kHz). Failure to meet this criteria may induce linearity errors into the conversion outside the rated specifications. It should be noted that during the entire conversion cycle, the A/D Converter does not require a constant clock speed or duty cycle, as long as all timing specifications are met.

#### 6.3 <u>Buffering/Filtering the Analog Inputs</u>

If the signal source for the A/D Converter is not a low impedance source, it will have to be buffered or inaccurate conversion results may occur. See Figure 4-2. It is also recommended that a filter be used to eliminate any signals that may be aliased back into the conversion results. This is illustrated in Figure 6-3 where an op amp is used to drive the analog input of the MCP3201. This amplifier provides a low impedance source for the converter input and a low pass filter, which eliminates unwanted high frequency noise.

Low pass (anti-aliasing) filters can be designed using Microchip's interactive FilterLab™ software. FilterLab will calculate capacitor and resistor values, as well as determine the number of poles that are required for the application. For more information on filtering signals, see the application note AN699 "Anti-Aliasing Analog Filters for Data Acquisition Systems."




**FIGURE 6-3:** The MCP601 Operational Amplifier is used to implement a 2nd order anti-aliasing filter for the signal being converted by the MCP3201.

#### 6.4 Layout Considerations

When laying out a printed circuit board for use with analog components, care should be taken to reduce noise wherever possible. A bypass capacitor should always be used with this device and should be placed as close as possible to the device pin. A bypass capacitor value of 1 µF is recommended.

Digital and analog traces should be separated as much as possible on the board and no traces should run underneath the device or the bypass capacitor. Extra precautions should be taken to keep traces with high frequency signals (such as clock lines) as far as possible from analog traces.


Use of an analog ground plane is recommended in order to keep the ground potential the same for all devices on the board. Providing V<sub>DD</sub> connections to devices in a "star" configuration can also reduce noise by eliminating current return paths and associated errors. See Figure 6-4. For more information on layout tips when using A/D Converter, refer to AN688 "Layout Tips for 12-Bit A/D Converter Applications".




**FIGURE 6-4:**  $V_{DD}$  traces arranged in a 'Star' configuration in order to reduce errors caused by current return paths.

#### 7.0 PACKAGING INFORMATION

### 7.1 Package Marking Information






8-Lead MSOP



8-Lead TSSOP







Example:



Example:



Legend: XX...X Customer-specific information

Y Year code (last digit of calendar year)
YY Year code (last 2 digits of calendar year)
WW Week code (week of January 1 is week '01')

NNN Alphanumeric traceability code

(e3) Pb-free JEDEC designator for Matte Tin (Sn)


This package is Pb-free. The Pb-free JEDEC designator (e3)

can be found on the outer packaging for this package.

**Note:** In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information.

# 8-Lead Plastic Dual In-Line (P) - 300 mil Body [PDIP]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units		INCHES	
Dimensio	n Limits	MIN	NOM	MAX
Number of Pins	N		8	
Pitch	е		.100 BSC	
Top to Seating Plane	Α	-	-	.210
Molded Package Thickness	A2	.115	.130	.195
Base to Seating Plane	A1	.015	-	_
Shoulder to Shoulder Width	Е	.290	.310	.325
Molded Package Width	E1	.240	.250	.280
Overall Length	D	.348	.365	.400
Tip to Seating Plane	L	.115	.130	.150
Lead Thickness	С	.008	.010	.015
Upper Lead Width	b1	.040	.060	.070
Lower Lead Width	b	.014	.018	.022
Overall Row Spacing §	eB	_	_	.430

#### Notes:


- 1. Pin 1 visual index feature may vary, but must be located with the hatched area.
- 2. § Significant Characteristic.
- 3. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed .010" per side.
- 4. Dimensioning and tolerancing per ASME Y14.5M.

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing C04-018B

# 8-Lead Plastic Small Outline (SN) - Narrow, 3.90 mm Body [SOIC]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units		MILLMETERS	
Dimension	on Limits	MIN	NOM	MAX
Number of Pins	Ν		8	
Pitch	е	1.27 BSC		
Overall Height	Α	-	-	1.75
Molded Package Thickness	A2	1.25	-	-
Standoff §	A1	0.10	-	0.25
Overall Width	Е	6.00 BSC		
Molded Package Width	E1	3.90 BSC		
Overall Length	D		4.90 BSC	
Chamfer (optional)	h	0.25	-	0.50
Foot Length	L	0.40	-	1.27
Footprint	L1		1.04 REF	
Foot Angle	ф	0°	-	8°
Lead Thickness	С	0.17	_	0.25
Lead Width	b	0.31	_	0.51
Mold Draft Angle Top	α	5°	-	15°
Mold Draft Angle Bottom	β	5°	_	15°


#### Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. § Significant Characteristic.
- 3. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.15 mm per side.
- 4. Dimensioning and tolerancing per ASME Y14.5M.
  - BSC: Basic Dimension. Theoretically exact value shown without tolerances.
  - REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-057B

# 8-Lead Plastic Micro Small Outline Package (MS) [MSOP]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units		MILLIMETERS	;
Dimension	n Limits	MIN	NOM	MAX
Number of Pins	N		8	
Pitch	е		0.65 BSC	
Overall Height	Α	_	_	1.10
Molded Package Thickness	A2	0.75	0.85	0.95
Standoff	A1	0.00	_	0.15
Overall Width	Е	4.90 BSC		
Molded Package Width	E1	3.00 BSC		
Overall Length	D	3.00 BSC		
Foot Length	L	0.40	0.60	0.80
Footprint	L1		0.95 REF	
Foot Angle	ф	0°	_	8°
Lead Thickness	С	0.08	-	0.23
Lead Width	b	0.22	_	0.40

### Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.15 mm per side.
- 3. Dimensioning and tolerancing per ASME Y14.5M.


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-111B

# 8-Lead Plastic Thin Shrink Small Outline (ST) – 4.4 mm Body [TSSOP]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units		MILLIMETERS	3
Dimensio	n Limits	MIN	NOM	MAX
Number of Pins	N		8	
Pitch	е		0.65 BSC	
Overall Height	Α	_	_	1.20
Molded Package Thickness	A2	0.80	1.00	1.05
Standoff	A1	0.05	-	0.15
Overall Width	Е		6.40 BSC	-
Molded Package Width	E1	4.30	4.40	4.50
Molded Package Length	D	2.90	3.00	3.10
Foot Length	L	0.45	0.60	0.75
Footprint	L1		1.00 REF	•
Foot Angle	ф	0°	_	8°
Lead Thickness	С	0.09	_	0.20
Lead Width	b	0.19	_	0.30

#### Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.15 mm per side.
- 3. Dimensioning and tolerancing per ASME Y14.5M.
  - BSC: Basic Dimension. Theoretically exact value shown without tolerances.
  - REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-086B

<b>MCP320</b>	1	
---------------	---	--

NOTES:

# **APPENDIX A: REVISION HISTORY**

Revision D (January 2007)

This revision includes updates to the packaging diagrams.

# **MCP3201**

NOTES:

# PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales office.

PART NO.	<u>x</u>	Examples:
Device T	emperature Package Range	a) MCP3201-I/P: Industrial Temperature,     PDIP package.     b) MCP3201-I/SN: Industrial Temperature,
Device:	MCP3201: 12-Bit A/D Converter w/SPI Interface MCP3201T: 12-Bit A/D Converter w/SPI Interface (Tape and Reel) (SOIC and TSSOP only)	solC package.  c) MCP3201-I/ST: Industrial Temperature, TSSOP package.  d) MCP3201-I/MS: Industrial Temperature, MSOP package.
Temperature Range:	I = -40°C to +85°C	
Package:	MS = Plastic Micro Small Outline (MSOP), 8-lead P = Plastic DIP (300 mil Body), 8-lead SN = Plastic SOIC (150 mil Body), 8-lead ST = Plastic TSSOP (4.4 mm), 8-lead	

# **MCP3201**

**NOTES:** 

#### Note the following details of the code protection feature on Microchip devices:

- · Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the
  intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights.

#### **Trademarks**

The Microchip name and logo, the Microchip logo, Accuron, dsPIC, Keeloq, microID, MPLAB, PIC, PICmicro, PICSTART, PRO MATE, PowerSmart, rfPIC, and SmartShunt are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AmpLab, FilterLab, Migratable Memory, MXDEV, MXLAB, SEEVAL, SmartSensor and The Embedded Control Solutions Company are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Analog-for-the-Digital Age, Application Maestro, CodeGuard, dsPICDEM, dsPICDEM.net, dsPICworks, ECAN, ECONOMONITOR, FanSense, FlexROM, fuzzyLAB, In-Circuit Serial Programming, ICSP, ICEPIC, Linear Active Thermistor, Mindi, MiWi, MPASM, MPLIB, MPLINK, PICkit, PICDEM, PICDEM.net, PICLAB, PICtail, PowerCal, PowerInfo, PowerMate, PowerTool, REAL ICE, rfLAB, rfPICDEM, Select Mode, Smart Serial, SmartTel, Total Endurance, UNI/O, WiperLock and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

All other trademarks mentioned herein are property of their respective companies.

© 2007, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.

Printed on recycled paper.

QUALITY MANAGEMENT SYSTEM

CERTIFIED BY DNV

ISO/TS 16949:2002

Microchip received ISO/TS-16949:2002 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona, Gresham, Oregon and Mountain View, California. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC DSCs, KEELOQ® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and manufacture of development systems is ISO 9001:2000 certified.



# WORLDWIDE SALES AND SERVICE

#### **AMERICAS**

**Corporate Office** 

2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200

Fax: 480-792-7277 Technical Support:

http://support.microchip.com

Web Address: www.microchip.com

Atlanta

Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

**Boston** 

Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL

Tel: 630-285-0071 Fax: 630-285-0075

Dallas

Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit

Farmington Hills, MI Tel: 248-538-2250 Fax: 248-538-2260

Kokomo

Kokomo, IN Tel: 765-864-8360 Fax: 765-864-8387

Los Angeles

Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608

Santa Clara

Santa Clara, CA Tel: 408-961-6444 Fax: 408-961-6445

**Toronto** 

Mississauga, Ontario, Canada

Tel: 905-673-0699 Fax: 905-673-6509

#### ASIA/PACIFIC

**Asia Pacific Office** 

Suites 3707-14, 37th Floor Tower 6, The Gateway Habour City, Kowloon Hong Kong

Tel: 852-2401-1200 Fax: 852-2401-3431

Australia - Sydney

Tel: 61-2-9868-6733 Fax: 61-2-9868-6755

China - Beijing

Tel: 86-10-8528-2100 Fax: 86-10-8528-2104

China - Chengdu

Tel: 86-28-8665-5511 Fax: 86-28-8665-7889

China - Fuzhou

Tel: 86-591-8750-3506 Fax: 86-591-8750-3521

China - Hong Kong SAR

Tel: 852-2401-1200 Fax: 852-2401-3431

China - Qingdao

Tel: 86-532-8502-7355 Fax: 86-532-8502-7205

China - Shanghai

Tel: 86-21-5407-5533 Fax: 86-21-5407-5066

China - Shenyang

Tel: 86-24-2334-2829 Fax: 86-24-2334-2393

China - Shenzhen

Tel: 86-755-8203-2660 Fax: 86-755-8203-1760

China - Shunde

Tel: 86-757-2839-5507 Fax: 86-757-2839-5571

China - Wuhan

Tel: 86-27-5980-5300 Fax: 86-27-5980-5118

China - Xian

Tel: 86-29-8833-7250 Fax: 86-29-8833-7256

#### ASIA/PACIFIC

India - Bangalore

Tel: 91-80-4182-8400 Fax: 91-80-4182-8422

India - New Delhi

Tel: 91-11-4160-8631 Fax: 91-11-4160-8632

India - Pune

Tel: 91-20-2566-1512 Fax: 91-20-2566-1513

Japan - Yokohama

Tel: 81-45-471- 6166 Fax: 81-45-471-6122

Korea - Gumi

Tel: 82-54-473-4301 Fax: 82-54-473-4302

Korea - Seoul

Tel: 82-2-554-7200 Fax: 82-2-558-5932 or 82-2-558-5934

Malaysia - Penang Tel: 60-4-646-8870 Fax: 60-4-646-5086

Philippines - Manila

Tel: 63-2-634-9065 Fax: 63-2-634-9069

Singapore Tel: 65-6334-8870

Fax: 65-6334-8850 Taiwan - Hsin Chu

Tel: 886-3-572-9526

Fax: 886-3-572-6459

Taiwan - Kaohsiung Tel: 886-7-536-4818

Fax: 886-7-536-4803

Taiwan - Taipei

Tel: 886-2-2500-6610 Fax: 886-2-2508-0102

Thailand - Bangkok

Tel: 66-2-694-1351 Fax: 66-2-694-1350

#### **EUROPE**

Austria - Wels

Tel: 43-7242-2244-39 Fax: 43-7242-2244-393 Denmark - Copenhagen

Tel: 45-4450-2828 Fax: 45-4485-2829

France - Paris

Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79

Germany - Munich

Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Italy - Milan

Tel: 39-0331-742611 Fax: 39-0331-466781

Netherlands - Drunen

Tel: 31-416-690399 Fax: 31-416-690340

Spain - Madrid

Tel: 34-91-708-08-90 Fax: 34-91-708-08-91 **UK - Wokingham** 

Tel: 44-118-921-5869 Fax: 44-118-921-5820

12/08/06