

Multi-range thread milling cutter solid carbide TiAlN (G) without internal cooling straight shank HA

for universal use up to 1500 N/mm² in male and female threads

ATORN[®]



Application

For producing right-hand and left-hand **pipe threads** on CNC machines in through holes and blind holes in the steel, stainless steel, non-ferrous metals, cast iron and special alloy material groups up to a strength of 1500 N/mm².

Advantage

- Innovative cutting geometry for very high dimensional accuracy, process reliability and chip removal.

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GJMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
		90	80	80	60			160	16	140	140	180	120	70					

Art. no.	13496 367
Cutting material	VHM
Surface	TiAlN
Hole type	Clearance/blind hole ≤ 2xD
Coolant supply	External
Tool holding device	HA parallel shank
Cutting edge diameter	16 mm
Suitable from thread size	G 1 inch
Length	105 mm
Cutting edge length	38.1 mm
Shaft diameter	16 mm
Number of cutting edges	4 PCS
f steel 1000	0.12 mm/r

EAN-Code

4050293206487