

I08H010

Part Number

weproTec



- Increased switching distance
- Innovative ASIC circuit technology
- Integrated error display
- Minimal mounting clearance thanks to wenglor weproTec

Inductive Sensors with increased switching distances are distinguished by rugged design, easy installation and reliable measured values. The large range makes additional types of sensor superfluous because they can also be used to implement special applications. In addition to error-free operation of several sensors in a very small space, the new generation also provides the possibility of detecting system errors before it's too late thanks to ASIC und wenglor weproTec.

Technical Data

Inductive Data

| | |
|--|---------------|
| Switching Distance | 4 mm |
| Correction Factors Stainless Steel V2A/CuZn/Al | 1,06/0,5/0,48 |
| Mounting | semi-flush |
| Mounting A/B/C/D in mm | 8/11/12/3 |
| Mounting B1 in mm | 0...6 |
| Switching Hysteresis | < 10 % |

Electrical Data

| | |
|---|--------------|
| Supply Voltage | 10...30 V DC |
| Current Consumption (U _b = 24 V) | < 11 mA |
| Switching Frequency | 630 Hz |
| Temperature Drift | < 10 % |
| Temperature Range | -40...80 °C |
| Switching Output Voltage Drop | < 1 V |
| Switching Output/Switching Current | 150 mA |
| Residual Current Switching Output | < 100 µA |
| Short Circuit Protection | yes |
| Reverse Polarity and Overload Protection | yes |
| Protection Class | III |

Mechanical Data

| | |
|-----------------------|---------------------|
| Housing Material | CuZn, nickel-plated |
| Degree of Protection | IP67 |
| Connection | Cable, 3-wire, 2 m |
| Cable Jacket Material | PVC |



Safety-relevant Data

| | |
|------------------------|-----------|
| MTTFd (EN ISO 13849-1) | 3706,54 a |
|------------------------|-----------|

Function

| | |
|----------------------------------|-------------------------------------|
| Error Indicator | yes |
| PNP NC | <input checked="" type="checkbox"/> |
| Connection Diagram No. | 206 |
| Suitable Mounting Technology No. | 200 202 |

* Temperature range with permanently installed cable, bending radius: > 40 mm



| Legend | | | |
|-----------|--|-----------|------------------------------------|
| + | Supply Voltage + | PT | Platinum measuring resistor |
| - | Supply Voltage 0 V | nc | not connected |
| ~ | Supply Voltage (AC Voltage) | U | Test Input |
| A | Switching Output (NO) | Ū | Test Input inverted |
| Ā | Switching Output (NC) | W | Trigger Input |
| V | Contamination/Error Output (NO) | W- | Ground for the Trigger Input |
| Ṽ | Contamination/Error Output (NC) | O | Analog Output |
| E | Input (analog or digital) | O- | Ground for the Analog Output |
| T | Teach Input | BZ | Block Discharge |
| Z | Time Delay (activation) | AWV | Valve Output |
| S | Shielding | a | Valve Control Output + |
| RxD | Interface Receive Path | b | Valve Control Output 0 V |
| TxD | Interface Send Path | SY | Synchronization |
| RDY | Ready | SY- | Ground for the Synchronization |
| GND | Ground | E+ | Receiver-Line |
| CL | Clock | S+ | Emitter-Line |
| E/A | Output/Input programmable | ± | Grounding |
| | IO-Link | SnR | Switching Distance Reduction |
| PoE | Power over Ethernet | Rx+/- | Ethernet Receive Path |
| IN | Safety Input | Tx+/- | Ethernet Send Path |
| OSSD | Safety Output | Bus | Interfaces-Bus A(+)/B(-) |
| Signal | Signal Output | La | Emitted Light disengageable |
| Bl..D+/- | Ethernet Gigabit bidirect. data line (A-D) | Mag | Magnet activation |
| EN0..5A2Z | Encoder 0-pulse 0-0 (TTL) | RES | Input confirmation |
| | | EDM | Contacting Monitoring |
| | | EN1..5A2Z | Encoder A/Ā (TTL) |
| | | EN2..5A2Z | Encoder B/B̄ (TTL) |
| | | ENa | Encoder A |
| | | ENb | Encoder B |
| | | AMIN | Digital output MIN |
| | | AMAX | Digital output MAX |
| | | AOk | Digital output OK |
| | | SY In | Synchronization In |
| | | SY OUT | Synchronization OUT |
| | | OLt | Brightness output |
| | | M | Maintenance reserved |
| | | rsv | reserved |
| | | | Wire Colors according to IEC 60757 |
| | | BK | Black |
| | | BN | Brown |
| | | RD | Red |
| | | OG | Orange |
| | | YE | Yellow |
| | | GN | Green |
| | | BU | Blue |
| | | VT | Violet |
| | | GY | Grey |
| | | WH | White |
| | | PK | Pink |
| | | GNYE | Green/Yellow |

Mounting

