



# V1255.01 ROCKY IGS

BROWN WATERPROOF ZIP SIDE HIGH LEG BOOT



With full grain waterproof cowhide leather and a breathable membrane, the Rocky IGS has been created to a new extreme comfort shape for daylong comfort. With a waterproof covered zip and a traditional lace system, it is the perfect combination of easy access and adjustability. A composite toecap and midsole regulates temperature no matter the weather, and a scuff cap and ankle support provide comfort and durability. The innovative IGS rubber sole unit ensures superb grip on all terrains.

## CE Specification

EN ISO 20345:2011 S3 HRO SRC

## Size

5 - 13 (38 - 48)



HEAT  
RESISTANT



ANTI STATIC



COMPOSITE  
TOE CAP



COMPOSITE  
MIDSOLE



WATERPROOF  
BREATHABLE

## Upper

Waterproof oiled full grain hide upper, with a waterproof covered zip and full bellows tongue to prevent water and dirt ingress. Scuff cap and rugged ankle support.

## Lining

Waterproof lining that is breathable to reduce perspiration.

## Footbed

Heel pump shock absorbing footbed. Contoured to support the foot, with air channels to wick moisture and reduce heat build up and odour.

## Toecap

Wide fitting composite non sparking and thermal insulating. Tested to impact of 200 Joules.

## Protective midsole

A woven fibre midsole designed to protect from sharp objects entering underfoot.

## Sole

Inspired by tyre technology and made from highly durable rubber, the IGS sole unit features a unique hexagonal tread ensuring superior traction, ladder grips offering firefighter levels of safety and a re-designed heel strike pad delivering exceptional water dispersal. The IGS is heat resistant to approximately 300°C. Non-marking and resistant to diesel, fat, acid and alkali.



## Safety Standards

Classification	Test to achieve classification	Safety Standards				
		S1	S2	S3	SBP	S1P
<b>SB</b>	Toe protection tested with 200J impact and 15kN compression force	●	●	●	●	●
<b>P</b>	Penetration resistant outsole tested at 1100 newtons			●	●	●
<b>A</b>	Electrical resistance between foot and ground of between 0.1 and 1000 mega ohms	●	●	●		●
<b>E</b>	Energy absorption of the seat region tested at 20 joules	●	●	●		●
<b>WRU</b>	Water resistant upper leather		●	●		

The below are further tests that can be added to the above classifications (e.g. S3 HRO)

<b>HRO</b>	Heat resistant outsole compound tested at 300°C
<b>CI</b>	Insulation against the cold - temperature drops less than 10°C when tested at -17°C
<b>M</b>	Metatarsal protection - tested to 100J impact

The below are further tests that can be added to the above classifications (e.g. S3 HRO SRC)

<b>SRA</b>	Slip resistant on ceramic tile floor with sodium lauryl sulphate solution
<b>SRB</b>	Slip resistant on steel floor with glycerol
<b>SRC</b>	Slip resistant for both SRA and SRB

## Anti-fatigue footwear solutions

Poor fitting footwear can cause all sorts of problems for your feet. Below we've listed a few common complaints, possible causes and simple ways of solving footwear problems.

Complaint	Possible cause	Suggested action
<b>Ingrowing toenails</b>	Nails cut too short. Very painful if knocked.	Cut nails square and wear wide fitting footwear with padded interior to protect toes.
<b>Aching feet</b>	Stiff footwear or footwear that flexes in the middle of the arch instead of at the ball of the foot.	Wear footwear with a shank. This is essential to make the footwear bend with the foot and not against it.
<b>Athlete's foot</b> A fungal infection which thrives in dark damp places.	Sweaty footwear, or damp footwear which has not been allowed to dry out. Fungal infections can spread very quickly from one foot to the other.	Wear breathable footwear and make sure shoes dry out well overnight. Full grain leather is essential if leather footwear is required. Buy a new pair of insoles and use a recommended powder, available from chemists.
<b>Hammer toe</b> Toe(s) curl over and stiffen in deformed position.	Footwear that is too small or too narrow, causing toes to bunch up.	Wear footwear that is wider fitting and correct size. All the V12 Footwear is wide fitting.
<b>Bunions /corns</b> Hard patches of skin on toes.	Narrow toed ill fitting footwear.	Wear wider fitting footwear to ensure foot freedom.
<b>Plantar fasciitis</b> Inflammation of tissue on the bottom of the heel.	Poor quality footwear with little or no shock absorption.	Wear the V Shok II footwear to cushion the heel and consult your doctor.

## Shoe care

"At the end of a day's work, the removable footbeds should be pulled half out of the boots to help make sure that they dry out and air properly overnight. If you don't do this you risk the boots becoming smelly and create ideal conditions for bacteria to thrive in."

"If you get your boots really muddy, brush the worst off then wipe them down with warm water and let them dry naturally. Don't put them on top of the boiler or in the airing cupboard as this will increase the tendency to crack the leather."

"Once a month, take out the replaceable insoles and stick them through the washing machine for a freshen up."

"When leather gets wet repeatedly, the natural oils eventually get washed out and if they are not replaced the leather will crack. You should periodically treat your boots to a dose of Chelsea Leather Food. This will feed and rejuvenate the leather and maintain its water resistant qualities."

"It's worth investing in good quality socks made of cotton or other natural material. Besides being another layer of cushioning and insulation, socks play the vital role of wicking moisture away from the foot."