

ROLINE Gigabit Ethernet Switch, 6x (5xGbE + 1x Gbic(SFP)), managed

Product No.	21.14.3523
Manufacturer	ROLINE
Manufacturer No.	21.14.3523
EAN (single piece)	7611990138128



Managed 5-Port Gigabit network switch for use in a industrial environment - including an additional SFP-Port!

- Provides 5x TP 10/100/1000Mbps Gigabit Ethernet ports and 1x Gbic (SFP) 100/1000Mbps
- Fibre: MultiMode 50/125µm, 60/125µm, SingleMode 9/125µm
- All 10/100/1000M ports support auto-negotiation and auto-MDI/MDI-X detection
- Supports full/half-duplex transfer mode for 10/100Mbps
- Supports full-duplex transfer mode for 1000Mbps
- Store-and-Forward switching method
- Supports SFP with Digital Diagnostic Monitoring (DDM)
- Provides Automatic Laser Shutdown (ALS) function
- Provides fiber optical power Alarm (OPA) function
- Alarm e-mail notification
- Wire-speed packet filtering and forwarding rate
- Supports IEEE 802.3x flow control
- MAC Address Table: 8K
- Buffer Memory: 0.5 MB
- LED Indication
- Environment Operating Temperature: 0°C - 40°C (main device)
- Dimensions (WxDxH): 144 x 104.5 x 26 mm

Technical specifications

Manufacturer	ROLINE
Product group	Network Switches
Product type	Gigabit Ethernet Switch
Colour	grey
Scope of delivery	Switch, power supply (5V DC, 2A), manual
Network standard	Gigabit Ethernet
LAN (Mbps)	10/100/1000
Quantity of ports	6
Gigabit Ethernet Ports	5
RJ-45	
Gigabit Ethernet Ports	1
Fibre	
Stackable	No
Dimensions (HxWxD)	144 x 104.5 x 26 mm
Power supply unit (internal/external)	External