


## Inset Kit LED IP23

*INSET TREND KIT SW REFLED ES50 36° WH NW DIM*  
3001761



### Product features

- GU10 Housing with REFLED ES50 36° lamp included, Ideal for indoor application, Loop in - loop out box included



### PRODUCT OVERVIEW

Product name	INSET TREND KIT SW REFLED ES50 36° WH NW DIM
Technology	LED
Cap/Base	GU10
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
E-number FI	4270033
E-number SE	7468150
Warranty	3 years
Fixture luminous flux (lm)	345
Luminaire efficacy (lm/W)	76
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Beam Angle (°)	36
Photobiological Risk Group	RG1
Light source included	0029128
Total power consumption (W)	4.5
Electrical protection	Class II
Control gear type	LED driver constant current
Dimmable	No
Dimming method	Mains: leading / trailing edge
Housing colour	White
IP rating	IP23/20
IK rating	IK02
Product EAN number	8711971017615

## Inset Kit LED IP23

*INSET TREND KIT SW REFLED ES50 36° WH NW DIM*  
3001761

### DATA TABLE

#### General data

<b>Product name</b>	INSET TREND KIT SW REFLED ES50 36° WH NW DIM
<b>Technology</b>	LED
<b>Cap/Base</b>	GU10
<b>Housing</b>	Aluminium
<b>Mount</b>	Ceiling recessed mounting
<b>Environment</b>	Indoor
<b>General application</b>	Hospitality, Residential & Consumer
<b>ETIM Class</b>	EC001744
<b>E-number FI</b>	4270033
<b>E-number SE</b>	7468150
<b>Warranty</b>	3 years

#### Optical data

<b>Fixture luminous flux (lm)</b>	345
<b>Luminaire efficacy (lm/W)</b>	76
<b>LOR (%)</b>	100
<b>Colour temperature (K)</b>	4000
<b>Light colour</b>	Neutral White
<b>CRI (Ra)</b>	80
<b>Colour Variation Initial (SDCM)</b>	SDCM6
<b>Adjustable chromaticity</b>	N
<b>Beam Angle (°)</b>	36
<b>Distribution type</b>	Symmetric
<b>Photobiological Risk Group</b>	RG1

#### Electrical data

<b>Light source included</b>	0029128
<b>Total power consumption (W)</b>	4.5
<b>Mains voltage (V)</b>	220-240V
<b>Electrical protection</b>	Class II
<b>Control gear type</b>	LED driver constant current
<b>Transformer required</b>	Yes
<b>Dimmable</b>	No
<b>Dimming method</b>	Mains: leading / trailing edge
<b>Glow Wire Test (°C)</b>	650
<b>Energy Efficiency Class (A-&gt;G) of contained light source</b>	F

#### Physical data

<b>Housing colour</b>	White
<b>IP rating</b>	IP23/20
<b>IK rating</b>	IK02
<b>Diffuser finish</b>	Other
<b>Diffuser material</b>	None
<b>Reflector finish</b>	None
<b>Nominal Product Height (mm)</b>	85

## Inset Kit LED IP23

*INSET TREND KIT SW REFLED ES50 36° WH NW DIM*

3001761

Nominal Product Diameter (mm)	83
Cutout Dimensions (W x L in mm or Diameter in mm)	75
Weight (kg)	0.181
Recessed Depth (mm)	100

### Packaging

Single packaging type	Carton
Product EAN number	8711971017615
Packaging single length / height (cm)	13.0
Packaging single width (cm)	9.9
Packaging single depth (cm)	8.5
DUN14 (outer)	18711971017612
Units per outer package	30
Packaging outer length / height (cm)	28.8
Packaging outer width (cm)	28.5
Packaging outer depth (cm)	52.5

## PHOTOMETRY

## TECHNICAL DRAWINGS

