

Revolving centring points

With extended 60°/60° moving point

ATORN[®]

Application

Perfect all-purpose point for universal use on manual lathes. Particularly suitable for copy turning. The extended moving point makes it easy to move the lathe tool up to the flat side of the workpiece.

Version

- Tool fully hardened and polished
- Bearings positioned to accommodate high axial forces
- Concentricity tolerance max. 0.005 mm

Advantage

- Radial shaft seal prevents the ingress of dirt and coolant



Art. No.	22134 060
Morse taper size	MK 5
Programming size	86 mm
Programming size for housing	93.5 mm
Max. workpiece weight	550 kg
Max. rotation speed	3200 U/min(rpm)
Concentricity tolerance	0.005 mm
Diameter of housing	86 mm
Tip diameter	19 mm

EAN-Code

4050293272536