

Slides DA 4160, Width 26.5 mm, to 300 kg, Full Extension

Material:

Slide elements: Aluminium, corrosion resistant.
Ball retainers and Balls: Stainless Steel.


Heavy Duty Telescopic ball bearing slides for applications in the industrial and electronics sector.

- Very high load capacity up to 300 kg.
- Good corrosion resistance.
- Only for vertical mounting.
- Service life 10,000 cycles.
- Temperature range: -20°C to +110°C.



Accuride

Ordering details: e.g.: Prod. No. 649 055 30, Slides DA 4160



Product No. per Pair	Slide Length mm	Travel +/-3,2 mm	A mm	B mm	C mm	D mm	Load Rating per Pair kg	Weight per Pair kg
649 055 30	300	300	285	-	100	-	240	2,50
649 055 35	350	350	335	-	150	-	255	2,93
649 055 40	400	400	385	-	200	-	270	3,37
649 055 45	450	450	435	-	250	-	285	3,80
649 055 50	500	500	485	-	300	-	300	4,24
649 055 55	550	550	-	267,5	-	150	300	4,68
649 055 60	600	600	-	292,5	-	175	300	5,12
649 055 65	650	650	-	317,5	-	200	295	5,56
649 055 70	700	700	-	342,5	-	225	290	6,00
649 055 80	800	800	-	392,5	-	275	270	6,87
649 055 90	900	900	-	442,5	-	325	250	7,75
649 056 00	1000	1000	-	492,5	-	375	230	8,62

Note

Recommended mounts: M6/M8 screw.
Use all mounting positions to achieve the max. load rating.

Attention: Vertical mounting only.

The load rating is based on slides mounted 600mm apart. These slides are also suitable for wider applications, if the drawer is stiff enough.

End stops have been tested to 10 cycles with the nominated loads at 0.8 m/s. We recommend that additional external stopping arrangements are used.

We recommend that quality grease, rated for extreme pressure, is re-applied at 2000 cycle intervals.