

Torque wrench

Service MANOSKOP® 730 N, with calibration certificate



Execution:

- With mount for replaceable plug-in tools
- Double stop signal
- Double scale
- Ergonomic 2-component handle

Advantage:

- Quick and precise adjustment



Art. no.	52282 004
Brand	STAH LWILLE
Manufacturer Part Number	50181102
Min. torque	4 Nm
Max. torque	20 Nm
Min./max. torque	4-20 Nm
Scale value torque	0.25 Nm
Insert shank square	9 x 12 mm
Length	275 mm
Error limit (%)	4 %
With scale	Yes
Calibration certificate	Yes
Gross Weight	1.002 kg
Product Group	531

EAN

4018754295234