

## Deburring machine for contours – Speedy contour



### Application:

The stationary edge and contour milling machines are perfect for machining square and round workpieces with flush internal and external contours. They are compact and convenient table-top devices, which are ideal for use with CNC machines.

### Execution:

- Chamfer angle can be changed using contour milling cutters with different tip angles
- Suitable for continuous operation
- Suitable for machining small to medium-sized workpieces
- Speed control (only for Speedy Kontur 270-KSL and Speedy Kontur 320-KSL)
- Can be used for steels, hardened steels, aluminium, brass, copper, plastics, from soft plastics to acrylic glass, wood and much more
- Guide ball bearing min. dia. 3 mm

### Advantage:

- For precise deburring and chamfering of inner and outer edges on flat workpieces
- Ideal for machining aluminium and plastic
- Fast set-up with maximum flexibility
- Simple operation, fast tool change



<b>Art. no.</b>	<b>79304 350</b>
<b>Brand</b>	ASSFALG
<b>Manufacturer Part Number</b>	938
<b>Type</b>	Speedy Kontur 320-KSL
<b>Max. chamfer width</b>	2 mm
<b>Min./max. rotation speed</b>	12000-28000 rpm
<b>Motor output</b>	0.14 kW
<b>Nominal voltage</b>	230 V
<b>Length x width x height</b>	320 x 200 x 140 mm
<b>Weight</b>	13 kg
<b>Gross Weight</b>	12.500 kg
<b>Product Group</b>	788