



Part no.: 50136383
TKS 40x60.Chem
Reflector

Figure can vary

Contents

- Technical data

Part no.: 50136383 – TKS 40x60.Chem – Reflector

Technical data

Basic data

Area of application	Food
---------------------	------

Mechanical data

Design	Rectangular
Mounting dimension, width	41 mm
Reflection surface width	37 mm
Mounting dimension, height	60 mm
Reflection surface height	56 mm
Mounting dimension, thickness	8 mm
Triple reflector size	4 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PET
Structure, active surface	Triple
Net weight	16 g
Type of fastening	Adhesive Through-hole mounting
Compatibility of materials	Alcohol ECOLAB H2O2

Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 67
----------------------	-------

Classification

Customs tariff number	90029000
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467