

Surface Mount 8 Wire Jack

**RoHS
Compliant**



Specifications

Material

Housing : PP, UL94V-0
 Contact : Phosphor Bronze, 3μ" gold plated
 RJ31 Surface Jack, 8P8C with Shorting Bar


Electrical

Rated Current/Voltage : 2A, 150V AC
 Dielectric Strength : 1,000V AC, 60Hz, 1min
 Insulation Resistance : 500MΩ
 Transmission : Meets FCC rules part 68, Subpart F.

Mechanical

Durability : 500 mating cycles.

Diagram



Part Number Table

Description	Part Number
Surface Mount 8 Wire Jack	36-105

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. MCM is the registered trademark of Premier Farnell Limited 2019.