

## Standard dial gauges

### Application:

For measuring lengths and length differences, e.g. concentricity, flatness, positional measurements.

### Execution:

- Measuring pin and clamping shaft made from durable stainless steel

### Delivery:

In a case



|   |                  |
|---|------------------|
| <b>Art. no.</b>                                     | <b>33031 010</b> |
| <b>Brand</b>  | HK               |
| <b>Manufacturer Part Number</b>                     | 33031010         |
| <b>Length measuring range</b>                       | 10 mm            |
| <b>Scale value</b>                                  | 0.1 mm           |
| <b>Measurement travel of one pointer revolution</b> | 10 mm            |
| <b>Outer diameter</b>                               | 58 mm            |
| <b>Shock protection</b>                             | No               |
| <b>Material of outer ring</b>                       | Plastic          |
| <b>Measurement force</b>                            | 1 N              |
| <b>Calibration Group</b>                            | CE               |
| <b>Gross Weight</b>                                 | 0.168 kg         |
| <b>Product Group</b>                                | 331              |

### EAN

4039247207077