

electronic dial gauge

1075 R



Application:

For static measurements of lengths and length differences

Execution:

- zero setting at any position
- large LCD display (12 mm)
- reference system
- mm/inch changeover

Advantage:

- LOCK function (key lock)
- Switched on by the ON button or automatically switched on by moving the button
- particularly energy-saving electronics (battery lifetime up to 3 years)



Art. no.	33167 510
Brand	MAHR
Manufacturer Part Number	4336010
Length measuring range	12.5 mm
Digit increment	0.01 mm
Min./max. measurement force	0.5-1 N
Data transmission type	multiCOM
IP protection class	IP 52
Absolute function	Yes
Automatic switch-off	Yes
Preset function	Yes
Number of rechargeable batteries/batteries	1 PCS
Rechargeable battery/battery capacity	200 mAh
Battery voltage	3 V
Weight of rechargeable battery/battery	0.003 kg
Battery designation	3V CR2032 Lithium
Reversible counting direction	Yes
Calibration Group Description	Dial gauge
Calibration Group	CE
Gross Weight	0.213 kg
Product Group	305

EAN

4059 1920 14308