

EUROPEAN GEM-VCEA FOOTSWITCH



European Gem-VCEA Footswitch

Environmental Ratings:

IP20

Key Benefits

All LINEMASTER foot switches can be CE marked.

SPECIFICATIONS

(Special variations are available to the O.E.M. on special order on the models listed below)



CATALOG NUMBER	SERIES	CIRCUIT	ELECTRICAL RATINGS	CORDSETS
 GEM-VCEA	Gem-V	All Models Momentary Contact & Wired SPST-N.O. & Grounded	10 A 125-250 VAC 1/2 H.P. 125-250 VAC	Complete with 2 meter 18/3 cord with brown, blue green/yellow leads.

