

**angular milling cutter, 90°, with thread**  
for indexable milling inserts LN.X 1006..

**ATORN®**

**Application**

4 flutes per indexable milling insert and special chip breaker geometry for profitability and high cutting rates when milling faces, milling corners, trimming and milling grooves.

**Version**

- wear-proof, nickel-plated design
- with internal cooling

**Advantage**

- 4 cutting edges on double-sided indexable insert
- special chip breaker geometry enables low power consumption
- large panel thickness



<b>Art. No.</b>	<b>16016 314</b>
<b>Cutting edge diameter</b>	25 mm
<b>Clearance length</b>	35 mm
<b>Thread dimension</b>	M12
<b>max. ap</b>	10 mm
<b>Number of cutting edges</b>	3 PCS

**EAN-Code**

4050293539868