

Conical washers DIN 6319 type G



Application:

For transferring clamping forces in cases where clamping elements need to adapt to uneven clamping surfaces.

Execution:

- Stamped, pressed and tempered

Advantage:

- Thanks to the large diameter, these are particularly ideal for clamping via the slot in the case of clamps.



Art. no.	26208 712
Brand	AMF
Manufacturer Part Number	81984
Suitable cheese-head screw DIN 912	M8
Internal diameter	9.6 mm
Outer diameter	24 mm
Height	5 mm
DIN	6319
Gross Weight	0.014 kg
Product Group	260

EAN

4020772081980