

ITEM	MOLEX P/N	DESCRIPTION	QTY	UOM
A	39014031	3CKT RECEPTACLE HOUSING 555703R2210	1	PC
B	39000077	MiniFit Term Crp Fem Chn Bs Tin 16awg	3	PC
C	--	RESIN TPE NAT SANTOPRENE	A/R	KG
D	--	MOLD PART INNER CAP	2	PC
E	--	MASTER BATCH BLACK COLOR	A/R	KG
F	--	RESIN PP RTP 151 A NAT UL94V-0 HF	A/R	KG

FROM	TO	CABLE DESCRIPTION	COLOR
A1	--	3CX16AWG UNSHD BK UL2464	BLACK
A2	--		RED
A3	--		WHITE




TABLE		
PART NUMBER	TITLE	L1
2171590305	3 CKT OVERMOLD MINIFIT JR PIGTAIL 500MM	500±10
2171590310	3 CKT OVERMOLD MINIFIT JR PIGTAIL 1M	1000±20
2171590320	3 CKT OVERMOLD MINIFIT JR PIGTAIL 2M	2000±25
2171590330	3 CKT OVERMOLD MINIFIT JR PIGTAIL 3M	3000±30

NOTES:

- MOLDING MATERIAL:
 - INNERCAP: PA66 NYLON RESIN.
 - OVERMOLD: SANTOPRENE TPE RESIN & MASTER BATCH BLACK
 - INNERMOLD: PP NAT UL94V-0
- ELECTRICAL PERFORMANCE:
 - VOLTAGE RATING: 300V AC.
 - THIS PRODUCT MUST PASS 100% CONTINUITY TEST PER MOLEX ES-36586-004.
 - DIELECTRONIC STRENGTH: 500V DC/0.01 SEC.
 - INSULATION RESISTANCE: 20M OHMS
- CONNECTOR VIEWS ARE SHOWN FROM MATING SIDE.
- MECHANICAL PERFORMANCE:
 - CABLE HARNESS SHOULD WITHSTAND AN AXIAL FORCE OF 5KGF FOR ONE MINUTE BETWEEN OVERMOLD AND CONNECTOR WITHOUT PHYSICAL DAMAGE.
 - OVERMOLD SIDE CAN PASS THE BENDING TEST IN 100 CYCLES AT EACH OF 2 PLANES, PER EIA364-41 CONDITION I.

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	CURRENT REV DESC:		molex																																																				
	<table border="1"> <tr> <th>DIMENSION UNITS</th> <th>SCALE</th> </tr> <tr> <td>mm</td> <td>NTS</td> </tr> </table>	DIMENSION UNITS	SCALE		mm	NTS	<table border="1"> <tr> <th colspan="4">GENERAL TOLERANCES (UNLESS SPECIFIED)</th> </tr> <tr> <td>ANGULAR TOL</td> <td>±</td> <td colspan="2">°</td> </tr> <tr> <td>4 PLACES</td> <td>±</td> <td colspan="2"></td> </tr> <tr> <td>3 PLACES</td> <td>±</td> <td colspan="2"></td> </tr> <tr> <td>2 PLACES</td> <td>±</td> <td colspan="2"></td> </tr> <tr> <td>1 PLACE</td> <td>±</td> <td colspan="2"></td> </tr> <tr> <td>0 PLACES</td> <td>±</td> <td colspan="2"></td> </tr> </table>		GENERAL TOLERANCES (UNLESS SPECIFIED)				ANGULAR TOL	±	°		4 PLACES	±			3 PLACES	±			2 PLACES	±			1 PLACE	±			0 PLACES	±			<table border="1"> <tr> <td>EC NO: 670688</td> <td>2021/07/16</td> </tr> <tr> <td>DRWN: SBS04</td> <td>2021/07/19</td> </tr> <tr> <td>CHK'D: RDESAI01</td> <td>2021/07/19</td> </tr> <tr> <td>APPR: RDESAI01</td> <td>2021/07/19</td> </tr> </table>	EC NO: 670688	2021/07/16	DRWN: SBS04	2021/07/19	CHK'D: RDESAI01	2021/07/19	APPR: RDESAI01	2021/07/19	<table border="1"> <tr> <th colspan="4">PRODUCT CUSTOMER DRAWING</th> </tr> <tr> <td>DOCUMENT NUMBER</td> <td>DOC TYPE</td> <td>DOC PART</td> <td>REVISION</td> </tr> <tr> <td>2171590305</td> <td>PSD</td> <td>000</td> <td>B1</td> </tr> </table>	PRODUCT CUSTOMER DRAWING				DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION	2171590305	PSD
DIMENSION UNITS	SCALE																																																							
mm	NTS																																																							
GENERAL TOLERANCES (UNLESS SPECIFIED)																																																								
ANGULAR TOL	±	°																																																						
4 PLACES	±																																																							
3 PLACES	±																																																							
2 PLACES	±																																																							
1 PLACE	±																																																							
0 PLACES	±																																																							
EC NO: 670688	2021/07/16																																																							
DRWN: SBS04	2021/07/19																																																							
CHK'D: RDESAI01	2021/07/19																																																							
APPR: RDESAI01	2021/07/19																																																							
PRODUCT CUSTOMER DRAWING																																																								
DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION																																																					
2171590305	PSD	000	B1																																																					
DIVISIONAL SYMBOLS	<table border="1"> <tr> <th colspan="4">INITIAL REVISION:</th> </tr> <tr> <td>DRWN: SBS04</td> <td>2021/05/01</td> <td colspan="2"></td> </tr> <tr> <td>APPR: MNARAYAN01</td> <td>2021/05/10</td> <td colspan="2"></td> </tr> </table>	INITIAL REVISION:				DRWN: SBS04	2021/05/01			APPR: MNARAYAN01	2021/05/10			<table border="1"> <tr> <th colspan="4">MATERIAL NUMBER</th> </tr> <tr> <td>217159</td> <td>CUSTOMER</td> <td colspan="2">SHEET NUMBER</td> </tr> <tr> <td>SEE TABLE</td> <td>GENERAL MARKET</td> <td colspan="2">1 OF 1</td> </tr> </table>	MATERIAL NUMBER				217159	CUSTOMER	SHEET NUMBER		SEE TABLE	GENERAL MARKET	1 OF 1																															
INITIAL REVISION:																																																								
DRWN: SBS04	2021/05/01																																																							
APPR: MNARAYAN01	2021/05/10																																																							
MATERIAL NUMBER																																																								
217159	CUSTOMER	SHEET NUMBER																																																						
SEE TABLE	GENERAL MARKET	1 OF 1																																																						