

IT50R9C2

Article Number: 111-85019

Identification Tie, 8" Long, 50lb Tensile Strength, PA66, Natural, 100/pkg



Download spec sheet

Base Data

Local Order Number IT50R9C2

Type IT50R

Color Natural (NA)

- Features and Benefits**
- Identification plate feature allows bundles to be easily marked and identified.
 - Wire and cable harnesses can be secured and identified using just one product, which saves time.
 - Plates can be marked manually with a permanent marker or with a pre-printed adhesive label.

Product Description HellermannTyton Identification cable ties feature an identification plate allowing wire and cable bundles to be easily marked and identified. These ties enable wire and cables to be secured and identified using just one product, saving installation time. The plates can be marked using a permanent marker or with a HellermannTyton adhesive label.

Mounting method Identification ETIM Others

Short Description Identification Tie, 8" Long, 50lb Tensile Strength, PA66, Natural, 100/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 50.0 lbs

Minimum Tensile Strength (Metric) 225.0 N

Length L (Imperial) 8.0 "

Length L (Metric) 203.0 mm

Fixation Method None

Identification Plate Position attached to bundle

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 1.1 "

Width W (Metric) 28.0 mm

Width W2 (Imperial) 0.18 "

Width W2 (Metric) 4.6 mm

Height H (Imperial) 0.51 "

Height H (Metric) 12.9 mm

Bundle Diameter Min. (Imperial) 0.37 "

Bundle Diameter Min. (Metric) 9.5 mm

Bundle Diameter Max. (Imperial) 1.8 "

Bundle Diameter Max. (Metric) 44.5 mm

Outside Diameter Min. (Imperial) 0.37 "

Outside Diameter Min. (Metric) 9.50 mm

Outside Diameter Max. (Imperial) 1.73 "

Outside Diameter Max. (Metric)	44.50 mm
Thickness T (Imperial)	0.05 "
Thickness T (Metric)	1.2
Width of Printable Area (imperial)	1.1 "
Width of printable area (metric)	28.00 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	100 Pieces
Carton Quantity	5000 Pieces
Weight (Metric)	1.5 kg

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
US MILSPEC	MS3368-1-9A
Flammability	UL94 V2
Halogenfree	Yes
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes
Certification/Specification	Cage Code 53421 SAE AS33681 UL-ZODZ2.E64139 MS3368
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes