

# Standard valves to ISO 5599-1



Festo core product range  
Covers 80% of your automation tasks

Worldwide:  
Superb:  
Easy:


Always in stock  
Festo quality at an attractive price  
Reduces procurement and storing complexity



Generally ready for shipping ex works in 24 hours  
Held in stock in 13 service centres worldwide  
More than 2200 product




Generally ready for shipping ex works in 5 days  
Assembled for you in 4 service centres worldwide  
Up to  $6 \times 10^{12}$  variants per product series



# Standard valves to ISO 5599-1

Key features

FESTO



## Innovative

- High-performance valves in a sturdy metal housing
- Individual electrical connection via square plug sockets or centrally for each valve via round plug sockets
- Valve replacement under pressure possible using vertical pressure shut-off plate
- Reverse operation
- Vacuum operation

## Versatile

- Modular system offering a range of configuration options
- Easy to convert or extend at a later date
- Integration of innovative function modules possible
  - Pressure regulator plate
  - Flow control plate
  - Vertical pressure shut-off plate
  - Vertical supply plate
- Vertical supply plates permit a flexible air supply and variable pressure zones
- Wide range of valve functions
- Extensive operating voltage range from 12 V DC to 230 V AC

## Reliable

- Sturdy and durable metal components
  - Valves
  - Horizontally linked sub-bases
  - Vertically stacked sub-bases
- Fast troubleshooting thanks to LED in the plug socket or illuminating seal
- LED integrated in the valve with the round plug variant
- Convenient servicing thanks to valves that can be replaced quickly and easily
- Manual override
- Durable thanks to tried-and-tested piston spool valves

## Easy to install


- Plug-in pressure gauges on the pressure regulator plate

# Standard valves to ISO 5599-1

Key features

FESTO

## Individual manifold assembly



## Equipment options

### 2x 2/2-way valve, single solenoid

- Normally closed
- Normally closed, vacuum operation possible at port 3 and 5

### 2x 3/2-way valve, single solenoid

- Normally open
- Normally closed
- 1x normally open, 1x normally closed
- Reverse operation possible (→ page 11)

### 5/2-way valve

- Single solenoid, mechanical or pneumatic spring return
- Double solenoid
- Double solenoid, with dominant signal at port 14

### 5/3-way valve

- Mid-position pressurised
- Mid-position closed
- Mid-position exhausted

## Special characteristics

### Operation with external pilot air supply

- For vacuum applications
- For working pressures lower than 3 bar
- For significant pressure fluctuations in the power section. Power section and pneumatic control section are isolated
- For heavily lubricated air in the power section
- For manifolds where the pressure zones are created via ducts 3 and 5 (not possible with 2x 3/2-way valves)
- For manifolds or pressure zones that are equipped with reversible 2x 3/2-way valves (valves on request)

### Operation with internal pilot air supply

- For small pressure fluctuations in the power section
- For using pressure regulator plates in a vertical stacking construction, also in reverse operation
- As a low-cost solution

### Reverse operation with compressed air supply via ducts 3 and 5

- Pressure zone separation via ducts 3 and 5
  - Example: Duct 3 vacuum, duct 5 ejector pulse
  - Example: Duct 3 high pressure for advancing the piston rod of a double-acting cylinder. Duct 5 low pressure for retracting the piston rod with low energy consumption
- 2x 3/2-way valves used as 5/4-way valve with controllable lap and pressure zone separation in the reversible variant

### Reverse operation with a pressure regulator plate, compressed air supply via duct 1

- Reversible pressure regulator combined with a reversible 2x 3/2-way valve regulates outputs 2 and 4
  - AB regulator for outputs 2 and 4
  - A regulator for output 4
  - B regulator for output 2
- Reversible pressure regulators are in the control position immediately after the power supply is switched on
  - Adjustment possible at all times
  - Dynamic response characteristics
  - Reduced regulator load because the supply pressure is maintained when the valve is switched
  - Not exhausted via the regulator

# Standard valves to ISO 5599-1

Key features




## Manifold assembly with vertical stacking

Solenoid valve with individual pilot valves and port pattern to ISO 15218, can be connected using square plug sockets

Solenoid valve with central round plug

Flow control plate for adjusting the speed of the drive



Pressure regulator for adjusting the force of the actuated drive

Vertical pressure shut-off plate for replacing solenoid valves during operation

Vertical supply plate as separate compressed air supply for a valve

## Vertical stacking function

### Pressure regulator

- Single variant to regulate the pressure in duct 4 or 2 or at 1
- Dual variant to regulate the pressure in ducts 4 and 2 individually
- As reversible version with internally replaced ducts 1 and 3/5
- With pressure gauge connection

### Flow control plate

- Designed with two flow control valves, at which the exhaust air flow rate at ducts 5 or 3 can be adjusted.
- The movement of the drive is initiated and the required speed is set via the flow control plate using the manual override on the valve.


### Vertical pressure shut-off plate

- Equipped with a switch via which the compressed air supply can be shut off. As a result, components mounted on the vertical pressure shut-off plate (e.g. a valve) can be replaced without switching off the overall air supply.
- If the control chain has a redundant connection, the cycle can continue even in the case of a cyclical control system.

### Vertical supply plate


- As additional air supply for a valve
- Separates the valve from duct 1 of the manifold sub-base
- To supply an additional pressure zone

## Individual connection with square plug



The directional control valve has a pilot control to ISO 15218. The solenoid coil plugged onto the armature can be chosen in different designs and operating voltages.

## Individual connection with central round plug




The electrical connection is established via a standardised M12 plug, 24 V DC (EN 61076-2-101).

# Standard valves to ISO 5599-1

Key features


## Pressure regulator with one regulated duct



### Versions

- For pressure regulation at the supply input (P), duct 1. Set pressure is identical for ducts 2 and 4
- For pressure regulation at the working port (A), duct 4
  - The pressure regulator for reverse operation is supplied via duct 1 of the manifold sub-base and supplies duct 5 on the valve
  - The valve is exhausted via duct 1 to ducts 3 and 5 of the manifold sub-base
- For pressure regulation at the working port (B), duct 2
  - In reverse operation duct 3 is supplied here


## Pressure regulator with 2 regulated ducts



### Versions

- For pressure regulation at the working ports (A and B), ducts 4 and 2
  - The pressure regulators for reverse operation are supplied via duct 1 of the manifold sub-base and supply ducts 5 and 3 on the valve
  - The directional control valve is exhausted via duct 1 to ducts 3 and 5 of the manifold sub-base


## Vertical supply plate



### Versions

- As intermediate supply
  - For one valve
  - To supply an additional pressure zone
- Can be equipped with a valve


## Flow control plate



### Versions

- Exhaust air flow control valves in ducts 3 and 5
  - The flow control plates act as supply air flow control valves for pressure zones that are created via ducts 3 and 5

## Vertical pressure shut-off plate



### Versions

- A switch activated with a slotted screwdriver shuts off duct 1.
  - The flow control plates, pressure regulators or valves positioned above it can be replaced
  - Other components of the control chain such as drives, for example, can be replaced following venting via the valve

## Pressure gauge



### Version

- Plugs into the pressure regulators

# Standard valves to ISO 5599-1

Key features




## Port pattern on sub-base to ISO 5599-1

Width 42 mm (ISO 1)

Width 52 mm (ISO 2)

Width 65 mm (ISO 3)


Width 76 mm (ISO 4)



## Sub-base port designations

Duct	Function	Description
14	Control section	Pilot air supply for pilot valves 12 and 14
5	Power section	Exhaust port
4	Power section	Working port
1	Power section	Working air supply port
2	Power section	Working port
3	Power section	Exhaust port
12	Control section	Exhaust port for pilot air supply

## Conversion of pilot air exhaust



- 1 Ducted pilot air exhaust
- 2 Turning the seal by 180°
- 3 Unducted pilot air exhaust (delivery status)

VSVA manifold assemblies are supplied with unducted pilot air exhaust. By turning the seal between the valve and manifold block, exhaust air (pilot air) can be diverted into pilot duct 12 and can thus be contained and silenced (see illustration).

# Standard valves to ISO 5599-1






Key features

Use of 2x 3/2-way valve as 5/4-way valve																			
Code	Symbol	Table of values	Equivalent circuit symbol	Function															
K		<table border="1"> <thead> <tr> <th>Y1</th> <th>Y2</th> <th>A</th> </tr> </thead> <tbody> <tr> <td>0</td> <td>0</td> <td></td> </tr> <tr> <td>0</td> <td>1</td> <td></td> </tr> <tr> <td>1</td> <td>0</td> <td></td> </tr> <tr> <td>1</td> <td>1</td> <td></td> </tr> </tbody> </table>	Y1	Y2	A	0	0		0	1		1	0		1	1			<ul style="list-style-type: none"> <li>• Normally exhausted</li> <li>• The double-acting drive connected to ducts 2 and 4 is unpressurised when the valve is in the normal position and can be moved by an external force</li> <li>• If there is a signal present at Y1(14) and Y2(12), there is pressure at ducts 2 and 4</li> </ul>
Y1	Y2	A																	
0	0																		
0	1																		
1	0																		
1	1																		
		<table border="1"> <thead> <tr> <th>Y1</th> <th>Y2</th> <th>A</th> </tr> </thead> <tbody> <tr> <td>0</td> <td>0</td> <td></td> </tr> <tr> <td>0</td> <td>1</td> <td></td> </tr> <tr> <td>1</td> <td>0</td> <td></td> </tr> <tr> <td>1</td> <td>1</td> <td></td> </tr> </tbody> </table>	Y1	Y2	A	0	0		0	1		1	0		1	1			<ul style="list-style-type: none"> <li>• Normally closed (by combining valve code K and two piloted non-return valves)</li> <li>• The piloted non-return valves connected to ducts 2 and 4 are unpressurised when the valve is in the normal position and the pressures in the drive close the non-return valves leak-tight</li> <li>• The drive remains stationary when the forces are balanced</li> <li>• Leakages can only occur via the drive seals</li> <li>• If there is a signal present at Y1(14) and Y2(12), the same pressure is present at ducts 2 and 4</li> </ul>
Y1	Y2	A																	
0	0																		
0	1																		
1	0																		
1	1																		
N		<table border="1"> <thead> <tr> <th>Y1</th> <th>Y2</th> <th>A</th> </tr> </thead> <tbody> <tr> <td>0</td> <td>0</td> <td></td> </tr> <tr> <td>0</td> <td>1</td> <td></td> </tr> <tr> <td>1</td> <td>0</td> <td></td> </tr> <tr> <td>1</td> <td>1</td> <td></td> </tr> </tbody> </table>	Y1	Y2	A	0	0		0	1		1	0		1	1			<ul style="list-style-type: none"> <li>• Normally open</li> <li>• The double-acting drive connected to ducts 2 and 4 is supplied with the same pressure at both ends when the valve is in the normal position and remains stationary when the forces are balanced</li> <li>• If there is a signal present at Y1(10) and Y2(10), ducts 2 and 4 are exhausted, the drive is unpressurised and can be moved by an external force</li> </ul>
Y1	Y2	A																	
0	0																		
0	1																		
1	0																		
1	1																		
H		<table border="1"> <thead> <tr> <th>Y1</th> <th>Y2</th> <th>A</th> </tr> </thead> <tbody> <tr> <td>0</td> <td>0</td> <td></td> </tr> <tr> <td>0</td> <td>1</td> <td></td> </tr> <tr> <td>1</td> <td>0</td> <td></td> </tr> <tr> <td>1</td> <td>1</td> <td></td> </tr> </tbody> </table>	Y1	Y2	A	0	0		0	1		1	0		1	1			<ul style="list-style-type: none"> <li>• Normally open to duct 2</li> <li>• The double-acting drive connected to ducts 2 and 4 is supplied with pressure via duct 2 when the valve is in the normal position. Duct 4 is exhausted. When the system is in its initial position, the drive is thus in a clearly defined position, as would also be the case with a 5/2-way single solenoid valve.</li> <li>• If there is a signal present at Y1(14) and Y2(10), duct 2 is exhausted and there is pressure at duct 4. The drive leaves the initial position</li> <li>• A closed circuit can be created with this 2x 3/2-way valve by combining it with piloted non-return valves. However, this is then selected by an active signal at Y2(10).</li> </ul>
Y1	Y2	A																	
0	0																		
0	1																		
1	0																		
1	1																		

# Standard valves to ISO 5599-1

Product range overview








Function	Type	Valve function	Flow rate	Operating voltage	→ Page/ Internet	
			Valve [l/min]			
Width 42 mm  Working port G1/4	<b>Valve with armature for solenoid coil MSN</b>					
		MN1H-5/2	5/2-way single solenoid valve	1200	12 V DC, 24 V DC, 24 V AC, 110 V AC, 230 V AC	20
		JMN1	5/2-way double solenoid valve	1200		
		MN1H-5/3	5/3-way solenoid valve, mid-position valve	1200		
	<b>Valve with armature for solenoid coil MSF</b>					
		MFH-5/2	5/2-way single solenoid valve	1200	12 V DC, 24 V DC, 42 V DC, 24 V AC, 42 V AC, 48 V AC, 110 V AC, 120 V AC, 230 V AC, 240 V AC	32
		JMF	5/2-way double solenoid valve	1200		
		MFH-5/3	5/3-way solenoid valve, mid-position valve	1200		
	<b>Valve with central plug M12, 3-pin</b>					
		VSVA-B-T22	2x 2/2-way single solenoid valve	1300	24 V DC	44
		VSVA-B-T32	2x 3/2-way single solenoid valve	1100		
		VSVA-B-M52	5/2-way single solenoid valve	1300		
		VSVA-B-B52	5/2-way double solenoid valve	1300		
		VSVA-B-D52	5/2-way double solenoid valve	1300		
		VSVA-B-P53	5/3-way solenoid valve, mid-position valve	1300		
	<b>Valve with individual plug M12</b>					
		MDH-5/2	5/2-way single solenoid valve	1200	24 V DC, 42 V AC, 110 V AC, 230 V AC	60
		JMD	5/2-way double solenoid valve	1200		
		MDH-5/3	5/3-way solenoid valve, mid-position valve	1200		
	<b>Pneumatic valve</b>					
		VL-5/2	5/2-way pneumatic valve, monostable	1200	-	81
J		5/2-way pneumatic valve, bistable	1200			
VL-5/3		5/3-way pneumatic valve, mid-position valve	1200			



# Standard valves to ISO 5599-1

Product range overview

Function	Type	Valve function	Flow rate	Operating voltage	→ Page/ Internet	
			Valve [l/min]			
Width 52 mm  Working port G3/8	<b>Valve with armature for solenoid coil MSN</b>					
		MN1H-5/2	5/2-way single solenoid valve	2300	12 V DC, 24 V DC, 24 V AC, 110 V AC, 230 V AC	24
		JMN1	5/2-way double solenoid valve	2300		
		MN1H-5/3	5/3-way solenoid valve, mid-position valve	2300		
	<b>Valve with armature for solenoid coil MSF</b>					
		MFH-5/2	5/2-way single solenoid valve	2300	12 V DC, 24 V DC, 42 V DC, 24 V AC, 42 V AC, 48 V AC, 110 V AC, 120 V AC, 230 V AC, 240 V AC	36
		JMF	5/2-way double solenoid valve	2300		
		MFH-5/3	5/3-way solenoid valve, mid-position valve	2300		
	<b>Valve with central plug M12, 3-pin</b>					
		VSA-B-T22	2x 2/2-way single solenoid valve	2800	24 V DC	51
		VSA-B-T32	2x 3/2-way single solenoid valve	2200		
		VSA-B-M52	5/2-way single solenoid valve	2800		
		VSA-B-B52	5/2-way double solenoid valve	2800		
		VSA-B-D52	5/2-way double solenoid valve	2800		
		VSA-B-P53	5/3-way solenoid valve, mid-position valve	2700		
	<b>Valve with individual plug M12</b>					
		MDH-5/2	5/2-way single solenoid valve	2300	24 V DC, 42 V AC, 110 V AC, 230 V AC	65
		JMD	5/2-way double solenoid valve	2300		
		MDH-5/3	5/3-way solenoid valve, mid-position valve	2300		
	<b>Pneumatic valve</b>					
	VL-5/2	5/2-way pneumatic valve, monostable	2300	-	86	
	J	5/2-way pneumatic valve, bistable	2300			
	VL-5/3	5/3-way pneumatic valve, mid-position valve	2300			

# Standard valves to ISO 5599-1

Product range overview



Function	Type	Valve function	Flow rate	Operating voltage	→ Page/ Internet	
			Valve [l/min]			
Width 65 mm  Working port G1/2	<b>Valve with armature for solenoid coil MSN</b>					
		MN1H-5/2	5/2-way single solenoid valve	4500	12 V DC, 24 V DC, 24 V AC, 110 V AC, 230 V AC	28
		JMN1	5/2-way double solenoid valve	4500		
		MN1H-5/3	5/3-way solenoid valve, mid-position valve	4000		
	<b>Valve with armature for solenoid coil MSF</b>					
		MFH-5/2	5/2-way single solenoid valve	4500	12 V DC, 24 V DC, 42 V DC, 24 V AC, 42 V AC, 48 V AC, 110 V AC, 120 V AC, 230 V AC, 240 V AC	40
		JMF	5/2-way double solenoid valve	4500		
		MFH-5/3	5/3-way solenoid valve, mid-position valve	4000		
	<b>Valve with central plug M12, 4-pin</b>					
		MEBH-5/2	5/2-way single solenoid valve	4500	24 V DC	56
		JMEB	5/2-way double solenoid valve	4500		
		MEBH-5/3	5/3-way solenoid valve, mid-position valve	4000		
	<b>Valve with individual plug M12</b>					
		MDH-5/2	5/2-way single solenoid valve	4500	24 V DC, 42 V AC, 110 V AC, 230 V AC	69
		JMD	5/2-way double solenoid valve	4500		
		MDH-5/3	5/3-way solenoid valve, mid-position valve	4000		
	<b>Pneumatic valve</b>					
		VL-5/2	5/2-way pneumatic valve, monostable	4500	-	91
		J	5/2-way pneumatic valve, bistable	4500		
		VL-5/3	5/3-way pneumatic valve, mid-position valve	4100		
Width 76 mm  Working port G3/4	<b>Valve with individual plug M12</b>					
		MDH-5/2	5/2-way single solenoid valve	6000	24 V DC, 42 V AC, 110 V AC, 230 V AC	73
		JMD	5/2-way double solenoid valve	6000		
		MDH-5/3	5/3-way solenoid valve, mid-position valve	4800		
	<b>Pneumatic valve</b>					
		VL-5/2	5/2-way pneumatic valve, monostable	6000	-	96
		J	5/2-way pneumatic valve, bistable	6000		
VL-5/3		5/3-way pneumatic valve, mid-position valve	4800			

# Standard valves to ISO 5599-1, central plug M12

Type codes for valves with round plug

		VSVA	-	B	-	T32F		-	A	Z	D	-	D1	-	1	R5	L
<b>Valve</b>																	
VSVA	Standard valves to ISO 5599-1																
<b>Valve type</b>																	
B	Sub-base valve																
<b>Valve function</b>																	
M52	5/2-way single solenoid valve																
B52	5/2-way double solenoid valve																
D52	5/2-way double solenoid valve, with dominant signal at 14																
P53U	5/3-way valve, mid-position pressurised																
P53E	5/3-way valve, mid-position exhausted																
P53C	5/3-way valve, mid-position closed																
T32U	2x 3/2-way valve, normally open																
T32C	2x 3/2-way valve, normally closed																
T32H	2x 3/2-way valve, 1x normally open, 1x normally closed																
T32F	2x 3/2-way valve, normally open, reverse operation																
T32N	2x 3/2-way valve, normally closed, reverse operation																
T32W	2x 3/2-way valve, 1x normally closed, 1x normally open, reverse operation																
T22C	2x 2/2-way valve, normally closed																
<b>Additional function</b>																	
	No additional function																
V	2x 2/2-way valve with vacuum operation																
<b>Reset method</b>																	
A	Pneumatic spring																
M	Mechanical spring																
<b>Pilot air supply</b>																	
Z	External																
	Internal																
<b>Manual override</b>																	
D	Non-detenting/detenting																
H	Non-detenting																
<b>Pneumatic port (width)</b>																	
D1	Width 42 mm/ISO size 1																
D2	Width 52 mm/ISO size 2																
<b>Operating voltage</b>																	
1	24 V DC																
<b>Electrical connection</b>																	
R5	Central plug M12x1																
<b>Signal status display</b>																	
L	LED (integrated)																

# Standard valves to ISO 5599-1, solenoid coil MSN1

Type codes for valves with armature for solenoid coil MSN

MN1H – 5/2 – D-1 – – – C

Type	
MN1H	Single solenoid
JMN1H	Double solenoid
JMN1DH	Double solenoid, with dominant signal at 14

Valve function	
5/2	5/2-way valve
5/3G	5/3-way valve, mid-position closed
5/3E	5/3-way valve, mid-position exhausted
5/3B	5/3-way valve, mid-position pressurised

Pneumatic port (width)	
D-1	Width 42 mm/ISO size 1
D-2	Width 52 mm/ISO size 2
D-3	Width 65 mm/ISO size 3


Reset method 5/2-way valve	
	Pneumatic spring
FR	Mechanical spring

Pilot air supply	
	Internal
S	External

Generation	
C	C series

# Standard valves to ISO 5599-1, solenoid coil MSF

Type codes for valves with armature for solenoid coil MSF



Type	
MFH	Single solenoid
JMFH	Double solenoid
JMFDH	Double solenoid, with dominant signal at 14

Valve function	
5/2	5/2-way valve
5/3G	5/3-way valve, mid-position closed
5/3E	5/3-way valve, mid-position exhausted
5/3B	5/3-way valve, mid-position pressurised

Pneumatic port (width)	
D-1	Width 42 mm/ISO size 1
D-2	Width 52 mm/ISO size 2
D-3	Width 65 mm/ISO size 3

Reset method 5/2-way valve	
	Pneumatic spring
FR	Mechanical spring

Pilot air supply	
	Internal
S	External

Generation	
C	C series

CE marking	
	Without
EX	ATEX category → technical data

# Standard valves to ISO 5599-1, central plug M12, 4-pin

Type codes for valves with central plug M12, 4-pin

MEBH – 5/3G – D-1 – – – C

Type	
MEBH	Single solenoid
JMEBH	Double solenoid
JMEBDH	Double solenoid, with dominant signal at 14

Valve function	
5/2	5/2-way valve
5/3G	5/3-way valve, mid-position closed
5/3E	5/3-way valve, mid-position exhausted
5/3B	5/3-way valve, mid-position pressurised

Pneumatic port (width)	
D-3	Width 65 mm/ISO size 3

Electrical connection, operating voltage	
ZSR	Central plug, round design, M12x1, 24 V DC

Reset method 5/2-way valve	
	Pneumatic spring
FR	Mechanical spring

Generation	
C	C series

# Standard valves to ISO 5599-1, solenoid coil MD

Type codes for valves with individual plug M12

MDH – 5/3G – D-1 – – – – C

**Type**

MDH	Single solenoid
JMDH	Double solenoid
JMDDH	Double solenoid, with dominant signal at 14

**Valve function**

5/2	5/2-way valve
5/3G	5/3-way valve, mid-position closed
5/3E	5/3-way valve, mid-position exhausted
5/3B	5/3-way valve, mid-position pressurised

**Pneumatic port (width)**

D-1	Width 42 mm/ISO size 1
D-2	Width 52 mm/ISO size 2
D-3	Width 65 mm/ISO size 3
3/4-D-4	Width 76 mm/ISO size 4

**Electrical connection, operating voltage**

	No pilot control
24 DC	Individual plug, square design, 3-pin socket with port pattern to EN 175301-803, type A, 24 V DC
M12	Individual plug, round design, M12x1, 2-pin to VDMA, 24 V DC
M12D	Individual plug, round design, M12x1, 4-pin to Desina, 24 V DC

**Pilot air supply**

	Internal
S	External

**Reset method 5/2-way valve**

	Pneumatic spring
FR	Mechanical spring

**Generation**

	Width 76 mm/ISO size 4
C	C series

# Standard valves to ISO 5599-1



Peripherals overview



## Valve on individual sub-base

Solenoid valve with solenoid coil MSN1

Solenoid valve with central plug M12, 3-pin



### Individual components

	Type	Description	→ Page/Internet	
1	Solenoid valve	MN1H...	Solenoid valve with solenoid coil, port pattern to ISO 5599-1, corresponding solenoid coils → page 120	20
	Solenoid valve	VSVA...	Solenoid valve with central plug M12, 3-pin, port pattern to ISO 5599-1	44
2	Individual sub-base	NAS...	Pneumatic ports, side	100
		NAU...	Pneumatic ports, underneath	101
3	Silencer	U...	For fitting in exhaust ports	silencer
4	Push-in fitting	QS...	For connecting O.D. tubing	qs
5	Connecting cable	KMC..., NEBV...	Without LED	121
6	Connecting cable	KMC..., NEBV...	With LED	121
7	Plug socket	MSSD...	For self-assembly	121
8	Illuminating seal	M...-LD	For indicating the signal status	121
9	Manual override	AHB...	Tool for detenting manual override	122
10	Connecting cable	NEBU...	-	122
11	Plug socket	SIE...	For self-assembly	122





### Valve variants

MN1H, JMN1H, MFH, JMFH

VSVA

MEBH, JMEBH

MDH, JMDH






# Standard valves to ISO 5599-1

Peripherals overview

FESTO

## Accessories




Individual components			
	Type	Description	→ Page/ Internet
1	U-...	For fitting in exhaust ports	silencer
2	QS-...	For connecting O.D. tubing	qs
3	PAGN-...	With push-in connector	122
4	KMC-..., NEBV-...	Without LED	121
5	KMC-...LED, NEBV-...	With LED	121
6	M...-LD	For indicating the signal status	121
7	MSSD-C-M16	With screw terminal connection	121
8	MSSD-C-S-M16	With insulation displacement connection	121
9	NEBU-...	Angled socket, M12x1, 5-pin	122
10	SIE-...	For self-assembly	122
11	NEBU-...	Straight socket, M12x1, 5-pin	122

# Standard valves to ISO 5599-1

System overview

FESTO

## Manifold assembly



# Standard valves to ISO 5599-1

System overview

FESTO

Individual components				
	Type	Description	→ Page/ Internet	
1	Solenoid valve	MN1H-...	With armature for solenoid coil MSN1	20
		JMN1H-...	With armature for solenoid coil MSN1	20
		JMN1DH-...	With armature for solenoid coil MSN1	20
		MFH-...	With armature for solenoid coil MSF	32
		JMFH-...	With armature for solenoid coil MSF	32
		JMFDH-...	With armature for solenoid coil MSF	32
		VVA-...	With central plug M12, 3-pin	44
		MEBH-...	With central plug M12, 4-pin	56
		JMEBH-...	With central plug M12, 4-pin	56
		JMEBDH-...	With central plug M12, 4-pin	56
		MDH-...	With solenoid coil MD with round plug M12x1	60
		JMDH-...	With solenoid coil MD with round plug M12x1	60
		JMDDH-...	With solenoid coil MD with round plug M12x1	60
	Pneumatic valve	VL-...	Port pattern to ISO 5599-1	81
J-...		Port pattern to ISO 5599-1	81	
JD-...		Port pattern to ISO 5599-1	81	
2	Blanking plate	NDV-...	For sealing unused manifold sub-bases	104
3	Flow control plate	VABF-S1-...-F1B1-C	Controls the flow of exhaust air in ducts 3 and 5	107
		GRO-ZP-...	Controls the flow of exhaust air in ducts 3 and 5	107
4	Vertical supply plate	VABF-S1-...-P1A3-G38	Alternative compressed air supply for port 1 of the assembled valve	110
5	Vertical pressure shut-off plate	VABF-S1-...-L1D1-C	For blocking duct 1 and duct 14 upstream of a valve	112
6	Regulator plate	VABF-S1-...-R...	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	114
		LR-ZP-...	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	114
7	End plate kit	NEV-...	With ports for air supply 1 and exhausts 3 and 5	103
8	Manifold sub-base	NAV-...	With ports 2 and 4 underneath	102
9	Isolating disc	NSC-...	For sealing ducts 1, 3, 5 between end plate and manifold sub-base, e.g. to create pressure zones	104

# Standard valves to ISO 5599-1, solenoid coil MSN1

FESTO

Technical data – Width 42 mm

Flow rate  
1200 l/min



General technical data	
Design	Piston spool valve
Sealing principle	Soft
Actuation type	Electric
Type of control	Piloted
Direction of flow	With external pilot air supply Reversible With internal pilot air supply Non-reversible
Exhaust function	With flow control
Manual override	Non-detenting, detenting via accessory
Type of mounting	On sub-base, via through-hole
Mounting position	Any
Nominal size [mm]	8
Lap	Overlap
Width [mm]	42
Grid dimension [mm]	43
Pneumatic ports	Sub-base size 1 to ISO 5599-1
Noise level [dB (A)]	85
Conforms to standard	ISO 5599-1
Certification	With internal pilot air supply c UL us Recognised (OL)
Maritime classification <sup>1)</sup>	See certificate

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Flow rates			
Valve function	5/2-way single solenoid valve	5/2-way double solenoid valve	5/3-way valve
Standard nominal flow rate [l/min]	1200		

Switching times [ms]					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way single solenoid valve	MN1H-5/2-D-1-C	23	32	–	–
	MN1H-5/2-D-1-S-C	23	32	–	–
	MN1H-5/2-D-1-FR-C	17	39	–	–
	MN1H-5/2-D-1-FR-S-C	17	39	–	–
5/2-way double solenoid valve	JMN1H-5/2-D-1-C	–	–	18	–
	JMN1H-5/2-D-1-S-C	–	–	18	–
	JMN1DH-5/2-D-1-C	–	–	18	15
	JMN1DH-5/2-D-1-S-C	–	–	18	15
5/3-way valve	MN1H-5/3G-D-1-C	20	44	–	–
	MN1H-5/3G-D-1-S-C	20	44	–	–
	MN1H-5/3E-D-1-C	20	46	–	–
	MN1H-5/3E-D-1-S-C	20	46	–	–
	MN1H-5/3B-D-1-C	20	46	–	–
	MN1H-5/3B-D-1-S-C	20	46	–	–

# Standard valves to ISO 5599-1, solenoid coil MSN1

Technical data – Width 42 mm


Operating and environmental conditions			
Reset method		Pneumatic spring	
		Mechanical spring	
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	Internal pilot air supply	[bar]	2 ... 10
	External pilot air supply	[bar]	-0.9 ... +16
Pilot pressure		[bar]	2 ... 10
Ambient temperature		[°C]	-5 ... +50
Temperature of medium		[°C]	-5 ... +50

Safety characteristics		
Max. positive test pulse with 0 signal	[µs]	3700
Max. negative test pulse with 1 signal	[µs]	4600
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27	
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6	

Electrical data	
Electrical connection	Via N1 coil, to be ordered separately
Degree of protection to EN 60529	IP65

## Materials

Sectional view



1	Housing	Die-cast aluminium
-	Seals	HNBR, NBR
-	Note on materials	RoHS-compliant

# Standard valves to ISO 5599-1, solenoid coil MSN1


Technical data – Width 42 mm



## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)


### 5/2-way single solenoid valves



- 2 Manual override
- 3 Captive mounting screws
- 4 Slot for inscription label

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
MN1H-5/2- ...	42	28	6	30	M5	M5	106	74	38	9	46.5	15.3	117.5	87.6	43.8	36	18	89
MN1H-5/2- ... -FR- ...													128	98				

### 5/2-way double solenoid valves, 5/3-way valves



- 2 Manual override
- 3 Captive mounting screws
- 4 Slot for inscription label

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
JMN1H-5/2- ...	42	28	6	30	M5	M5	106	74	38	9	46.5	15.3	147.3	87.6	43.8	36	18	89
JMN1DH-5/2- ...														87.6				
MN1H-5/3- ...														108.4				

# Standard valves to ISO 5599-1, solenoid coil MSN1

Ordering data – Width 42 mm

Ordering data – Valves with armature for solenoid coil MSN1 <sup>1)</sup>					
Circuit symbol	Description	Pilot air supply	Weight [g]	Part No.	Type
<b>5/2-way single solenoid valve</b>					
	Pneumatic spring reset method	Internal	450	<b>159688</b>	<b>MN1H-5/2-D-1-C</b>
	Pneumatic spring reset method	External	450	<b>159686</b>	<b>MN1H-5/2-D-1-S-C</b>
	Mechanical spring reset method	Internal	450	<b>159687</b>	<b>MN1H-5/2-D-1-FR-C</b>
	Mechanical spring reset method	External	450	<b>159716</b>	<b>MN1H-5/2-D-1-FR-S-C</b>
<b>5/2-way double solenoid valve</b>					
	–	Internal	610	<b>159690</b>	<b>JMN1H-5/2-D-1-C</b>
	–	External	610	<b>159689</b>	<b>JMN1H-5/2-D-1-S-C</b>
	With dominant signal at 14	Internal	610	<b>159691</b>	<b>JMN1DH-5/2-D-1-C</b>
	With dominant signal at 14	External	610	<b>159717</b>	<b>JMN1DH-5/2-D-1-S-C</b>
<b>5/3-way valve</b>					
	Normally closed, mechanical spring reset method	Internal	650	<b>159681</b>	<b>MN1H-5/3G-D-1-C</b>
	Normally closed, mechanical spring reset method	External	650	<b>159680</b>	<b>MN1H-5/3G-D-1-S-C</b>
	Normally exhausted, mechanical spring reset method	Internal	650	<b>159683</b>	<b>MN1H-5/3E-D-1-C</b>
	Normally exhausted, mechanical spring reset method	External	650	<b>159682</b>	<b>MN1H-5/3E-D-1-S-C</b>
	Normally open, mechanical spring reset method	Internal	650	<b>159685</b>	<b>MN1H-5/3B-D-1-C</b>
	Normally open, mechanical spring reset method	External	650	<b>159684</b>	<b>MN1H-5/3B-D-1-S-C</b>

1) Solenoid coils → Page 120

# Standard valves to ISO 5599-1, solenoid coil MSN1

FESTO

Technical data – Width 52 mm

Flow rate  
2300 l/min



General technical data	
Design	Piston spool valve
Sealing principle	Soft
Actuation type	Electric
Type of control	Piloted
Direction of flow	With external pilot air supply Reversible With internal pilot air supply Non-reversible
Exhaust function	With flow control
Manual override	Non-detenting, detenting via accessory
Type of mounting	On sub-base, with through-hole and screw
Mounting position	Any
Nominal size [mm]	11.5
Lap	Overlap
Width [mm]	52
Grid dimension [mm]	56
Pneumatic ports	Sub-base size 2 to ISO 5599-1
Noise level [dB (A)]	85
Conforms to standard	ISO 5599-1
Certification	With internal pilot air supply c UL us Recognised (OL)
Maritime classification <sup>1)</sup>	See certificate

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Flow rates			
Valve function	5/2-way single solenoid valve	5/2-way double solenoid valve	5/3-way valve
Standard nominal flow rate [l/min]	2300		

Switching times [ms]					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way single solenoid valve	MN1H-5/2-D-2-C	46	69	–	–
	MN1H-5/2-D-2-S-C	43	62	–	–
	MN1H-5/2-D-2-FR-C	24	62	–	–
	MN1H-5/2-D-2-FR-S-C	24	62	–	–
5/2-way double solenoid valve	JMN1H-5/2-D-2-C	–	–	21	–
	JMN1H-5/2-D-2-S-C	–	–	21	–
	JMN1DH-5/2-D-2-C	–	–	24	21
	JMN1DH-5/2-D-2-S-C	–	–	24	21
5/3-way valve	MN1H-5/3G-D-2-C	33	82	–	–
	MN1H-5/3G-D-2-S-C	33	82	–	–
	MN1H-5/3E-D-2-C	36	84	–	–
	MN1H-5/3E-D-2-S-C	36	84	–	–
	MN1H-5/3B-D-2-C	35	78	–	–
	MN1H-5/3B-D-2-S-C	35	78	–	–



# Standard valves to ISO 5599-1, solenoid coil MSN1

Technical data – Width 52 mm


Operating and environmental conditions			
Reset method		Pneumatic spring	Mechanical spring
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	Internal pilot air supply	[bar] 2 ... 10	3 ... 10
	External pilot air supply	[bar] -0.9 ... +16	-0.9 ... +16
Pilot pressure		[bar] 2 ... 10	3 ... 10
Ambient temperature		[°C] -5 ... +50	
Temperature of medium		[°C] -5 ... +50	

Safety characteristics		
Max. positive test pulse with 0 signal	[µs]	3700
Max. negative test pulse with 1 signal	[µs]	4600
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27	
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6	

Electrical data	
Electrical connection	Via N1 coil, to be ordered separately
Degree of protection to EN 60529	IP65

## Materials

Sectional view



1	Housing	Die-cast aluminium
-	Seals	HNBR, NBR
-	Note on materials	RoHS-compliant

# Standard valves to ISO 5599-1, solenoid coil MSN1


Technical data – Width 52 mm



## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)


### 5/2-way single solenoid valves



- 2 Manual override
- 3 Captive mounting screws
- 4 Slot for inscription label

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
MN1H-5/2- ...	54	38	9	30	M6	M5	116	84	48	9.5	56.5	15.3	147.6	123.4	61.7	48	24	98
MN1H-5/2- ... -FR- ...													161.5	140.7				

### 5/2-way double solenoid valves, 5/3-way valves

















- 2 Manual override
- 3 Captive mounting screws
- 4 Slot for inscription label

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
JMN1H-5/2- ...	54	38	9	30	M6	M5	116	84	48	9.5	56.5	15.3	165	123.4	61.7	48	24	98
JMN1DH-5/2- ...														123.4	61.7			
MN1H-5/3...														158	79			

# Standard valves to ISO 5599-1, solenoid coil MSN1


Ordering data – Width 52 mm


Ordering data – Valves with armature for solenoid coil MSN1 <sup>1)</sup>					
Circuit symbol	Description	Pilot air supply	Weight [g]	Part No.	Type
<b>5/2-way single solenoid valve</b>					
	Pneumatic spring reset method	Internal	710	<b>159700</b>	<b>MN1H-5/2-D-2-C</b>
	Pneumatic spring reset method	External	710	<b>159698</b>	<b>MN1H-5/2-D-2-S-C</b>
	Mechanical spring reset method	Internal	710	<b>159699</b>	<b>MN1H-5/2-D-2-FR-C</b>
	Mechanical spring reset method	External	710	<b>159718</b>	<b>MN1H-5/2-D-2-FR-S-C</b>
<b>5/2-way double solenoid valve</b>					
	–	Internal	940	<b>159702</b>	<b>JMN1H-5/2-D-2-C</b>
	–	External	940	<b>159701</b>	<b>JMN1H-5/2-D-2-S-C</b>
	With dominant signal at 14	Internal	940	<b>159703</b>	<b>JMN1DH-5/2-D-2-C</b>
	With dominant signal at 14	External	940	<b>159719</b>	<b>JMN1DH-5/2-D-2-S-C</b>
<b>5/3-way valve</b>					
	Normally closed, mechanical spring reset method	Internal	940	<b>159693</b>	<b>MN1H-5/3G-D-2-C</b>
	Normally closed, mechanical spring reset method	External	940	<b>159692</b>	<b>MN1H-5/3G-D-2-S-C</b>
	Normally exhausted, mechanical spring reset method	Internal	940	<b>159695</b>	<b>MN1H-5/3E-D-2-C</b>
	Normally exhausted, mechanical spring reset method	External	940	<b>159694</b>	<b>MN1H-5/3E-D-2-S-C</b>
	Normally open, mechanical spring reset method	Internal	940	<b>159697</b>	<b>MN1H-5/3B-D-2-C</b>
	Normally open, mechanical spring reset method	External	940	<b>159696</b>	<b>MN1H-5/3B-D-2-S-C</b>

1) Solenoid coils → Page 120

# Standard valves to ISO 5599-1, solenoid coil MSN1

Technical data – Width 65 mm

-  - Flow rate  
Up to 4600 l/min



General technical data	
Design	Piston spool valve
Sealing principle	Soft
Actuation type	Electric
Type of control	Piloted
Direction of flow	With external pilot air supply Reversible With internal pilot air supply Non-reversible
Exhaust function	With flow control
Manual override	Non-detenting, detenting via accessory
Type of mounting	On sub-base, with through-hole and screw
Mounting position	Any
Nominal size [mm]	14.5
Lap	Overlap
Width [mm]	65
Grid dimension [mm]	71
Pneumatic ports	Sub-base size 3 to ISO 5599-1
Noise level [dB (A)]	85
Conforms to standard	ISO 5599-1
Certification With internal pilot air supply	c UL us Recognised (OL)
Maritime classification <sup>1)</sup>	See certificate

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Flow rates				
Valve function	5/2-way valve	5/3-way valve		
		Normally closed	Normally exhausted	Normally open
Standard nominal flow rate [l/min]	4500	4100	4600	4000

# Standard valves to ISO 5599-1, solenoid coil MSN1

Technical data – Width 65 mm

Switching times [ms]		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way single solenoid valve	MN1H-5/2-D-3-C	49	71	–	–
	MN1H-5/2-D-3-S-C	49	71	–	–
	MN1H-5/2-D-3-FR-C	33	74	–	–
	MN1H-5/2-D-3-FR-S-C	33	74	–	–
5/2-way double solenoid valve	JMN1H-5/2-D-3-C	–	–	21	–
	JMN1H-5/2-D-3-S-C	–	–	21	–
	JMN1DH-5/2-D-3-C	–	–	24	21
	JMN1DH-5/2-D-3-S-C	–	–	24	21
5/3-way valve	MN1H-5/3G-D-3-C	33	82	–	–
	MN1H-5/3G-D-3-S-C	33	82	–	–
	MN1H-5/3E-D-3-C	36	84	–	–
	MN1H-5/3E-D-3-S-C	36	84	–	–
	MN1H-5/3B-D-3-C	35	78	–	–
	MN1H-5/3B-D-3-S-C	35	78	–	–


Operating and environmental conditions		
Reset method		Pneumatic spring   Mechanical spring
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	Internal pilot air supply [bar]	2 ... 10   3 ... 10
	External pilot air supply [bar]	–0.9 ... +16   –0.9 ... +16
Pilot pressure	[bar]	2 ... 10   3 ... 10
Ambient temperature	[°C]	–5 ... +50
Temperature of medium	[°C]	–5 ... +50

Safety characteristics	
Max. positive test pulse with 0 signal [µs]	3700
Max. negative test pulse with 1 signal [µs]	4600
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6

Electrical data	
Electrical connection	Via N1 coil, to be ordered separately
Degree of protection to EN 60529	IP65

## Materials

Sectional view



1	Housing	Die-cast aluminium
–	Seals	HNBR, NBR
–	Note on materials	RoHS-compliant

# Standard valves to ISO 5599-1, solenoid coil MSN1


Technical data – Width 65 mm



## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)


### 5/2-way single solenoid valves



- 2 Manual override
- 3 Captive mounting screws
- 4 Slot for inscription label

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
MN1H-5/2- ...	65	48	12	30	M8	M5	123	87.3	55	12	63.5	15.3	169	145.4	72.7	64	32	109
MN1H-5/2- ... -FR- ...													184.8	164.7				

### 5/2-way double solenoid valves, 5/3-way valves



- 2 Manual override
- 3 Captive mounting screws
- 4 Slot for inscription label

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
JMN1H-5/2- ...	65	48	12	30	M8	M5	123	87.3	55	12	-	15.3	185.7	145.4	72.7	64	32	109
JMN1DH-5/2- ...											-			145.4	72.7			
MN1H-5/3...											63.5	184	92					

# Standard valves to ISO 5599-1, solenoid coil MSN1

Ordering data – Width 65 mm


Ordering data – Valves with armature for solenoid coil MSN1 <sup>1)</sup>					
Circuit symbol	Description	Pilot air supply	Weight [g]	Part No.	Type
<b>5/2-way single solenoid valve</b>					
	Pneumatic spring reset method	Internal	1000	<b>159712</b>	<b>MN1H-5/2-D-3-C</b>
	Pneumatic spring reset method	External	1000	<b>159710</b>	<b>MN1H-5/2-D-3-S-C</b>
	Mechanical spring reset method	Internal	1000	<b>159711</b>	<b>MN1H-5/2-D-3-FR-C</b>
	Mechanical spring reset method	External	1000	<b>160896</b>	<b>MN1H-5/2-D-3-FR-S-C</b>
<b>5/2-way double solenoid valve</b>					
	–	Internal	1090	<b>159714</b>	<b>JMN1H-5/2-D-3-C</b>
	–	External	1090	<b>159713</b>	<b>JMN1H-5/2-D-3-S-C</b>
	With dominant signal at 14	Internal	1090	<b>159715</b>	<b>JMN1DH-5/2-D-3-C</b>
	With dominant signal at 14	External	1090	<b>160897</b>	<b>JMN1DH-5/2-D-3-S-C</b>
<b>5/3-way valve</b>					
	Normally closed, mechanical spring reset method	Internal	1170	<b>159705</b>	<b>MN1H-5/3G-D-3-C</b>
	Normally closed, mechanical spring reset method	External	1170	<b>159704</b>	<b>MN1H-5/3G-D-3-S-C</b>
	Normally exhausted, mechanical spring reset method	Internal	1170	<b>159707</b>	<b>MN1H-5/3E-D-3-C</b>
	Normally exhausted, mechanical spring reset method	External	1170	<b>159706</b>	<b>MN1H-5/3E-D-3-S-C</b>
	Normally open, mechanical spring reset method	Internal	1170	<b>159709</b>	<b>MN1H-5/3B-D-3-C</b>
	Normally open, mechanical spring reset method	External	1170	<b>159708</b>	<b>MN1H-5/3B-D-3-S-C</b>

1) Solenoid coils → Page 120

# Standard valves to ISO 5599-1, solenoid coil MSF

Technical data – Width 42 mm

Flow rate  
1200 l/min



General technical data		
Type	MFH- ... -C, JMF- ... -C	MFH- ... -EX, JMF- ... -EX
Design	Piston spool valve	Piston spool valve
Sealing principle	Soft	Soft
Actuation type	Electric	Electric
Type of control	Piloted	Piloted
Direction of flow	With external pilot air supply	Reversible
	With internal pilot air supply	Non-reversible
Exhaust function	With flow control	With flow control
Manual override	Non-detenting, detenting via accessory	Non-detenting, detenting via accessory
Type of mounting	On sub-base, via through-hole	On sub-base, via through-hole
Mounting position	Any	Any
Nominal size [mm]	8	8
Lap	Overlap	Overlap
Width [mm]	42	42
Grid dimension [mm]	43	43
Pneumatic ports	Sub-base size 1 to ISO 5599-1	Sub-base size 1 to ISO 5599-1
Noise level [dB (A)]	85	85
Conforms to standard	ISO 5599-1	ISO 5599-1
Maritime classification <sup>1)</sup>	See certificate	–

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Flow rates			
Valve function	5/2-way single solenoid valve	5/2-way double solenoid valve	5/3-way valve
Standard nominal flow rate [l/min]	1200		

Switching times [ms]					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way single solenoid valve	MFH-5/2-...	23	35	–	–
	MFH-5/2-D-1-FR-...	16	45	–	–
5/2-way double solenoid valve	JMFH-...	–	–	16	–
	JMFDH-...	–	–	16	13
5/3-way valve	MFH-5/3G-D-1-C	18	35	–	–
	MFH-5/3G-D-1-C-EX	18	35	–	–
	MFH-5/3G-D-1-S-C	18	36	–	–
	MFH-5/3G-D-1-S-C-EX	18	36	–	–
	MFH-5/3E-D-1-C	18	36	–	–
	MFH-5/3E-D-1-C-EX	18	36	–	–
	MFH-5/3E-D-1-S-C	18	36	–	–
	MFH-5/3E-D-1-S-C-EX	18	36	–	–
	MFH-5/3B-D-1-C	18	36	–	–
	MFH-5/3B-D-1-C-EX	18	36	–	–
	MFH-5/3B-D-1-S-C	18	36	–	–
	MFH-5/3B-D-1-S-C-EX	18	36	–	–



# Standard valves to ISO 5599-1, solenoid coil MSF

Technical data – Width 42 mm

ATEX	
Type	MFH- ... -EX, JMFH- ... -EX, JMFDH- ... -EX
ATEX category gas	II 2G
Ignition protection type for gas	Ex h IIC T4 Gb
ATEX category for dust	II 2D
Ignition protection type for dust	Ex h IIIC T105°C Db
Explosion-proof ambient temperature [°C]	-5 ≤ Ta ≤ +40
CE marking (see declaration of conformity)	As per EU Explosion Protection Directive (ATEX)


Operating and environmental conditions			
Reset method		Pneumatic spring	Mechanical spring
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	Internal pilot air supply [bar]	2 ... 10	3 ... 10
	External pilot air supply [bar]	-0.9 ... +16	-0.9 ... +16
Pilot pressure [bar]		2 ... 10	3 ... 10
Ambient temperature [°C]		-5 ... +40	
Temperature of medium [°C]		-10 ... +60	
		-5 ... +40 (MFH- ... -EX, JMFH- ... -EX, JMFDH- ... -EX)	

Safety characteristics	
Max. positive test pulse with 0 signal [μs]	2200
Max. negative test pulse with 1 signal [μs]	3700
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6

Electrical data	
Electrical connection	Via F coil, to be ordered separately
Degree of protection to EN 60529	IP65

## Materials

Sectional view



1	Housing	Die-cast aluminium
-	Seals	HNBR, NBR
-	Note on materials	RoHS-compliant

# Standard valves to ISO 5599-1, solenoid coil MSF


Technical data – Width 42 mm



## Dimensions


Download CAD data → [www.festo.com](http://www.festo.com)

### 5/2-way single solenoid valves



Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
MFH-5/2- ...	42	28	6	30	M5	M5	100	70.3	38	9	46.5	13.5	115	87.6	43.8	36	18	89
MFH-5/2- ... -FR- ...													125.6	98				

### 5/2-way double solenoid valves, 5/3-way valves



Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
JMFH-5/2- ...	42	28	6	30	M5	M5	100	70.3	38	9	-	13.5	142.6	87.6	43.8	36	18	89
JMFDH-5/2- ...														87.6	43.8			
MFH-5/3...														108.4	54.2			

# Standard valves to ISO 5599-1, solenoid coil MSF

Ordering data – Width 42 mm

Ordering data – Valves with armature for solenoid coil MSF <sup>1)</sup>						
Circuit symbol	Description	Pilot air supply	Weight [g]		Part No.	Type
<b>5/2-way single solenoid valve</b>						
	Pneumatic spring reset method	Internal	390	–	<b>150981</b>	<b>MFH-5/2-D-1-C</b>
				ATEX category → page 33	<b>535954</b>	<b>MFH-5/2-D-1-C-EX</b>
	Pneumatic spring reset method	External	390	–	<b>152562</b>	<b>MFH-5/2-D-1-S-C</b>
				ATEX category → page 33	<b>535957</b>	<b>MFH-5/2-D-1-S-C-EX</b>
	Mechanical spring reset method	Internal	390	–	<b>151016</b>	<b>MFH-5/2-D-1-FR-C</b>
				ATEX category → page 33	<b>535960</b>	<b>MFH-5/2-D-1-FR-C-EX</b>
	Mechanical spring reset method	External	390	–	<b>188510</b>	<b>MFH-5/2-D-1-FR-S-C</b>
<b>5/2-way double solenoid valve</b>						
	–	Internal	490	–	<b>150980</b>	<b>JMFH-5/2-D-1-C</b>
				ATEX category → page 33	<b>535963</b>	<b>JMFH-5/2-D-1-C-EX</b>
	–	External	490	–	<b>152563</b>	<b>JMFH-5/2-D-1-S-C</b>
				ATEX category → page 33	<b>535966</b>	<b>JMFH-5/2-D-1-S-C-EX</b>
	With dominant signal at 14	Internal	490	–	<b>151019</b>	<b>JMFDH-5/2-D-1-C</b>
				ATEX category → page 33	<b>536071</b>	<b>JMFDH-5/2-D-1-C-EX</b>
<b>5/3-way valve</b>						
	Normally closed, mechanical spring reset method	Internal	520	–	<b>150982</b>	<b>MFH-5/3G-D-1-C</b>
				ATEX category → page 33	<b>535969</b>	<b>MFH-5/3G-D-1-C-EX</b>
	Normally closed, mechanical spring reset method	External	520	–	<b>152564</b>	<b>MFH-5/3G-D-1-S-C</b>
				ATEX category → page 33	<b>535972</b>	<b>MFH-5/3G-D-1-S-C-EX</b>
	Normally exhausted, mechanical spring reset method	Internal	520	–	<b>150983</b>	<b>MFH-5/3E-D-1-C</b>
				ATEX category → page 33	<b>535975</b>	<b>MFH-5/3E-D-1-C-EX</b>
	Normally exhausted, mechanical spring reset method	External	520	–	<b>152565</b>	<b>MFH-5/3E-D-1-S-C</b>
				ATEX category → page 33	<b>535978</b>	<b>MFH-5/3E-D-1-S-C-EX</b>
	Normally open, mechanical spring reset method	Internal	520	–	<b>150984</b>	<b>MFH-5/3B-D-1-C</b>
				ATEX category → page 33	<b>535981</b>	<b>MFH-5/3B-D-1-C-EX</b>
	Normally open, mechanical spring reset method	External	520	–	<b>152566</b>	<b>MFH-5/3B-D-1-S-C</b>
				ATEX category → page 33	<b>535984</b>	<b>MFH-5/3B-D-1-S-C-EX</b>

1) Solenoid coils → page 120

# Standard valves to ISO 5599-1, solenoid coil MSF

FESTO

Technical data – Width 52 mm

Flow rate  
2300 l/min



General technical data		
Type	MFH- ... -C, JMF- ... -C	MFH- ... -EX, JMF- ... -EX
Design	Piston spool valve	Piston spool valve
Sealing principle	Soft	Soft
Actuation type	Electric	Electric
Type of control	Piloted	Piloted
Direction of flow	With external pilot air supply	Reversible
	With internal pilot air supply	Non-reversible
Exhaust function	With flow control	With flow control
Manual override	Non-detenting, detenting via accessory	Non-detenting, detenting via accessory
Type of mounting	On sub-base, with through-hole and screw	On sub-base, with through-hole and screw
Mounting position	Any	Any
Nominal size [mm]	11.5	11.5
Lap	Overlap	Overlap
Width [mm]	52	52
Grid dimension [mm]	56	56
Pneumatic ports	Sub-base size 2 to ISO 5599-1	Sub-base size 2 to ISO 5599-1
Noise level [dB (A)]	85	85
Conforms to standard	ISO 5599-1	ISO 5599-1
Maritime classification <sup>1)</sup>	See certificate	–

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Flow rates			
Valve function	5/2-way single solenoid valve	5/2-way double solenoid valve	5/3-way valve
Standard nominal flow rate [l/min]	2300		

Switching times [ms]					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way single solenoid valve	MFH-5/2-...	48	71	–	–
	MFH-5/2-D-2-FR-...	27	73	–	–
5/2-way double solenoid valve	JMFH-...	–	–	18	–
	JMFDH-...	–	–	18	18
5/3-way valve	MFH-5/3G-...	33	63	–	–
	MFH-5/3E-...	35	67	–	–
	MFH-5/3B-...	35	69	–	–

ATEX	
Type	MFH- ... -EX, JMFH- ... -EX, JMFDH- ... -EX
ATEX category gas	II 2G
Ignition protection type for gas	Ex h IIC T4 Gb
ATEX category for dust	II 2D
Ignition protection type for dust	Ex h IIIC T105°C Db
Explosion-proof ambient temperature [°C]	–5 ≤ Ta ≤ +40
CE marking (see declaration of conformity)	As per EU Explosion Protection Directive (ATEX)

# Standard valves to ISO 5599-1, solenoid coil MSF

Technical data – Width 52 mm


Operating and environmental conditions			
Reset method		Pneumatic spring	
		Mechanical spring	
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	Internal pilot air supply	[bar]	2 ... 10
			3 ... 10
Operating pressure	External pilot air supply	[bar]	-0.9 ... +16
			-0.9 ... +16
Pilot pressure		[bar]	2 ... 10
			3 ... 10
Ambient temperature		[°C]	-5 ... +40
Temperature of medium		[°C]	-10 ... +60

Safety characteristics		
Max. positive test pulse with 0 signal	[µs]	2200
Max. negative test pulse with 1 signal	[µs]	3700
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance		Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6

Electrical data	
Electrical connection	Via F coil, to be ordered separately
Degree of protection to EN 60529	IP65

## Materials

Sectional view



1	Housing	Die-cast aluminium
-	Seals	HNBR, NBR
-	Note on materials	RoHS-compliant

# Standard valves to ISO 5599-1, solenoid coil MSF


Technical data – Width 52 mm



## Dimensions


Download CAD data → [www.festo.com](http://www.festo.com)

### 5/2-way single solenoid valves



Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
MFH-5/2- ...	54	38	9	30	M6	M5	110	80.3	48	9.5	56.5	13.5	142	123.4	61.7	48	24	98
MFH-5/2- ... -FR- ...													159.4	140.7				













### 5/2-way double solenoid valves, 5/3-way valves



Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
JMFH-5/2- ...	54	38	9	30	M6	M5	110	80.3	48	9.5	-	13.5	160.4	123.4	61.7	48	24	97
JMFDH-5/2- ...													160.4	123.4	61.7			97
MFH-5/3...													160	158	79			98

# Standard valves to ISO 5599-1, solenoid coil MSF


Ordering data – Width 52 mm


Ordering data – Valves with armature for solenoid coil MSF <sup>1)</sup>						
Circuit symbol	Description	Pilot air supply	Weight [g]		Part No.	Type
<b>5/2-way single solenoid valve</b>						
	Pneumatic spring reset method	Internal	650	–	<b>151851</b>	<b>MFH-5/2-D-2-C</b>
				ATEX category → page 36	<b>535955</b>	<b>MFH-5/2-D-2-C-EX</b>
	Pneumatic spring reset method	External	650	–	<b>151022</b>	<b>MFH-5/2-D-2-S-C</b>
				ATEX category → page 36	<b>535958</b>	<b>MFH-5/2-D-2-S-C-EX</b>
	Mechanical spring reset method	Internal	650	–	<b>151709</b>	<b>MFH-5/2-D-2-FR-C</b>
				ATEX category → page 36	<b>535961</b>	<b>MFH-5/2-D-2-FR-C-EX</b>
<b>5/2-way double solenoid valve</b>						
	–	Internal	820	–	<b>151852</b>	<b>JMFH-5/2-D-2-C</b>
				ATEX category → page 36	<b>535964</b>	<b>JMFH-5/2-D-2-C-EX</b>
	–	External	820	–	<b>151023</b>	<b>JMFH-5/2-D-2-S-C</b>
				ATEX category → page 36	<b>535967</b>	<b>JMFH-5/2-D-2-S-C-EX</b>
	With dominant signal at 14	Internal	820	–	<b>151853</b>	<b>JMFDH-5/2-D-2-C</b>
				ATEX category → page 36	<b>536072</b>	<b>JMFDH-5/2-D-2-C-EX</b>
<b>5/3-way valve</b>						
	Normally closed, mechanical spring reset method	Internal	820	–	<b>151854</b>	<b>MFH-5/3G-D-2-C</b>
				ATEX category → page 36	<b>535970</b>	<b>MFH-5/3G-D-2-C-EX</b>
	Normally closed, mechanical spring reset method	External	820	–	<b>151024</b>	<b>MFH-5/3G-D-2-S-C</b>
				ATEX category → page 36	<b>535973</b>	<b>MFH-5/3G-D-2-S-C-EX</b>
	Normally exhausted, mechanical spring reset method	Internal	820	–	<b>151855</b>	<b>MFH-5/3E-D-2-C</b>
				ATEX category → page 36	<b>535976</b>	<b>MFH-5/3E-D-2-C-EX</b>
	Normally exhausted, mechanical spring reset method	External	820	–	<b>151025</b>	<b>MFH-5/3E-D-2-S-C</b>
				ATEX category → page 36	<b>535979</b>	<b>MFH-5/3E-D-2-S-C-EX</b>
	Normally open, mechanical spring reset method	Internal	820	–	<b>151856</b>	<b>MFH-5/3B-D-2-C</b>
				ATEX category → page 36	<b>535982</b>	<b>MFH-5/3B-D-2-C-EX</b>
	Normally open, mechanical spring reset method	External	820	–	<b>151026</b>	<b>MFH-5/3B-D-2-S-C</b>
				ATEX category → page 36	<b>535985</b>	<b>MFH-5/3B-D-2-S-C-EX</b>

1) Solenoid coils → page 120

# Standard valves to ISO 5599-1, solenoid coil MSF

Technical data – Width 65 mm

 Flow rate  
Up to 4600 l/min



General technical data		
Type	MFH- ... -C, JMF- ... -C	MFH- ... -EX, JMF- ... -EX
Design	Piston spool valve	Piston spool valve
Sealing principle	Soft	Soft
Actuation type	Electric	Electric
Type of control	Piloted	Piloted
Direction of flow	With external pilot air supply	Reversible
	With internal pilot air supply	Non-reversible
Exhaust function	With flow control	With flow control
Manual override	Non-detenting, detenting via accessory	Non-detenting, detenting via accessory
Type of mounting	On sub-base, with through-hole and screw	On sub-base, with through-hole and screw
Mounting position	Any	Any
Nominal size [mm]	14.5	14.5
Lap	Overlap	Overlap
Width [mm]	65	65
Grid dimension [mm]	71	71
Pneumatic ports	Sub-base size 3 to ISO 5599-1	Sub-base size 3 to ISO 5599-1
Noise level [dB (A)]	85	85
Conforms to standard	ISO 5599-1	ISO 5599-1
Maritime classification <sup>1)</sup>	See certificate	–

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Flow rates				
Valve function	5/2-way valve	5/3-way valve		
		Normally closed	Normally exhausted	Normally open
Nominal flow rate [l/min]	4500	4100	4600	4000

Switching times [ms]					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way single solenoid valve	MFH-5/2-...	60	66	–	–
	MFH-5/2-D-1-FR-...	28	79	–	–
5/2-way double solenoid valve	JMFH-...	–	–	18	–
	JMFDH-...	–	–	18	18
5/3-way valve	MFH-5/3G-...	36	77	–	–
	MFH-5/3E-...	37	78	–	–
	MFH-5/3B-...	36	75	–	–



# Standard valves to ISO 5599-1, solenoid coil MSF

Technical data – Width 65 mm

ATEX	
Type	MFH- ... -EX, JMFH- ... -EX, JMFDH- ... -EX
ATEX category gas	II 2G
Ignition protection type for gas	Ex h IIC T4 Gb
ATEX category for dust	II 2D
Ignition protection type for dust	Ex h IIIC T105°C Db
Explosion-proof ambient temperature [°C]	-5 ≤ Ta ≤ +40
CE marking (see declaration of conformity)	As per EU Explosion Protection Directive (ATEX)


Operating and environmental conditions			
Reset method		Pneumatic spring	Mechanical spring
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	Internal pilot air supply [bar]	2 ... 10	3 ... 10
	External pilot air supply [bar]	-0.9 ... +16	-0.9 ... +16
Pilot pressure [bar]		2 ... 10	3 ... 10
Ambient temperature [°C]		-5 ... +40	
Temperature of medium [°C]		-10 ... +60	

Safety characteristics		
Max. positive test pulse with 0 signal [µs]		2200
Max. negative test pulse with 1 signal [µs]		3700
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27	
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6	

Electrical data	
Electrical connection	Via F coil, to be ordered separately
Degree of protection to EN 60529	IP65

## Materials

Sectional view



1	Housing	Die-cast aluminium
-	Seals	HNBR, NBR
-	Note on materials	RoHS-compliant

# Standard valves to ISO 5599-1, solenoid coil MSF


Technical data – Width 65 mm



## Dimensions


Download CAD data → [www.festo.com](http://www.festo.com)

### 5/2-way single solenoid valves



Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
MFH-5/2- ...	65	48	12	30	M8	M5	117	87.3	55	12	63.5	13.5	163	145.4	72.7	64	32	109
MFH-5/2- ... -FR- ...													182	164.7				

### 5/2-way double solenoid valves, 5/3-way valves



Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
JMFH-5/2- ...	65	48	12	30	M8	M5	117	87.3	55	12	-	13.5	181	145.4	72.7	64	32	109
JMFDH-5/2- ...														145.4	72.7			
MFH-5/3...														184	92			

# Standard valves to ISO 5599-1, solenoid coil MSF

Ordering data – Width 65 mm


Ordering data – Valves with armature for solenoid coil MSF <sup>1)</sup>						
Circuit symbol	Description	Pilot air supply	Weight [g]		Part No.	Type
<b>5/2-way single solenoid valve</b>						
	Pneumatic spring reset method	Internal	960	–	<b>151870</b>	<b>MFH-5/2-D-3-C</b>
				ATEX category → page 41	<b>535956</b>	<b>MFH-5/2-D-3-C-EX</b>
	Pneumatic spring reset method	External	960	–	<b>151032</b>	<b>MFH-5/2-D-3-S-C</b>
				ATEX category → page 41	<b>535959</b>	<b>MFH-5/2-D-3-S-C-EX</b>
	Mechanical spring reset method	Internal	960	–	<b>151711</b>	<b>MFH-5/2-D-3-FR-C</b>
				ATEX category → page 41	<b>535962</b>	<b>MFH-5/2-D-3-FR-C-EX</b>
<b>5/2-way double solenoid valve</b>						
	–	Internal	1060	–	<b>151871</b>	<b>JMFH-5/2-D-3-C</b>
				ATEX category → page 41	<b>535965</b>	<b>JMFH-5/2-D-3-C-EX</b>
	–	External	1060	–	<b>151033</b>	<b>JMFH-5/2-D-3-S-C</b>
				ATEX category → page 41	<b>535968</b>	<b>JMFH-5/2-D-3-S-C-EX</b>
	With dominant signal at 14	Internal	1060	–	<b>151872</b>	<b>JMFDH-5/2-D-3-C</b>
				ATEX category → page 41	<b>536073</b>	<b>JMFDH-5/2-D-3-C-EX</b>
<b>5/3-way valve</b>						
	Normally closed, mechanical spring reset method	Internal	1040	–	<b>151873</b>	<b>MFH-5/3G-D-3-C</b>
				ATEX category → page 41	<b>535971</b>	<b>MFH-5/3G-D-3-C-EX</b>
	Normally closed, mechanical spring reset method	External	1040	–	<b>151034</b>	<b>MFH-5/3G-D-3-S-C</b>
				ATEX category → page 41	<b>535974</b>	<b>MFH-5/3G-D-3-S-C-EX</b>
	Normally exhausted, mechanical spring reset method	Internal	1040	–	<b>151874</b>	<b>MFH-5/3E-D-3-C</b>
				ATEX category → page 41	<b>535977</b>	<b>MFH-5/3E-D-3-C-EX</b>
	Normally exhausted, mechanical spring reset method	External	1040	–	<b>151035</b>	<b>MFH-5/3E-D-3-S-C</b>
				ATEX category → page 41	<b>535980</b>	<b>MFH-5/3E-D-3-S-C-EX</b>
	Normally open, mechanical spring reset method	Internal	1040	–	<b>151875</b>	<b>MFH-5/3B-D-3-C</b>
				ATEX category → page 41	<b>535983</b>	<b>MFH-5/3B-D-3-C-EX</b>
	Normally open, mechanical spring reset method	External	1040	–	<b>151036</b>	<b>MFH-5/3B-D-3-S-C</b>
				ATEX category → page 41	<b>535986</b>	<b>MFH-5/3B-D-3-S-C-EX</b>

1) Solenoid coils → page 120


## Standard valves to ISO 5599-1, central plug M12, 3-pin

FESTO

Technical data – Width 42 mm

-  - Flow rate  
Up to 1300 l/min

-  - Voltage  
24 V DC



General technical data	
Design	Piston spool valve
Sealing principle	Soft
Actuation type	Electric
Type of control	Piloted
Exhaust function	Flow control, external or via vertically stacked flow control plate
Manual override	Non-detenting, detenting
Type of mounting	On sub-base
Mounting position	Any
Nominal size [mm]	11
Lap	Overlap
Width [mm]	42
Grid dimension [mm]	43
Pneumatic ports	Sub-base size 1 to ISO 5599-1
Conforms to standard	ISO 5599-1
Certification	c CSA us (OL) c UL us - Recognised (OL)

Flow rates				
Valve function	2/2-way valve	3/2-way valve	5/2-way valve	5/3-way valve
Standard nominal flow rate [l/min]	1300	1100	1300	1300
Valve	1600	1600	2000	1900
Valve on individual sub-base	1400	1200	1400	1400
Valve pneumatically interlinked	1300	1100	1300	1400

Switching times [ms]		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
2x 2/2-way valve	VSVA-B-T22...	20	38	–	–
2x 3/2-way valve	VSVA-B-T32...	20	38	–	–
2x 3/2-way valve, reversible	VSVA-B-T32...	34	28	–	–
5/2-way single solenoid valve	VSVA-B-M52-A...	27	45	–	–
	VSVA-B-M52-M...	22	60	–	–
5/2-way double solenoid valve	VSVA-B-B52...	–	–	16	–
	VSVA-B-D52...	–	–	–	19
5/3-way valve	VSVA-B-P53...	22	65	–	–

# Standard valves to ISO 5599-1, central plug M12, 3-pin

FESTO

Technical data – Width 42 mm

Operating and environmental conditions							
Valve function		2x 2/2-way valve	2x 3/2-way valve	2x 3/2-way valve, reversible	5/2-way valve	5/3-way valve	
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]					
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]					
Note on operating/pilot medium		Lubricated operation (in which case lubricated operation will always be required)					
Operating pressure	Internal pilot air supply	[bar]	3 ... 10	3 ... 10	–	3 ... 10	3 ... 10
	External pilot air supply	[bar]	3 ... 10	3 ... 10	–0.9 ... +10	–0.9 ... +16	–0.9 ... +16
Pilot pressure		[bar]	3 ... 10				
Ambient temperature		[°C]	–5 ... +50				
Relative humidity		[%]	0 ... 90				

Safety characteristics						
Valve function		2x 3/2-way valve	5/2-way valve	5/2-way valve, with dominant signal at 14	5/3-way valve	
Max. positive test pulse with 0 signal		[µs]	1600	1400	1600	1400
Max. negative test pulse with 1 signal		[µs]	1100	900	1100	900
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27				
Vibration resistance		Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6				

Electrical data					
Valve function		2x 2/2-way valve	2x 3/2-way valve	5/2-way valve	5/3-way valve
Electrical connection		Central plug, round design M12x1, 3-pin			
Signal status display		LED			
Characteristic coil data	Voltage	[V DC]	24		
	Power	[W]	1.3	1.3	1.6
Permissible voltage fluctuations		[%]	±10		
Duty cycle		[%]	100		
Degree of protection to EN 60529		IP65, NEMA4 (in combination with a plug socket)			

Materials	
Housing	PA
Seals	NBR, FPM
Screws	Galvanised steel
Note on materials	RoHS-compliant

Product weight		
2x 2/2-way valve	[g]	442
2x 3/2-way valve	[g]	442
5/2-way single solenoid valve	[g]	426
5/2-way double solenoid valve	[g]	439
5/3-way valve	[g]	456


# Standard valves to ISO 5599-1, central plug M12, 3-pin

Technical data – Width 42 mm




## Pilot pressure p12/14 as a function of working pressure p1

2x 2/2-way valve and 2x 3/2-way valve




5/2-way valve and 5/3-way valve, external pilot air supply




## Protective circuit

Each VSVA solenoid coil is provided with a spark arresting protective circuit and protected against polarity reversal.

### 24 V DC version




### M12x1 – Pin allocation on the valve



- 2 Signal (+) Solenoid 12
- 3 com (-)
- 4 Signal (+) Solenoid 14

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)






- 1 Plug, 3-pin
- 2 Manual override
- 3 Captive screws M5 x48
- 4 Slot for inscription label
- 5 LED

Type	B1	B2	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5
VSVA-B ...-D1-1R5L	42	28	M5	58.3	48	0.25	46.6	55.3	137.8	32	36	18	69.3

# Standard valves to ISO 5599-1, central plug M12, 3-pin

Ordering data – Width 42 mm

## ★ Core product range










Ordering data					
Circuit symbol	Description	Direction of flow	Pilot air supply	Part No.	Type
5/2-way single solenoid valve					
	Pneumatic spring reset method	Non-reversible	Internal	★ 561362	VSVA-B-M52-AD-D1-1R5L
	Mechanical spring reset method	Non-reversible	Internal	★ 561363	VSVA-B-M52-MD-D1-1R5L
5/2-way double solenoid valve					
	Dominance at 1st signal	Non-reversible	Internal	★ 561364	VSVA-B-B52-D-D1-1R5L

Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ☆ Generally ready for shipping ex works in 5 days

# Standard valves to ISO 5599-1, central plug M12, 3-pin

Ordering data – Width 42 mm

Ordering data					
Circuit symbol	Description	Direction of flow	Pilot air supply	Part No.	Type
<b>2x 2/2-way valve</b>					
	2x normally closed, pneumatic spring reset method	Non-reversible	Internal	Order via online configurator ➔ Internet: vsva	
	2x normally closed, pneumatic spring reset method	Non-reversible	External		
	2x normally closed, vacuum operation possible at 3 and 5, pneumatic spring reset method	Reversible	Internal		
<b>2x 3/2-way valve</b>					
	2x normally closed, pneumatic spring reset method	Non-reversible	Internal	561359	VSVA-B-T32C-AD-D1-1R5L
	2x normally closed, pneumatic spring reset method	Non-reversible	External	561369	VSVA-B-T32C-AZD-D1-1R5L
	2x normally open, pneumatic spring reset method	Non-reversible	Internal	561360	VSVA-B-T32U-AD-D1-1R5L
	2x normally open, pneumatic spring reset method	Non-reversible	External	561370	VSVA-B-T32U-AZD-D1-1R5L
	1x normally closed, 1x normally open, pneumatic spring reset method	Non-reversible	Internal	561361	VSVA-B-T32H-AD-D1-1R5L
	1x normally closed, 1x normally open, pneumatic spring reset method	Non-reversible	External	561371	VSVA-B-T32H-AZD-D1-1R5L



# Standard valves to ISO 5599-1, central plug M12, 3-pin

Ordering data – Width 42 mm

Ordering data				
Circuit symbol	Description	Direction of flow	Pilot air supply	Part No. Type
2x 3/2-way valve, reversible				
	2x normally closed, pneumatic spring reset method	Reversible	External	Order via online configurator ➔ Internet: vsva
	2x normally open, pneumatic spring reset method	Reversible	External	
	1x normally closed, 1x normally open, pneumatic spring reset method	Reversible	External	

# Standard valves to ISO 5599-1, central plug M12, 3-pin


Ordering data – Width 42 mm

Ordering data					
Circuit symbol	Description	Direction of flow	Pilot air supply	Part No.	Type
<b>5/2-way single solenoid valve</b>					
	Pneumatic spring reset method	Reversible	External	561372	VSVA-B-M52-AZD-D1-1R5L
	Mechanical spring reset method	Reversible	External	561373	VSVA-B-M52-MZD-D1-1R5L
<b>5/2-way double solenoid valve</b>					
	Dominance at 1st signal	Reversible	External	561374	VSVA-B-B52-ZD-D1-1R5L
	Dominant signal at 14	Non-reversible	Internal	561365	VSVA-B-D52-D-D1-1R5L
	Dominant signal at 14	Reversible	External	561375	VSVA-B-D52-ZD-D1-1R5L
<b>5/3-way valve</b>					
	Normally closed, mechanical spring reset method	Non-reversible	Internal	561366	VSVA-B-P53C-D-D1-1R5L
	Normally closed, mechanical spring reset method	Reversible	External	561376	VSVA-B-P53C-ZD-D1-1R5L
	Normally open, mechanical spring reset method	Non-reversible	Internal	561368	VSVA-B-P53U-D-D1-1R5L
	Normally open, mechanical spring reset method	Reversible	External	561378	VSVA-B-P53U-ZD-D1-1R5L
	Normally exhausted, mechanical spring reset method	Non-reversible	Internal	561367	VSVA-B-P53E-D-D1-1R5L
	Normally exhausted, mechanical spring reset method	Reversible	External	561377	VSVA-B-P53E-ZD-D1-1R5L

## Standard valves to ISO 5599-1, central plug M12, 3-pin

FESTO

Technical data – Width 52 mm

-  - Flow rate  
Up to 2800 l/min

-  - Voltage  
24 V DC



General technical data	
Design	Piston spool valve
Sealing principle	Soft
Actuation type	Electric
Type of control	Piloted
Exhaust-air function	Flow control, external or via vertically stacked flow control plate
Manual override	Non-detenting, detenting
Type of mounting	On sub-base
Mounting position	Any
Nominal size [mm]	15
Lap	Overlap
Width [mm]	52
Grid dimension [mm]	59
Pneumatic ports	Sub-base size 2 to ISO 5599-1
Conforms to standard	ISO 5599-1
Certification	c CSA us (OL)
	c UL us - Recognised (OL)
	C-Tick

Flow rates				
Valve function	2/2-way valve	3/2-way valve	5/2-way valve	5/3-way valve
Standard nominal flow rate [l/min]	2800	2200	2800	2700
Valve	4000	3000	4000	3600
Valve on individual sub-base	2400	2000	2400	2300
Valve pneumatically interlinked	2800	2200	2800	2700

Switching times [ms]					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
2x 2/2-way valve	VSVA-B-T22...	14	35	–	–
2x 3/2-way valve	VSVA-B-T32...	20	35	–	–
2x 3/2-way valve, reversible	VSVA-B-T32...	30	30	–	–
5/2-way single solenoid valve	VSVA-B-M52-A...	40	45	–	–
	VSVA-B-M52-M...	20	60	–	–
5/2-way double solenoid valve	VSVA-B-B52...	–	–	18	–
	VSVA-B-D52...	–	–	–	18
5/3-way valve	VSVA-B-P53...	23	60	–	–

# Standard valves to ISO 5599-1, central plug M12, 3-pin

FESTO

Technical data – Width 52 mm

Operating and environmental conditions						
Valve function			2x 2/2-way valve	2x 3/2-way valve	2x 3/2-way valve, reversible	5/2-way valve 5/3-way valve
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]				
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]				
Note on operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)				
Operating pressure	Internal pilot air supply	[bar]	3 ... 10	3 ... 10	–	3 ... 10 3 ... 10
	External pilot air supply	[bar]	3 ... 10	3 ... 10	–0.9 ... +10	–0.9 ... +16 –0.9 ... +16
Pilot pressure		[bar]	3 ... 10			
Ambient temperature		[°C]	–5 ... +50			
Relative humidity		[%]	0 ... 90			

Safety characteristics	
CE marking (see declaration of conformity)	To EU EMC Directive <sup>1)</sup>
KC mark	KC EMC
Max. positive test pulse with 0 signal	[µs] 1000
Max. negative test pulse with 1 signal	[µs] 3500
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6

- 1) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: [www.festo.com/sp](http://www.festo.com/sp) → Certificates.  
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

Electrical data			
Electrical connection		Central plug, round design M12x1, 3-pin	
Signal status display		LED	
Characteristic coil data	Voltage	[V DC]	24
	Power	[W]	4.6
Permissible voltage fluctuations		[%]	±10
Nominal pick-up current per solenoid coil		[mA]	165
Nominal current with current reduction		[mA]	35
Time until current reduction		[ms]	30
Duty cycle		[%]	100
Degree of protection to EN 60529		IP65, NEMA4 (in combination with a plug socket)	

Materials	
Housing	Die-cast aluminium, PA
Seals	HNBR, NBR, FPM
Screws	Galvanised steel
Note on materials	RoHS-compliant


Product weight		
2x 2/2-way valve	[g]	740
2x 3/2-way valve	[g]	740
5/2-way single solenoid valve	[g]	702
5/2-way double solenoid valve	[g]	732
5/3-way valve	[g]	780

# Standard valves to ISO 5599-1, central plug M12, 3-pin


Technical data – Width 52 mm

## Pilot pressure p12/14 as a function of working pressure p1

2x 2/2-way valve and 2x 3/2-way valve




5/2-way valve and 5/3-way valve, external pilot air supply



## Protective circuit


Each VSVA solenoid coil is provided with a spark arresting protective circuit and protected against polarity reversal.

## 24 V DC version



1 Reduction of holding current




## M12x1 – Pin allocation on the valve



- 2 Signal (+) Solenoid 12
- 3 com (-)
- 4 Signal (+) Solenoid 14

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



- 1 Plug, 3-pin
- 2 Manual override
- 3 Captive screws M6 x60
- 4 Slot for inscription label
- 5 LED

Type	B1	B2	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5
VSVA-B ...D2-1R5L	52	38	M6	58.3	60	0.3	56.4	55.3	160.7	40.9	48	24	64.3















# Standard valves to ISO 5599-1, central plug M12, 3-pin

Ordering data – Width 52 mm

Ordering data					
Circuit symbol	Description	Direction of flow	Pilot air supply	Part No.	Type
<b>2x 2/2-way valve</b>					
	2x normally closed, pneumatic spring reset method	Non-reversible	Internal	Order via online configurator ➔ Internet: vsva	
	2x normally closed, pneumatic spring reset method	Non-reversible	External		
<b>2x 3/2-way valve</b>					
	2x normally closed, pneumatic spring reset method	Non-reversible	Internal	<b>566990</b>	<b>VSVA-B-T32C-AD-D2-1R5L</b>
	2x normally closed, pneumatic spring reset method	Non-reversible	External	<b>567000</b>	<b>VSVA-B-T32C-AZD-D2-1R5L</b>
	2x normally open, pneumatic spring reset method	Non-reversible	Internal	<b>566991</b>	<b>VSVA-B-T32U-AD-D2-1R5L</b>
	2x normally open, pneumatic spring reset method	Non-reversible	External	<b>567001</b>	<b>VSVA-B-T32U-AZD-D2-1R5L</b>
	1x normally closed, 1x normally open, pneumatic spring reset method	Non-reversible	Internal	<b>566992</b>	<b>VSVA-B-T32H-AD-D2-1R5L</b>
	1x normally closed, 1x normally open, pneumatic spring reset method	Non-reversible	External	<b>567002</b>	<b>VSVA-B-T32H-AZD-D2-1R5L</b>
<b>2x 3/2-way valve, reversible</b>					
	2x normally closed, pneumatic spring reset method	Reversible	External	Order via online configurator ➔ Internet: vsva	
	2x normally open, pneumatic spring reset method	Reversible	External		
	1x normally closed, 1x normally open, pneumatic spring reset method	Reversible	External		

# Standard valves to ISO 5599-1, central plug M12, 3-pin


Ordering data – Width 52 mm

Ordering data					
Circuit symbol	Description	Direction of flow	Pilot air supply	Part No.	Type
<b>5/2-way single solenoid valve</b>					
	Pneumatic spring reset method	Non-reversible	Internal	566993	VSVA-B-M52-AD-D2-1R5L
	Pneumatic spring reset method	Reversible	External	567003	VSVA-B-M52-AZD-D2-1R5L
	Mechanical spring reset method	Non-reversible	Internal	566994	VSVA-B-M52-MD-D2-1R5L
	Mechanical spring reset method	Reversible	External	567004	VSVA-B-M52-MZD-D2-1R5L
<b>5/2-way double solenoid valve</b>					
	Dominance at 1st signal	Non-reversible	Internal	566995	VSVA-B-B52-D-D2-1R5L
	Dominance at 1st signal	Reversible	External	567005	VSVA-B-B52-ZD-D2-1R5L
	Dominant signal at 14	Non-reversible	Internal	566996	VSVA-B-D52-D-D2-1R5L
	Dominant signal at 14	Reversible	External	567006	VSVA-B-D52-ZD-D2-1R5L
<b>5/3-way valve</b>					
	Normally closed, mechanical spring reset method	Non-reversible	Internal	566997	VSVA-B-P53C-D-D2-1R5L
	Normally closed, mechanical spring reset method	Reversible	External	567007	VSVA-B-P53C-ZD-D2-1R5L
	Normally open, mechanical spring reset method	Non-reversible	Internal	566999	VSVA-B-P53U-D-D2-1R5L
	Normally open, mechanical spring reset method	Reversible	External	567009	VSVA-B-P53U-ZD-D2-1R5L
	Normally exhausted, mechanical spring reset method	Non-reversible	Internal	566998	VSVA-B-P53E-D-D2-1R5L
	Normally exhausted, mechanical spring reset method	Reversible	External	567008	VSVA-B-P53E-ZD-D2-1R5L


## Standard valves to ISO 5599-1, central plug M12, 4-pin

FESTO

Technical data – Width 65 mm

-  - Flow rate  
Up to 4600 l/min

-  - Voltage  
24 V DC



General technical data	
Design	Piston spool valve
Sealing principle	Soft
Actuation type	Electric
Type of control	Piloted
Direction of flow	Non-reversible
Exhaust function	With flow control
Manual override	Non-detenting
Type of mounting	Via through-hole
Mounting position	Any
Nominal size	[mm] 14.5
Width	[mm] 65
Grid dimension	[mm] 71
Pneumatic ports	Sub-base size 3 to ISO 5599-1
Conforms to standard	ISO 5599-1

Flow rates					
Valve function		5/2-way valve	5/3-way valve		
			Normally closed	Normally exhausted	Normally open
Standard nominal flow rate	[l/min]	4500	4100	4600	4000

Switching times [ms]					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way single solenoid valve	MEBH-5/2-...	59	87	-	-
	MEBH-5/2-D-1-ZSR-FR-...	28	109	-	-
5/2-way double solenoid valve	JMEBH-...	-	-	16	-
	JMEBDH-...	-	-	-	20
5/3-way valve	MEBH-5/3G-...	38	130	-	-
	MEBH-5/3E-...	38	130	-	-
	MEBH-5/3B-...	38	130	-	-



# Standard valves to ISO 5599-1, central plug M12, 4-pin


Technical data – Width 65 mm

Operating and environmental conditions			
Reset method		Pneumatic spring	Mechanical spring
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[bar]	2 ... 10	3 ... 10
Ambient temperature	[°C]	-5 ... +50	
Temperature of medium	[°C]	-5 ... +50	
Relative humidity	[%]	0 ... 90	


Electrical data			
Electrical connection		Central plug, round design M12x1, 4-pin	
Characteristic coil data	Voltage	[V DC]	24
	Power	[W]	2.5
Degree of protection to EN 60529		IP65	

## Materials


Sectional view MEBH-5/2- ...



Sectional view JMEBH-5/2- ..., JMEBDH-5/2- ...



Sectional view MEBH-5/3...



1	Housing	Die-cast aluminium
-	Seals	NBR


# Standard valves to ISO 5599-1, central plug M12, 4-pin

Technical data – Width 65 mm

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)


### 5/2-way single solenoid valves



- 1 Attachment of plug socket adjustable by 3x30°
- 2 Manual override
- 3 Captive mounting screws
- 5 LED display
- 6 Angled plug socket SIE-WD-TR  
→ page 122

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
MEBH-5/2 ...	65	48	12	17.5	M8	M12	130	97.8	55	12	93.1	158.7	145.4	72.7	64	32	86
MEBH-5/2- ... -FR-C												178	164.7				

### 5/2-way double solenoid valves, 5/3-way valves



- 1 Attachment of plug socket adjustable by 3x30°
- 2 Manual override
- 3 Captive mounting screws
- 5 LED display
- 6 Angled plug socket SIE-WD-TR  
→ page 122


Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
JMEBH-5/2- ...	65	48	12	17.5	M8	M12	130	97.8	55	12	93.1	171.9	145.4	72.7	64	32	86
JMEBDH-5/2- ...													145.4	72.7			
MEBH-5/3...													184	92			

# Standard valves to ISO 5599-1, central plug M12, 4-pin

Ordering data – Width 65 mm


## Central plug M12 – Pin allocation

### 5/2-way single solenoid valve



- 1 Unused
- 2 Unused
- 3 com (-)
- 4 Signal (+) Solenoid 14

### 5/2-way double solenoid valve and 5/3-way valve



- 1 Unused
- 2 Signal (+) Solenoid 12
- 3 com (-)
- 4 Signal (+) Solenoid 14


## Ordering data

Circuit symbol	Description	Pilot air supply	Weight [g]	Part No.	Type
<b>5/2-way single solenoid valve</b>					
	Pneumatic spring reset method	Internal	1000	<b>184507</b>	<b>MEBH-5/2-D-3-ZSR-C</b>
	Mechanical spring reset method	Internal	1000	<b>184508</b>	<b>MEBH-5/2-D-3-ZSR-FR-C</b>
<b>5/2-way double solenoid valve</b>					
	–	Internal	1080	<b>184509</b>	<b>JMEBH-5/2-D-3-ZSR-C</b>
	With dominant signal at 14	Internal	1080	<b>184510</b>	<b>JMEBDH-5/2-D-3-ZSR-C</b>
<b>5/3-way valve</b>					
	Normally closed, mechanical spring reset method	Internal	1120	<b>184512</b>	<b>MEBH-5/3G-D-3-ZSR-C</b>
	Normally exhausted, mechanical spring reset method	Internal	1120	<b>184511</b>	<b>MEBH-5/3E-D-3-ZSR-C</b>
	Normally open, mechanical spring reset method	Internal	1120	<b>184513</b>	<b>MEBH-5/3B-D-3-ZSR-C</b>

# Standard valves to ISO 5599-1, individual plug M12x1

FESTO

Technical data – Width 42 mm

-  - Flow rate  
1200 l/min

-  - Voltage  
24 V DC



General technical data		
Design		Piston spool valve
Sealing principle		Soft
Actuation type		Electric
Type of control		Piloted
Direction of flow	With external pilot air supply	Reversible
	With internal pilot air supply	Non-reversible
Exhaust function		With flow control
Manual override		Non-detenting
Type of mounting		On sub-base via through-holes
Mounting position		Any
Nominal size	[mm]	8
Lap		Overlap
Width	[mm]	42
Grid dimension	[mm]	43
Pneumatic ports		Sub-base size 1 to ISO 5599-1
Noise level	[dB (A)]	85
Conforms to standard		ISO 5599-1

Flow rates		
Standard nominal flow rate	[l/min]	1200

Switching times [ms]					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way single solenoid valve	MDH-5/2-...	25	36	-	-
	MDH-5/2-...-FR-...	20	42	-	-
5/2-way double solenoid valve	JMDH-...	-	-	18	-
	JMDDH-...	-	-	18	18
5/3-way valve	MDH-5/3G-...	25	55	-	-
	MDH-5/3E-...	25	55	-	-
	MDH-5/3B-...	25	55	-	-

# Standard valves to ISO 5599-1, individual plug M12x1

Technical data – Width 42 mm

Operating and environmental conditions			
Reset method		Pneumatic spring	Mechanical spring
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	Internal pilot air supply	[bar]	2 ... 10
	External pilot air supply	[bar]	-0.9 ... +16
Pilot pressure	Internal pilot air supply	[bar]	2 ... 10
	External pilot air supply	[bar]	3 ... 10
Ambient temperature		[°C]	-10 ... +50
Temperature of medium		[°C]	-10 ... +50

Safety characteristics		
Max. positive test pulse with 0 signal	[µs]	3800
Max. negative test pulse with 1 signal	[µs]	4900
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27	
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6	

Electrical data			
Electrical connection		M12x1	
Characteristic coil data	Voltage	[V DC]	24
	Power	[W]	2.7
Permissible voltage fluctuations		[%]	±10
Duty cycle		[%]	100
Degree of protection to EN 60529		IP65	

# Standard valves to ISO 5599-1, individual plug M12x1



FESTO

Technical data – Width 42 mm


## Materials

Sectional view MDH-5/2- ...

Sectional view JMDH-5/2- ..., JMDDH-5/2- ...



Sectional view MDH-5/3...



1	Housing	Die-cast aluminium
-	Seals	HNBR, NBR


# Standard valves to ISO 5599-1, individual plug M12x1

Technical data – Width 42 mm

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)


### 5/2-way single solenoid valves



- 1 Solenoid coil can be repositioned by 90° regardless of manual override
- 2 Manual override
- 3 Captive mounting screws
- 4 Slot for inscription label
- 5 LED display
- 6 Device plug M12x1  
2-pin coil to VDMA  
4-pin coil to Desina

Type	B1	B2	B3	B4	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
MDH-5/2 ...	42	28	6	30	M5	87.2	77.2	38	9	46.5	121.8	87.6	43.8	36	18	-
MDH-5/2- ... -FR...											132.2	98				

### 5/2-way double solenoid valves, 5/3-way valves














- 1 Solenoid coil can be repositioned by 90° regardless of manual override
- 2 Manual override
- 3 Captive mounting screws
- 4 Slot for inscription label
- 5 LED display
- 6 Device plug M12x1  
2-pin coil to VDMA  
4-pin coil to Desina

Type	B1	B2	B3	B4	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
JMDH-5/2- ...	42	28	6	30	M5	87.2	77.2	38	9	-	148	87.6	43.8	36	18	108.5
JMDDH-5/2- ...												87.6	43.8			
MDH-5/3...												108.4	54.3			

# Standard valves to ISO 5599-1, individual plug M12x1

Ordering data – Width 42 mm


Pin allocation	
M12 plug – 2-pin to VDMA	M12 plug – 4-pin to Desina
	
1 Unused 2 Unused 3 com (-) 4 Signal (+)	1 Connected to 2 2 Connected to 1 3 com (-) 4 Signal (+)

Ordering data – Solenoid valves						
Circuit symbol	Description	Coil	Pilot air supply	Weight [g]	Part No.	Type
<b>5/2-way single solenoid valve</b>						
	Pneumatic spring reset method	2-pin to VDMA	Internal	420	<b>197125</b>	<b>MDH-5/2-D-1-M12-C</b>
		4-pin to Desina	Internal	420	<b>540803</b>	<b>MDH-5/2-D-1-M12D-C</b>
	Pneumatic spring reset method	2-pin to VDMA	External	420	<b>533332</b>	<b>MDH-5/2-D-1-S-M12-C</b>
		4-pin to Desina	External	420	<b>540810</b>	<b>MDH-5/2-D-1-S-M12D-C</b>
	Mechanical spring reset method	2-pin to VDMA	Internal	420	<b>533010</b>	<b>MDH-5/2-D-1-FR-M12-C</b>
		4-pin to Desina	Internal	420	<b>540804</b>	<b>MDH-5/2-D-1-FR-M12D-C</b>
	Mechanical spring reset method	2-pin to VDMA	External	420	<b>533761</b>	<b>MDH-5/2-D-1-S-FR-M12-C</b>
		4-pin to Desina	External	420	<b>540811</b>	<b>MDH-5/2-D-1-S-FR-M12D-C</b>
<b>5/2-way double solenoid valve</b>						
	-	2-pin to VDMA	Internal	550	<b>532687</b>	<b>JMDH-5/2-D-1-M12-C</b>
		4-pin to Desina	Internal	550	<b>540809</b>	<b>JMDH-5/2-D-1-M12D-C</b>
	With dominant signal at 14	2-pin to VDMA	Internal	550	<b>539079</b>	<b>JMDDH-5/2-D-1-M12-C</b>
		4-pin to Desina	Internal	550	<b>540808</b>	<b>JMDDH-5/2-D-1-M12D-C</b>
<b>5/3-way valve</b>						
	Normally closed, mechanical spring reset method	2-pin to VDMA	Internal	580	<b>525307</b>	<b>MDH-5/3G-D-1-M12-C</b>
		4-pin to Desina	Internal	580	<b>540806</b>	<b>MDH-5/3G-D-1-M12D-C</b>
	Normally exhausted, mechanical spring reset method	2-pin to VDMA	Internal	580	<b>197126</b>	<b>MDH-5/3E-D-1-M12-C</b>
		4-pin to Desina	Internal	580	<b>540805</b>	<b>MDH-5/3E-D-1-M12D-C</b>
	Normally open, mechanical spring reset method	2-pin to VDMA	Internal	580	<b>533005</b>	<b>MDH-5/3B-D-1-M12-C</b>
		4-pin to Desina	Internal	580	<b>540807</b>	<b>MDH-5/3B-D-1-M12D-C</b>



# Standard valves to ISO 5599-1, individual plug M12x1

Technical data – Width 52 mm

-  - Flow rate  
2300 l/min

-  - Voltage  
24 V DC



General technical data	
Design	Piston spool valve
Sealing principle	Soft
Actuation type	Electric
Type of control	Piloted
Direction of flow	Non-reversible
Exhaust function	With flow control
Manual override	Non-detenting
Type of mounting	On sub-base, with through-hole and screw
Mounting position	Any
Nominal size	[mm] 11.5
Lap	Overlap
Width	[mm] 52
Grid dimension	[mm] 56
Pneumatic ports	Sub-base size 2 to ISO 5599-1
Noise level	[dB (A)] 85
Conforms to standard	ISO 5599-1

Flow rates	
Standard nominal flow rate	[l/min] 2300

Switching times [ms]					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way single solenoid valve	MDH-5/2-...	45	60	-	-
	MDH-5/2-...-FR-...	25	60	-	-
5/2-way double solenoid valve	JMDH-...	-	-	20	-
	JMDDH-...	-	-	20	20
5/3-way valve	MDH-5/3G-...	35	70	-	-
	MDH-5/3E-...	35	70	-	-
	MDH-5/3B-...	35	70	-	-

# Standard valves to ISO 5599-1, individual plug M12x1

Technical data – Width 52 mm

Operating and environmental conditions		
Reset method		Pneumatic spring      Mechanical spring
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[bar]	2 ... 10      3 ... 10
Ambient temperature	[°C]	-10 ... +50
Temperature of medium	[°C]	-10 ... +50



Safety characteristics		
Max. positive test pulse with 0 signal	[µs]	3800
Max. negative test pulse with 1 signal	[µs]	4900
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance		Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6

Electrical data		
Electrical connection		M12x1
Characteristic coil data	Voltage	[V DC] 24
	Power	[W] 2.7
Permissible voltage fluctuations	[%]	±10
Duty cycle	[%]	100
Degree of protection to EN 60529		IP65


## Materials

Sectional view MDH-5/2- ...

Sectional view JMDH-5/2- ..., JMDDH-5/2- ...



Sectional view MDH-5/3...



1	Housing	Die-cast aluminium
-	Seals	HNBR, NBR
-	Note on materials	RoHS-compliant


# Standard valves to ISO 5599-1, individual plug M12x1

Technical data – Width 52 mm

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)


### 5/2-way single solenoid valves



- 1 Solenoid coil can be repositioned by 90° regardless of manual override
- 2 Manual override
- 3 Captive mounting screws
- 4 Slot for inscription label
- 5 LED display
- 6 Device plug M12x1  
2-pin coil to VDMA  
4-pin coil to Desina

Type	B1	B2	B3	B4	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
MDH-5/2 ...	54	38	9	30	M6	97.2	87.2	48	9.5	56.5	144.6	123.4	61.7	48	24	-
MDH-5/2- ... -FR...											161.9	140.6				

### 5/2-way double solenoid valves, 5/3-way valves









- 1 Solenoid coil can be repositioned by 90° regardless of manual override
- 2 Manual override
- 3 Captive mounting screws
- 5 LED display
- 6 Device plug M12x1  
2-pin coil to VDMA  
4-pin coil to Desina

Type	B1	B2	B3	B4	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
JMDH-5/2- ...	54	38	9	30	M6	97.2	87.2	48	9.5	-	165.8	123.4	61.7	48	24	126.3
JMDDH-5/2- ...												123.4	61.7			
MDH-5/3...												158	79			

# Standard valves to ISO 5599-1, individual plug M12x1


Ordering data – Width 52 mm

Pin allocation	
M12 plug – 2-pin to VDMA	M12 plug – 4-pin to Desina
	
1 Unused 2 Unused 3 com (-) 4 Signal (+)	1 Connected to 2 2 Connected to 1 3 com (-) 4 Signal (+)

Ordering data						
Circuit symbol	Description	Coil	Pilot air supply	Weight [g]	Part No.	Type
<b>5/2-way single solenoid valve</b>						
	Pneumatic spring reset method	2-pin to VDMA	Internal	810	<b>533008</b>	<b>MDH-5/2-D-2-M12-C</b>
		4-pin to Desina	Internal	810	<b>540812</b>	<b>MDH-5/2-D-2-M12D-C</b>
	Mechanical spring reset method	2-pin to VDMA	Internal	810	<b>533011</b>	<b>MDH-5/2-D-2-FR-M12-C</b>
		4-pin to Desina	Internal	810	<b>540813</b>	<b>MDH-5/2-D-2-FR-M12D-C</b>
<b>5/2-way double solenoid valve</b>						
	–	2-pin to VDMA	Internal	940	<b>533013</b>	<b>JMDH-5/2-D-2-M12-C</b>
		4-pin to Desina	Internal	940	<b>540818</b>	<b>JMDH-5/2-D-2-M12D-C</b>
	With dominant signal at 14	2-pin to VDMA	Internal	940	<b>539077</b>	<b>JMDDH-5/2-D-2-M12-C</b>
		4-pin to Desina	Internal	940	<b>540817</b>	<b>JMDDH-5/2-D-2-M12D-C</b>
<b>5/3-way valve</b>						
	Normally closed, mechanical spring reset method	2-pin to VDMA	Internal	1000	<b>539078</b>	<b>MDH-5/3G-D-2-M12-C</b>
		4-pin to Desina	Internal	1000	<b>540815</b>	<b>MDH-5/3G-D-2-M12D-C</b>
	Normally exhausted, mechanical spring reset method	2-pin to VDMA	Internal	1000	<b>533016</b>	<b>MDH-5/3E-D-2-M12-C</b>
		4-pin to Desina	Internal	1000	<b>540814</b>	<b>MDH-5/3E-D-2-M12D-C</b>
	Normally open, mechanical spring reset method	2-pin to VDMA	Internal	1000	<b>533006</b>	<b>MDH-5/3B-D-2-M12-C</b>
		4-pin to Desina	Internal	1000	<b>540816</b>	<b>MDH-5/3B-D-2-M12D-C</b>

# Standard valves to ISO 5599-1, individual plug M12x1

Technical data – Width 65 mm

-  - Flow rate  
4500 l/min

-  - Voltage  
24 V DC



General technical data	
Design	Piston spool valve
Sealing principle	Soft
Actuation type	Electric
Type of control	Piloted
Direction of flow	Non-reversible
Exhaust function	With flow control
Manual override	Non-detenting
Type of mounting	On sub-base, with through-hole and screw
Mounting position	Any
Nominal size [mm]	14.5
Lap	Overlap
Width [mm]	65
Grid dimension [mm]	71
Pneumatic ports	Sub-base size 3 to ISO 5599-1
Noise level [dB (A)]	85
Conforms to standard	ISO 5599-1

Flow rates				
Valve function	5/2-way valve	5/3-way valve		
		Normally closed	Normally exhausted	Normally open
Standard nominal flow rate [l/min]	4500	4100	4600	4000

Switching times [ms]					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way single solenoid valve	MDH-5/2-...	54	57	-	-
	MDH-5/2-...-FR-...	28	68	-	-
5/2-way double solenoid valve	JMDH-...	-	-	21	-
	JMDDH-...	-	-	23	23
5/3-way valve	MDH-5/3G-...	35	79	-	-
	MDH-5/3E-...	36	84	-	-
	MDH-5/3B-...	36	84	-	-

# Standard valves to ISO 5599-1, individual plug M12x1

Technical data – Width 65 mm

Operating and environmental conditions		
Reset method		Pneumatic spring      Mechanical spring
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[bar]	2 ... 10      3 ... 10
Ambient temperature	[°C]	-10 ... +50
Temperature of medium	[°C]	-10 ... +50



Safety characteristics		
Max. positive test pulse with 0 signal	[µs]	3800
Max. negative test pulse with 1 signal	[µs]	4900
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance		Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6

Electrical data		
Electrical connection		M12x1
Characteristic coil data	Voltage	[V DC] 24
	Power	[W] 2.7
Permissible voltage fluctuations	[%]	±10
Duty cycle	[%]	100
Degree of protection to EN 60529		IP65


## Materials

Sectional view MDH-5/2- ...

Sectional view JMDH-5/2- ..., JMDDH-5/2- ...



Sectional view MDH-5/3...



1	Housing	Die-cast aluminium
-	Seals	HNBR, NBR
-	Note on materials	RoHS-compliant


# Standard valves to ISO 5599-1, individual plug M12x1

Technical data – Width 65 mm

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)


### 5/2-way single solenoid valves



- 1 Solenoid coil can be repositioned by 90° regardless of manual override
- 2 Manual override
- 3 Captive mounting screws
- 4 Slot for inscription label
- 5 LED display
- 6 Device plug M12x1  
2-pin coil to VDMA  
4-pin coil to Desina

Type	B1	B2	B3	B4	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
MDH-5/2 ...	65	48	12	30	M8	104.2	94.2	55	12	62.5	165.9	145.4	72.7	64	32	-
MDH-5/2- ... -FR...											182.5	140.6				

### 5/2-way double solenoid valves, 5/3-way valves












- 1 Solenoid coil can be repositioned by 90° regardless of manual override
- 2 Manual override
- 3 Captive mounting screws
- 5 LED display
- 6 Device plug M12x1  
2-pin coil to VDMA  
4-pin coil to Desina

Type	B1	B2	B3	B4	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
JMDH-5/2- ...	65	48	12	30	M8	104.2	94.2	55	12	-	186.4	145.4	72.7	64	32	146.9
JMDDH-5/2- ...												145.4	72.7			
MDH-5/3...												184	92			

# Standard valves to ISO 5599-1, individual plug M12x1

Ordering data – Width 65 mm

Pin allocation	
M12 plug – 2-pin to VDMA	M12 plug – 4-pin to Desina
	
1 Unused 2 Unused 3 com (-) 4 Signal (+)	1 Connected to 2 2 Connected to 1 3 com (-) 4 Signal (+)


Ordering data						
Circuit symbol	Description	Coil	Pilot air supply	Weight [g]	Part No.	Type
<b>5/2-way single solenoid valve</b>						
	Pneumatic spring reset method	2-pin to VDMA	Internal	1000	<b>533009</b>	<b>MDH-5/2-D-3-M12-C</b>
		4-pin to Desina	Internal	1000	<b>540819</b>	<b>MDH-5/2-D-3-M12D-C</b>
	Mechanical spring reset method	2-pin to VDMA	Internal	1000	<b>533012</b>	<b>MDH-5/2-D-3-FR-M12-C</b>
		4-pin to Desina	Internal	1000	<b>540820</b>	<b>MDH-5/2-D-3-FR-M12D-C</b>
<b>5/2-way double solenoid valve</b>						
	–	2-pin to VDMA	Internal	1100	<b>533015</b>	<b>JMDH-5/2-D-3-M12-C</b>
		4-pin to Desina	Internal	1100	<b>540825</b>	<b>JMDH-5/2-D-3-M12D-C</b>
	With dominant signal at 14	2-pin to VDMA	Internal	1100	<b>539081</b>	<b>JMDDH-5/2-D-3-M12-C</b>
		4-pin to Desina	Internal	1100	<b>540824</b>	<b>JMDDH-5/2-D-3-M12D-C</b>
<b>5/3-way valve</b>						
	Normally closed, mechanical spring reset method	2-pin to VDMA	Internal	1120	<b>539080</b>	<b>MDH-5/3G-D-3-M12-C</b>
		4-pin to Desina	Internal	1120	<b>540822</b>	<b>MDH-5/3G-D-3-M12D-C</b>
	Normally exhausted, mechanical spring reset method	2-pin to VDMA	Internal	1120	<b>533017</b>	<b>MDH-5/3E-D-3-M12-C</b>
		4-pin to Desina	Internal	1120	<b>540821</b>	<b>MDH-5/3E-D-3-M12D-C</b>
	Normally open, mechanical spring reset method	2-pin to VDMA	Internal	1120	<b>533007</b>	<b>MDH-5/3B-D-3-M12-C</b>
		4-pin to Desina	Internal	1120	<b>540823</b>	<b>MDH-5/3B-D-3-M12D-C</b>




## Standard valves to ISO 5599-1, square plug design A

FESTO

Technical data – Width 76 mm

-  - Flow rate  
Up to 6000 l/min

-  - Voltage  
24 V DC  
48 V AC



General technical data	
Design	Piston spool valve
Sealing principle	Soft
Actuation type	Electric
Type of control	Piloted
Direction of flow	Non-reversible
Exhaust function	With flow control
Manual override	Non-detenting
Type of mounting	On sub-base, with through-hole and screw
Mounting position	Any
Nominal size [mm]	18
Lap	Overlap
Width [mm]	76
Grid dimension [mm]	82
Pneumatic ports	Sub-base size 4 to ISO 5599-1
Noise level [dB (A)]	85
Conforms to standard	ISO 5599-1

Flow rates		
Valve function	5/2-way valve	5/3-way valve
Standard nominal flow rate [l/min]	6000	4800

Switching times [ms]				
		Switching time on	Switching time off	Switching time changeover
5/2-way valve	Single solenoid valve	120	160	–
	Double solenoid valve	–	–	40
5/3-way valve		85	290	–

# Standard valves to ISO 5599-1, square plug design A

FESTO

Technical data – Width 76 mm

Operating and environmental conditions			
Valve function		5/2-way single solenoid valve	5/2-way double solenoid valve   5/3-way valve
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[bar]	3 ... 16	2 ... 16   3 ... 16
Ambient temperature	[°C]	-10 ... +50	
Temperature of medium	[°C]	-10 ... +60	

Safety characteristics			
Type		MDH-...-D-4-24DC, JMDH-...-D-4-24DC	MDH-...-D-4, JMDH-...-D-4
Max. positive test pulse with 0 signal	[μs]	4300	-
Max. negative test pulse with 1 signal	[μs]	2100	-

Electrical data – MDH-...-24DC, JMDH-...-24DC					
		Direct voltage		Alternating voltage	
Electrical connection		To DIN EN 175301-803			
Characteristic coil data	Voltage	[V DC]	24		-
		[AC V]	-		48
	Frequency	[Hz]	-		50/60
	Power	[W]	6.8		-
	Pick-up power	[VA]	-		14.5
	Holding power	[VA]	-		9.9
Duty cycle	[%]	100			
Degree of protection to EN 60529		IP65			

Electrical data – Pilot valve MDH-3/2-...													
Type		MDH-3/2-24DC			MDH-3/2-24DC/42AC			MDH-3/2-110AC		MDH-3/2-230AC			
Electrical connection		Plug, square design to EN 175301-803, type A											
Characteristic coil data	Voltage	[V DC]	24	-	-	24	-	-	-	-	110	-	-
		[AC V]	-	48	53	-	42	42	110	110	-	230	230
	Frequency	[Hz]	-	50	60	-	50	60	50	60	-	50	60
	Power	[W]	6.8	-	-	8.4	-	-	-	-	6.3	-	-
	Pick-up power	[VA]	-	14.5	15	-	14	12	14.5	12	-	14.5	12
	Holding power	[VA]	-	9.9	9.3	-	10	7	10.5	7.6	-	10.5	7.6
Permissible voltage fluctuations		[%]	±10	±10	±10	±10	±10	±10	±10	±10	±10	±10	±10
Permissible frequency fluctuations		[%]	-	-	-	±10	±10	±10	±10	±10	±10	±10	±10
Duty cycle		[%]	100										
Degree of protection to EN 60529		IP65											



# Standard valves to ISO 5599-1, square plug design A

Technical data – Width 76 mm


## Materials

Sectional view MDH-5/2- ...

Sectional view JMDH-5/2- ...



Sectional view MDH-5/3...



1	Housing	Aluminium
-	Seals	NBR
-	Note on materials	RoHS-compliant

# Standard valves to ISO 5599-1, square plug design A


Technical data – Width 76 mm

FESTO

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)


### 5/2-way single solenoid valves



- 1 Port for plug socket with port pattern to EN 175301-803, type A  
→ page 121
- 2 Manual override
- 3 Captive mounting screws
- 4 Solenoid coil can be repositioned by 90° regardless of manual override

Type	B1	B2	D1	H1	H2	H3	H4	L1	L2	L3	L4	L5
MDH-5/2 ...	76	58	M8	139	110.5	74	14	182	67.5	80	40	81

### 5/2-way double solenoid valves, 5/3-way valves








- 1 Port for plug socket with port pattern to EN 175301-803, type A  
→ page 121
- 2 Manual override
- 3 Captive mounting screws
- 4 Solenoid coil can be repositioned by 90° regardless of manual override

Type	B1	B2	D1	H1	H2	H3	H4	L1	L2	L3	L4	L5
JMDH-5/2- ...	76	58	M8	139	110.5	74	14	182	135	80	40	162
MDH-5/3...									182			

# Standard valves to ISO 5599-1, square plug design A


Ordering data – Width 76 mm

Ordering data						
Circuit symbol	Description	Voltage	Pilot air supply	Weight [g]	Part No.	Type
<b>5/2-way single solenoid valve</b>						
	Pneumatic spring reset method	24 V DC	Internal	2600	<b>12457</b>	<b>MDH-5/2-3/4-D-4-24DC</b>
		–	Internal	2600	<b>14544</b>	<b>MDH-5/2-3/4-D-4<sup>1)</sup></b>
<b>5/2-way double solenoid valve</b>						
	–	24 V DC	Internal	2600	<b>12458</b>	<b>JMDH-5/2-3/4-D-4-24DC</b>
		–	Internal	2600	<b>14545</b>	<b>JMDH-5/2-3/4-D-4<sup>1)</sup></b>
<b>5/3-way valve</b>						
	Normally closed, mechanical spring reset method	24 V DC	Internal	2600	<b>12459</b>	<b>MDH-5/3G-3/4-D-4-24DC</b>
		–	Internal	2600	<b>14546</b>	<b>MDH-5/3G-3/4-D-4<sup>1)</sup></b>
	Normally exhausted, mechanical spring reset method	24 V DC	Internal	2600	<b>12460</b>	<b>MDH-5/3E-3/4-D-4-24DC</b>
		–	Internal	2600	<b>14547</b>	<b>MDH-5/3E-3/4-D-4<sup>1)</sup></b>
<b>Usable pilot valves</b>						
	Electrical connection to EN 175301-803 design A	24 V DC	–	140	<b>119600</b>	<b>MDH-3/2-24DC</b>
		24 V DC/ 42 V AC	–	140	<b>119603</b>	<b>MDH-3/2-24DC/42AC</b>
		110 V AC	–	140	<b>119601</b>	<b>MDH-3/2-110AC</b>
		110 V DC/ 230 V AC	–	140	<b>119602</b>	<b>MDH-3/2-230AC</b>

1) Without pilot valve. The part no. of the pilot valve must be added after the type code when ordering.  
Order example: 14546 MDH-5/3G-3/4-D-4-119602 (for MDH-3/2-230AC with part no. 119602)

# Standard valves to ISO 5599-1, pneumatic valves


Type codes



# Standard valves to ISO 5599-1, pneumatic valves

Peripherals overview

## Valve on individual sub-base




Individual components			
	Type	Description	→ Page/Internet
1	Push-in fitting	QS-...	For connecting O.D. tubing qs
2	Individual sub-base	NAS-...	Pneumatic ports, side 100
		NAU-...	Pneumatic ports, underneath 101
3	Silencer	U-...	For fitting in exhaust ports silencer
4	Pneumatic valve	VL-...	Port pattern to ISO 5599-1 81
		J-...	Port pattern to ISO 5599-1 81
		JD-...	Port pattern to ISO 5599-1 81

# Standard valves to ISO 5599-1, pneumatic valves

Peripherals overview



## Manifold assembly




Individual components			
	Type	Description	→ Page/Internet
1	NEV-...	For sealing the manifold sub-bases	103
2	QS-...	For connecting O.D. tubing	qs
3	NAW-...	For routing ports 2 and 4 to the front	102
4	NAV-...	With ports 2 and 4 underneath	102
5	NSC-...	For sealing ducts 1, 3, 5 between end plate and manifold sub-base, e.g. to create pressure zones	104
6	NZV-...	For connecting manifold sub-bases of different sizes	106
7	NAVW-...	With ports 2 and 4 either underneath or to the front	103
8	U-...	For fitting in exhaust ports	silencer
9	VL-...	Port pattern to ISO 5599-1	81
	J-...	Port pattern to ISO 5599-1	81
	JD-...	Port pattern to ISO 5599-1	81
10	NDV-...	For sealing unused manifold sub-bases	104
11	VABF-S1-...-F1B1-C	Controls the flow of exhaust air in ducts 3 and 5	107
	GRO-ZP-...	Controls the flow of exhaust air in ducts 3 and 5	107
12	VABF-S1-...-R...	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	114
	LR-ZP-...	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	114



# Standard valves to ISO 5599-1, pneumatic valves

Technical data – Width 42 mm

 Flow rate  
1200 l/min



General technical data		
Type	VL- ... -C, J ... -C	VL- ... -EX, J ... -EX
Design	Piston spool valve	Piston spool valve
Sealing principle	Soft	Soft
Actuation type	Pneumatic	Pneumatic
Type of control	Direct	Direct
Direction of flow	Reversible	Reversible
	VL-5/2-D-1-C: non-reversible	VL-5/2-D-1-C-EX: non-reversible
Exhaust function	With flow control	With flow control
Manual override	None	None
Type of mounting	On sub-base via through-hole	On sub-base via through-hole
Mounting position	Any	Any
Nominal size [mm]	8	8
Lap	Overlap	Overlap
Width [mm]	42	42
Grid dimension [mm]	43	43
Pneumatic ports	Sub-base size 1 to ISO 5599-1	Sub-base size 1 to ISO 5599-1
Noise level [dB (A)]	85	85
Conforms to standard	ISO 5599-1	ISO 5599-1
Certification	UL Recognised (OL)	–
Maritime classification <sup>1)</sup>	See certificate	–

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Flow rates		
Standard nominal flow rate	[l/min]	1200

Switching times [ms]					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way single solenoid valve	VL-5/2-D-1-C	9	18	–	–
	VL-5/2-D-1-C-EX	9	18	–	–
	VL-5/2-D-1-FR-C	6	23	–	–
	VL-5/2-D-1-FR-C-EX	6	23	–	–
5/2-way double solenoid valve	J-5/2-D-1-C	–	–	6	–
	J-5/2-D-1-C-EX	–	–	6	–
	JD-5/2-D-1-C	–	–	6	4
	JD-5/2-D-1-C-EX	–	–	6	4
5/3-way valve	VL-5/3G-D-1-C	7	44	–	–
	VL-5/3G-D-1-C-EX	7	44	–	–
	VL-5/3E-D-1-C	7	45	–	–
	VL-5/3E-D-1-C-EX	7	45	–	–
	VL-5/3B-D-1-C	7	44	–	–
	VL-5/3B-D-1-C-EX	7	44	–	–

# Standard valves to ISO 5599-1, pneumatic valves

Technical data – Width 42 mm


ATEX	
Type	VL- ... -EX, J ... -EX
ATEX category gas	II 2G
Ignition protection type for gas	Ex h IIC T4 Gb
ATEX category for dust	II 2D
Ignition protection type for dust	Ex h IIIC T130°C Db
Explosion-proof ambient temperature [°C]	-10 ≤ Ta ≤ +60
CE marking (see declaration of conformity)	As per EU Explosion Protection Directive (ATEX)

Operating and environmental conditions				
Valve function	5/2-way valve			5/3-way valve
	Single solenoid valve		Double solenoid valve	
	Pneumatic spring	Mechanical spring		
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]			
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]			
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)			
Operating pressure [bar]	2 ... 16	-0.9 ... +16	-0.9 ... +16	-0.9 ... +16
Pilot pressure [bar]	2 ... 16	3 ... 16	2 ... 16	3 ... 16
Ambient temperature [°C]	-10 ... +60			
Temperature of medium [°C]	-10 ... +60			

Safety characteristics	
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6

## Materials

Sectional view



1	Housing	Die-cast aluminium
-	Seals	HNBR, NBR
-	Note on materials	RoHS-compliant


# Standard valves to ISO 5599-1, pneumatic valves

Technical data – Width 42 mm

## Dimensions


Download CAD data → [www.festo.com](http://www.festo.com)

5/2-way valves, pneumatic spring reset method, 5/2-way double solenoid valves



Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/2- ...	42	28	6	M5	38	9	46.5	87.6	43.8	36	18
J-5/2- ...											
JD-5/2- ...											

5/2-way valves, mechanical spring reset method



Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/2- ... -FR- ...	42	28	6	M5	38	9	46.5	98	43.8	36	18


# Standard valves to ISO 5599-1, pneumatic valves

Technical data – Width 42 mm

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)








5/3-way valves



Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/3...	42	28	6	M5	38	9	46.5	108.4	54.2	36	18

# Standard valves to ISO 5599-1, pneumatic valves

Technical data – Width 42 mm

Ordering data					
Circuit symbol	Description		Weight [g]	Part No.	Type
<b>5/2-way single solenoid valve</b>					
	Pneumatic spring reset method	–	290	<b>151009</b>	<b>VL-5/2-D-1-C</b>
		ATEX category ➔ page 82	290	<b>536007</b>	<b>VL-5/2-D-1-C-EX</b>
	Mechanical spring reset method	–	290	<b>151014</b>	<b>VL-5/2-D-1-FR-C</b>
		ATEX category ➔ page 82	290	<b>536010</b>	<b>VL-5/2-D-1-FR-C-EX</b>
<b>5/2-way double solenoid valve</b>					
	–	–	290	<b>151007</b>	<b>J-5/2-D-1-C</b>
		ATEX category ➔ page 82	290	<b>536013</b>	<b>J-5/2-D-1-C-EX</b>
	With dominant signal at 14	–	290	<b>151008</b>	<b>JD-5/2-D-1-C</b>
		ATEX category ➔ page 82	290	<b>536016</b>	<b>JD-5/2-D-1-C-EX</b>
<b>5/3-way valve</b>					
	Normally closed Mechanical spring reset method	–	320	<b>151010</b>	<b>VL-5/3G-D-1-C</b>
		ATEX category ➔ page 82	320	<b>536019</b>	<b>VL-5/3G-D-1-C-EX</b>
	Normally exhausted Mechanical spring reset method	–	320	<b>151011</b>	<b>VL-5/3E-D-1-C</b>
		ATEX category ➔ page 82	320	<b>536022</b>	<b>VL-5/3E-D-1-C-EX</b>
	Normally pressurised Mechanical spring reset method	–	320	<b>151012</b>	<b>VL-5/3B-D-1-C</b>
		ATEX category ➔ page 82	320	<b>536025</b>	<b>VL-5/3B-D-1-C-EX</b>

# Standard valves to ISO 5599-1, pneumatic valves

Technical data – Width 52 mm

Flow rate  
2300 l/min



General technical data		
Type	VL- ... -C, J ... -C	VL- ... -EX, J ... -EX
Design	Piston spool valve	Piston spool valve
Sealing principle	Soft	Soft
Actuation type	Pneumatic	Pneumatic
Type of control	Direct	Direct
Direction of flow	Reversible	Reversible
	VL-5/2-D-2-C: non-reversible	VL-5/2-D-2-C-EX: non-reversible
Exhaust function	With flow control	With flow control
Manual override	None	None
Type of mounting	On sub-base, with through-hole and screw	On sub-base, with through-hole and screw
Mounting position	Any	Any
Nominal size [mm]	11.5	11.5
Lap	Overlap	Overlap
Width [mm]	52	52
Grid dimension [mm]	56	56
Pneumatic ports	Sub-base size 2 to ISO 5599-1	Sub-base size 2 to ISO 5599-1
Noise level [dB (A)]	85	85
Conforms to standard	ISO 5599-1	ISO 5599-1
Certification	UL Recognised (OL)	–
Maritime classification <sup>1)</sup>	See certificate	–

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Flow rates		
Standard nominal flow rate	[l/min]	2300

Switching times [ms]					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way single solenoid valve	VL-5/2-D-2-C	23	39	–	–
	VL-5/2-D-2-C-EX	23	39	–	–
	VL-5/2-D-2-FR-C	11	39	–	–
	VL-5/2-D-2-FR-C-EX	11	39	–	–
5/2-way double solenoid valve	J-5/2-D-2-C	–	–	8	–
	J-5/2-D-2-C-EX	–	–	8	–
	JD-5/2-D-2-C	–	–	8	8
	JD-5/2-D-2-C-EX	–	–	8	8
5/3-way valve	VL-5/3G-D-2-C	15	56	–	–
	VL-5/3G-D-2-C-EX	15	56	–	–
	VL-5/3E-D-2-C	16	59	–	–
	VL-5/3E-D-2-C-EX	16	59	–	–
	VL-5/3B-D-2-C	15	57	–	–
	VL-5/3B-D-2-C-EX	15	57	–	–

# Standard valves to ISO 5599-1, pneumatic valves

Technical data – Width 52 mm


ATEX	
Type	VL- ... -EX, J ... -EX
ATEX category gas	II 2G
Ignition protection type for gas	Ex h IIC T4 Gb
ATEX category for dust	II 2D
Ignition protection type for dust	Ex h IIIC T1 30°C Db
Explosion-proof ambient temperature [°C]	-10 ≤ Ta ≤ +60
CE marking (see declaration of conformity)	As per EU Explosion Protection Directive (ATEX)

Operating and environmental conditions					
Valve function	5/2-way valve			5/3-way valve	
	Monostable		Bistable		
	Pneumatic spring	Mechanical spring			
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]				
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]				
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)				
Operating pressure [bar]	2 ... 16	-0.9 ... +16	-0.9 ... +16	-0.9 ... +16	
Pilot pressure [bar]	2 ... 16	3 ... 16	2 ... 16	3 ... 16	
Ambient temperature [°C]	-10 ... +60				
Temperature of medium [°C]	-10 ... +60				

Safety characteristics	
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6

## Materials

Sectional view



1	Housing	Die-cast aluminium
-	Seals	HNBR, NBR
-	Note on materials	RoHS-compliant


# Standard valves to ISO 5599-1, pneumatic valves

Technical data – Width 52 mm

## Dimensions


Download CAD data → [www.festo.com](http://www.festo.com)

5/2-way valves, pneumatic spring reset method, 5/2-way double solenoid valves



Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/2- ...	54	38	9	M6	48	9.5	56.5	123.4	61.7	48	24
J-5/2- ...											
JD-5/2- ...											

5/2-way valves, mechanical spring reset method



Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/2- ... -FR- ...	54	38	9	M6	48	9.5	56.5	140.7	61.7	48	24




# Standard valves to ISO 5599-1, pneumatic valves

Technical data – Width 52 mm

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

5/3-way valves



Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/3...	54	38	9	M6	48	9.5	56.5	158	79	48	24


# Standard valves to ISO 5599-1, pneumatic valves

Technical data – Width 52 mm

Ordering data					
Circuit symbol	Description		Weight [g]	Part No.	Type
<b>5/2-way single solenoid valve</b>					
	Pneumatic spring reset method	–	550	<b>151845</b>	<b>VL-5/2-D-2-C</b>
		ATEX category → page 87	550	<b>536008</b>	<b>VL-5/2-D-2-C-EX</b>
	Mechanical spring reset method	–	550	<b>151844</b>	<b>VL-5/2-D-2-FR-C</b>
		ATEX category → page 87	550	<b>536011</b>	<b>VL-5/2-D-2-FR-C-EX</b>
<b>5/2-way double solenoid valve</b>					
	–	–	550	<b>151846</b>	<b>J-5/2-D-2-C</b>
		ATEX category → page 87	550	<b>536014</b>	<b>J-5/2-D-2-C-EX</b>
	With dominant signal at 14	–	550	<b>151847</b>	<b>JD-5/2-D-2-C</b>
		ATEX category → page 87	550	<b>536017</b>	<b>JD-5/2-D-2-C-EX</b>
<b>5/3-way valve</b>					
	Normally closed Mechanical spring reset method	–	825	<b>151848</b>	<b>VL-5/3G-D-2-C</b>
		ATEX category → page 87	825	<b>536020</b>	<b>VL-5/3G-D-2-C-EX</b>
	Normally exhausted Mechanical spring reset method	–	825	<b>151849</b>	<b>VL-5/3E-D-2-C</b>
		ATEX category → page 87	825	<b>536023</b>	<b>VL-5/3E-D-2-C-EX</b>
	Normally pressurised Mechanical spring reset method	–	825	<b>151850</b>	<b>VL-5/3B-D-2-C</b>
		ATEX category → page 87	825	<b>536026</b>	<b>VL-5/3B-D-2-C-EX</b>

# Standard valves to ISO 5599-1, pneumatic valves

Technical data – Width 65 mm

 Flow rate  
Up to 4600 l/min



General technical data		
Type	VL- ... -C, J ... -C	VL- ... -EX, J ... -EX
Design	Piston spool valve	Piston spool valve
Sealing principle	Soft	Soft
Actuation type	Pneumatic	Pneumatic
Type of control	Direct	Direct
Direction of flow	Reversible	Reversible
	VL-5/2-D-3-C: non-reversible	VL-5/2-D-3-C-EX: non-reversible
Exhaust function	With flow control	With flow control
Manual override	None	None
Type of mounting	On sub-base, with through-hole and screw	On sub-base, with through-hole and screw
Mounting position	Any	Any
Nominal size [mm]	14.5	14.5
Lap	Overlap	Overlap
Width [mm]	65	65
Grid dimension [mm]	71	71
Pneumatic ports	Sub-base size 3 to ISO 5599-1	Sub-base size 3 to ISO 5599-1
Noise level [dB (A)]	85	85
Conforms to standard	ISO 5599-1	ISO 5599-1
Certification	UL Recognised (OL)	–
Maritime classification <sup>1)</sup>	See certificate	–

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Flow rates				
Valve function	5/2-way valve	5/3-way valve		
		Normally closed	Normally exhausted	Normally pressurised
Standard nominal flow rate [l/min]	4500	4100	4600	4100

# Standard valves to ISO 5599-1, pneumatic valves

FESTO

Technical data – Width 65 mm

Switching times [ms]		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way single solenoid valve	VL-5/2-D-1-C	29	36	–	–
	VL-5/2-D-1-C-EX	29	36	–	–
	VL-5/2-D-1-FR-C	13	43	–	–
	VL-5/2-D-1-FR-C-EX	13	43	–	–
5/2-way double solenoid valve	J-5/2-D-1-C	–	–	8	–
	J-5/2-D-1-C-EX	–	–	8	–
	JD-5/2-D-1-C	–	–	8	8
	JD-5/2-D-1-C-EX	–	–	8	8
5/3-way valve	VL-5/3G-D-1-C	17	61	–	–
	VL-5/3G-D-1-C-EX	17	61	–	–
	VL-5/3E-D-1-C	18	63	–	–
	VL-5/3E-D-1-C-EX	18	63	–	–
	VL-5/3B-D-1-C	16	60	–	–
	VL-5/3B-D-1-C-EX	16	60	–	–

ATEX	
Type	VL- ... -EX, J ... -EX
ATEX category gas	II 2G
Ignition protection type for gas	Ex h IIC T4 Gb
ATEX category for dust	II 2D
Ignition protection type for dust	Ex h IIIC T1 30°C Db
Explosion-proof ambient temperature [°C]	–10 ≤ Ta ≤ +60
CE marking (see declaration of conformity)	As per EU Explosion Protection Directive (ATEX)

Operating and environmental conditions				
Valve function	5/2-way valve			5/3-way valve
	Monostable		Bistable	
	Pneumatic spring	Mechanical spring		
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]			
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]			
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)			
Operating pressure [bar]	2 ... 16	–0.9 ... +16	–0.9 ... +16	–0.9 ... +16
Pilot pressure [bar]	2 ... 16	3 ... 16	2 ... 16	3 ... 16
Ambient temperature [°C]	–10 ... +60			
Temperature of medium [°C]	–10 ... +60			


Safety characteristics	
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6

# Standard valves to ISO 5599-1, pneumatic valves

Technical data – Width 65 mm

## Materials

Sectional view




1	Housing	Die-cast aluminium
-	Seals	HNBR, NBR
-	Note on materials	RoHS-compliant

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

5/2-way valves, pneumatic spring reset method, 5/2-way double solenoid valves



- 3 Captive mounting screws
- 4 Slot for inscription label

Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/2- ...	65	48	12	M8	55	12	63.5	145.4	72.7	64	32
J-5/2- ...											
JD-5/2- ...											

# Standard valves to ISO 5599-1, pneumatic valves


Technical data – Width 65 mm



## Dimensions


Download CAD data → [www.festo.com](http://www.festo.com)

5/2-way valves, mechanical spring reset method



Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/2- ... -FR- ...	65	48	12	M8	55	12	63.5	164.7	72.7	64	32

5/3-way valves



Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/3...	65	48	12	M8	55	12	63.5	184	92	64	32


# Standard valves to ISO 5599-1, pneumatic valves

Technical data – Width 65 mm

Ordering data					
Circuit symbol	Description		Weight [g]	Part No.	Type
<b>5/2-way single solenoid valve</b>					
	Pneumatic spring reset method	–	810	<b>151864</b>	<b>VL-5/2-D-3-C</b>
		ATEX category → page 92	810	<b>536009</b>	<b>VL-5/2-D-3-C-EX</b>
	Mechanical spring reset method	–	810	<b>151863</b>	<b>VL-5/2-D-3-FR-C</b>
		ATEX category → page 92	810	<b>536012</b>	<b>VL-5/2-D-3-FR-C-EX</b>
<b>5/2-way double solenoid valve</b>					
	–	–	810	<b>151865</b>	<b>J-5/2-D-3-C</b>
		ATEX category → page 92	810	<b>536015</b>	<b>J-5/2-D-3-C-EX</b>
	With dominant signal at 14	–	810	<b>151866</b>	<b>JD-5/2-D-3-C</b>
		ATEX category → page 92	810	<b>536018</b>	<b>JD-5/2-D-3-C-EX</b>
<b>5/3-way valve</b>					
	Normally closed Mechanical spring reset method	–	910	<b>151867</b>	<b>VL-5/3G-D-3-C</b>
		ATEX category → page 92	910	<b>536021</b>	<b>VL-5/3G-D-3-C-EX</b>
	Normally exhausted Mechanical spring reset method	–	910	<b>151868</b>	<b>VL-5/3E-D-3-C</b>
		ATEX category → page 92	910	<b>536024</b>	<b>VL-5/3E-D-3-C-EX</b>
	Normally pressurised Mechanical spring reset method	–	910	<b>151869</b>	<b>VL-5/3B-D-3-C</b>
		ATEX category → page 92	910	<b>536027</b>	<b>VL-5/3B-D-3-C-EX</b>

# Standard valves to ISO 5599-1, pneumatic valves

Technical data – Width 76 mm

 Flow rate  
 Up to 6000 l/min



General technical data	
Design	Piston spool valve
Sealing principle	Soft
Actuation type	Pneumatic
Type of control	Direct
Direction of flow	Reversible
Exhaust function	With flow control
Manual override	None
Type of mounting	On sub-base, with through-hole and screw
Mounting position	Any
Nominal size [mm]	18
Lap	Overlap
Width [mm]	76
Grid dimension [mm]	82
Pneumatic ports	Sub-base size 4 to ISO 5599-1
Noise level [dB (A)]	85
Conforms to standard	ISO 5599-1

Flow rates			
Valve function		5/2-way valve	5/3-way valve
Standard nominal flow rate [l/min]		6000	4800

Switching times [ms]				
		Switching time on	Switching time off	Switching time changeover
5/2-way single solenoid valve	VL-5/2-3/4-D-4	25	90	–
5/2-way double solenoid valve	J-5/2-3/4-D-4	–	–	20
5/3-way valve	VL-5/3G-3/4-D-4	40	130	–
	VL-5/3E-3/4-D-4	50	170	–




# Standard valves to ISO 5599-1, pneumatic valves

Technical data – Width 76 mm

Operating and environmental conditions			
Valve function	5/2-way valve		5/3-way valve
	Monostable	Bistable	
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]		
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]		
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)		
Operating pressure	[bar]	-0.9 ... +16	-0.9 ... +16
Pilot pressure	[bar]	3 ... 16	2 ... 16
Ambient temperature	[°C]	-10 ... +60	
Temperature of medium	[°C]	-10 ... +60	

## Materials

Sectional view




1	Housing	Aluminium
-	Seals	NBR
-	Note on materials	RoHS-compliant

# Standard valves to ISO 5599-1, pneumatic valves

Technical data – Width 76 mm

Dimensions





Download CAD data → [www.festo.com](http://www.festo.com)



Type	B1	B2	D1	H3	H4	L2	L3	L4	L5
VL-5/2-3/4-D-4	76	58	M8	74	14	182	91	80	40
J-5/2-3/4-D-4									
VL-5/3E-3/4-D-4									
VL-5/3G-3/4-D-4									

# Standard valves to ISO 5599-1, pneumatic valves

Technical data – Width 76 mm

Ordering data				
Circuit symbol	Description	Weight [g]	Part No.	Type
<b>5/2-way single solenoid valve</b>				
	Mechanical spring reset method	1800	12461	VL-5/2-3/4-D-4
<b>5/2-way double solenoid valve</b>				
	–	1800	12462	J-5/2-3/4-D-4
<b>5/3-way valve</b>				
	Normally closed Mechanical spring reset method	2000	12463	VL-5/3G-3/4-D-4
	Normally exhausted Mechanical spring reset method	2000	12464	VL-5/3E-3/4-D-4

# Standard valves to ISO 5599-1, individual sub-base

FESTO

Accessories

## Individual sub-base NAS

Ports at side

Materials:

Width 42 mm, 52 mm, 65 mm:

Die-cast aluminium

Width 76 mm:

Anodised aluminium




General technical data	
Conforms to standard	ISO 5599-1
Type of mounting	2 through-holes in housing

Operating and environmental conditions				
Width	42 mm	52 mm	65 mm	76 mm
Note on materials	Free of copper and PTFE			-
Certification	UL Recognised (OL)			-

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



Width	B1	D1	D2	D3	H1	H2	H4	H5	H6	L1	L2	L3	L4	L5
42 mm	48	G1/4	G1/8	5.5	32	10	9	20.3	20.3	110	98	23	60	46
52 mm	57	G3/8	G1/8	6.6	40	13	9	25	25	124	112	27	71	54
65 mm	71	G1/2	G1/8	6.6	32	18	9	16	16	149	136	32	91	64
76 mm	85	G3/4	G1/8	9	42	19	9	21	21	186	170	42	111	84

Ordering data						
Designation to VDMA	Width	Pneumatic port		Weight [g]	Part No.	Type
		1, 2, 3, 4, 5	12, 14			
VDMA 24345-A-1	42 mm	G1/4	G1/8	190	★ 9484	NAS-1/4-1A-ISO
VDMA 24345-A-2	52 mm	G3/8	G1/8	300	11310	NAS-3/8-2A-ISO
VDMA 24345-A-3	65 mm	G1/2	G1/8	360	10336	NAS-1/2-3A-ISO
VDMA 24345-A-4	76 mm	G3/4	G1/8	1260	152813	NAS-3/4-4A-ISO

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Festo core product range

★ Generally ready for shipping ex works in 24 hours

☆ Generally ready for shipping ex works in 5 days

# Standard valves to ISO 5599-1, individual sub-base

Accessories

## Individual sub-base NAU

Ports underneath

Materials:

Width 42 mm, 52 mm, 65 mm:  
Die-cast aluminium

Width 76 mm:  
Anodised aluminium




General technical data	
Conforms to standard	ISO 5599-1
Type of mounting	2 through-holes in housing

Operating and environmental conditions				
Width	42 mm	52 mm	65 mm	76 mm
Note on materials	Free of copper and PTFE			-
Certification	UL Recognised (OL)		-	-

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



Width	B1	D1	D2	D3	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5
42 mm	46	G1/4	G1/8	5.5	30	10	5	7.5	20	110	98	23	60.7	46
52 mm	56	G3/8	G1/8	6.6	35	13	6.5	8.3	24	124	112	27	70	54
65 mm	71	G1/2	G1/8	6.6	32	18	9	10	30	149	136	33	90	66
76 mm	85	G3/4	G1/8	9	28	19	9.5	12	37	186	170	42	111	84

Ordering data							
Designation to VDMA	Width	Pneumatic port		Weight [g]	Part No.	Type	
		1, 2, 3, 4, 5	12, 14				
VDMA 24345-B-1	42 mm	G1/4	G1/8	280	★ 9485	NAU-1/4-1B-ISO	
VDMA 24345-B-2	52 mm	G3/8	G1/8	450	11416	NAU-3/8-2B-ISO	
VDMA 24345-B-3	65 mm	G1/2	G1/8	660	10337	NAU-1/2-3B-ISO	
VDMA 24345-B-4	76 mm	G3/4	G1/8	1080	152814	NAU-3/4-4B-ISO	

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ☆ Generally ready for shipping ex works in 5 days

# Standard valves to ISO 5599-1, manifold components

Accessories

## Manifold sub-base NAV

Ports underneath

Materials:

Width 42 mm, 52 mm, 65 mm:

Die-cast aluminium

Width 76 mm:

Anodised aluminium

Dimensions → page 105



General technical data	
Conforms to standard	ISO 5599-1

Operating and environmental conditions				
Width	42 mm	52 mm	65 mm	76 mm
Certification	–	UL Recognised (OL)	–	–

Ordering data						
Designation to VDMA	Width	Pneumatic port		Weight [g]	Part No.	Type
		2, 4	12, 14			
VDMA 24345-C-1	42 mm	G1/4	G1/8	240	★ 10173	NAV-1/4-1C-ISO
VDMA 24345-C-2	52 mm	G3/8	G1/8	400	11305	NAV-3/8-2C-ISO
VDMA 24345-C-3	65 mm	G1/2	G1/8	700	10175	NAV-1/2-3C-ISO
VDMA 24345-C-4	76 mm	G3/4	G1/8	1400	11139	NAV-3/4-4C-ISO

## 90° connection plate NAW

Ports at side and top

Materials:

Width 42 mm, 52 mm, 65 mm:

Die-cast aluminium

Width 76 mm:

Anodised aluminium

Dimensions → page 105



General technical data	
Conforms to standard	ISO 5599-1

Operating and environmental conditions				
Width	42 mm	52 mm	65 mm	76 mm
Note on materials	Free of copper and PTFE	–	–	–

Ordering data						
Designation to VDMA	Width	Pneumatic port		Weight [g]	Part No.	Type
		2, 4	12, 14			
VDMA 24345-E-1	42 mm	G1/4	G1/8	360	11304	NAW-1/4-1E-ISO
VDMA 24345-E-2	52 mm	G3/8	G1/8	600	11307	NAW-3/8-2E-ISO
VDMA 24345-E-3	65 mm	G1/2	G1/8	920	11309	NAW-1/2-3E-ISO
VDMA 24345-E-4	76 mm	G3/4	G1/8	1550	11141	NAW-3/4-4E-ISO

– Note: This product conforms to ISO 1179-1 and to ISO 228-1

Festo core product range	★ Generally ready for shipping ex works in 24 hours
	☆ Generally ready for shipping ex works in 5 days

# Standard valves to ISO 5599-1, manifold components

Accessories

## Manifold sub-base with 90° connections NAVW

Ports at side and underneath

Materials:

Die-cast aluminium

Dimensions → page 105



General technical data	
Conforms to standard	ISO 5599-1

Operating and environmental conditions	
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]

Ordering data					
Width	Pneumatic port		Weight [g]	Part No.	Type
	2, 4	12, 14			
42 mm	G1/4	G1/8	320	152789	NAVW-1/4-1-ISO
52 mm	G3/8	G1/8	550	152790	NAVW-3/8-2-ISO
65 mm	G1/2	G1/8	1020	152791	NAVW-1/2-3-ISO

## End plate kit NEV

Materials:

Width 42 mm, 52 mm, 65 mm:

Die-cast aluminium

Width 76 mm:

Anodised aluminium

Dimensions → page 105



General technical data	
Conforms to standard	ISO 5599-1

Operating and environmental conditions				
Width	42 mm	52 mm	65 mm	76 mm
Note on materials	Free of copper and PTFE			-

Ordering data					
Designation to VDMA	Width	Pneumatic port	Weight [g]	Part No.	Type
		1, 3, 5			
VDMA 24345-D-1	42 mm	G3/8	280	★ 10174	NEV-1DA/DB-ISO
VDMA 24345-D-2	52 mm	G1/2	450	11306	NEV-2DA/DB-ISO
VDMA 24345-D-3	65 mm	G1	760	10176	NEV-3DA/DB-ISO
VDMA 24345-D-4	76 mm	G1	1390	11140	NEV-4DA/DB-ISO

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Festo core product range

★ Generally ready for shipping ex works in 24 hours

☆ Generally ready for shipping ex works in 5 days

# Standard valves to ISO 5599-1, manifold components

Accessories

## Blanking plate NDV

Materials:  
Width 42 mm, 52 mm, 65 mm:  
Steel

Width 76 mm:  
Wrought aluminium alloy

Dimensions → page 105



General technical data	
Conforms to standard	ISO 5599-1

Operating and environmental conditions	
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)

Ordering data			
Width	Weight [g]	Part No.	Type
42 mm	113	★ 9489	NDV-1-ISO
52 mm	166	11308	NDV-2-ISO
65 mm	314	10340	NDV-3-ISO
76 mm	1480	11142	NDV-4-ISO

## Isolating disc NSC

Materials:  
Die-cast aluminium

Dimensions → page 105



General technical data	
Conforms to standard	ISO 5599-1

Operating and environmental conditions				
Width	42 mm	52 mm	65 mm	76 mm
Note on materials	Free of copper and PTFE			-

Ordering data				
Width	Pneumatic port	Weight [g]	Part No.	Type
42 mm	G1/4	6	★ 11550	NSC-1/4-1-ISO
52 mm	G3/8	9.2	11908	NSC-3/8-2-ISO
65 mm	G1/2	20	11551	NSC-1/2-3-ISO
76 mm	G3/4	24	11699	NSC-3/4-4-ISO

Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ☆ Generally ready for shipping ex works in 5 days




# Standard valves to ISO 5599-1, manifold components

Accessories

## Dimensions – Manifold assembly

Download CAD data → [www.festo.com](http://www.festo.com)



- 1 Left-hand end plate, end plate kit NEV
- 2 Manifold sub-base NAV
- 3 Blanking plate NDV
- 4 Right-hand end plate, end plate kit NEV
- 5 90° connection plate NAW
- 6 Port pattern to ISO 5599-1
- 7 Manifold sub-base with 90° connections NAVW
- 8 Isolating disc NSC

Width	B1	B2	B3	B4	B5	B6	B7	B8	B9	D1	D2	D3	D4	D5	D6
42 mm	43	22	42	40	11	7.5	1.5	4	21.6	G1/4	G3/8	G1/8	10	5.5	7
52 mm	56	26	55	50	13	6	5	6	27	G3/8	G1/2	G1/8	11	6.6	9
65 mm	71	30	70	70	15	8	6	6	35.5	G1/2	G1	G1/8	15	9	12
76 mm	82	30	80	80	15	9	8	-	-	G3/4	G1	G1/8	15	9	12

Width	H1	H2	H3	H4	H5	H6	H7	L1	L2	L3	L4	L5	L6	L7	T1
42 mm	81	46	44	50.5	12.5	37	5	110	95	80	28	26	11	11	5.7
52 mm	85	47	45	60	15	40	5	135	115	96	35	30	15	14	6.8
65 mm	99	56	54	66	17.5	45	5	190	168	120	52	38	19	19	9
76 mm	120	58	55	-	-	65	5	215	184	-	56	52	-	-	9

— Note: This product conforms to ISO 1179-1 and to ISO 228-1

# Standard valves to ISO 5599-1, manifold components




Accessories

## Intermediate plate NZV



For connecting manifold sub-bases of different sizes

Materials:  
Die-cast aluminium, anodised



General technical data	
Based on standard	ISO 5599-1
Note on materials	Free of copper and PTFE

## Dimensions Download CAD data → [www.festo.com](http://www.festo.com)




Type	B1	B2	B3	B4	D1	D2	D3	D4	H1	H2	L1	L2	L3	L4	L5	T1	T2
NZV-1-2	47	24	23	-	M6	M5	7	-	25	7.5	135	115	95	30	-	13	12
NZV-3-2/1	56	25	24	22	M6	M5	12	9	30	15	190	168	115	52	95	12	10

Ordering data		Weight [g]	Part No.	Type
For manifold sub-bases of width 42 mm, 52 mm		393	<b>164940</b>	<b>NZV-1-2</b>
For manifold sub-bases of width 42 mm and 65 mm or 52 mm and 65 mm		473	<b>12911</b>	<b>NZV-3-2/1</b>

# Standard valves to ISO 5599-1, flow control plate

Accessories

Function



Exhaust air flow control valve for 3 and 5.



General technical data			
Type	VABF-S1-1-F1B1-C	VABF-S1-2-F1B1-C	GRO-ZP-3-ISO
Based on standard	ISO 5599-1		
Pneumatic vertical stacking	Flow control plate, exhaust air flow control		
Mounting position	Any		
Type of mounting	Via through-hole		
Standard nominal flow rate [l/min]	1100	–	1500
Degree of protection	IP65	IP65	–
	NEMA4	NEMA4	–

Materials	
Housing	Die-cast aluminium
Note on materials	RoHS-compliant

Operating and environmental conditions			
Type	VABF-S1-1-F1B1-C	VABF-S1-2-F1B1-C	GRO-ZP-3-ISO
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]		Compressed air to ISO 8573-1:2010 [7:--:--]
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)		Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure [bar]	–0.9 ... +10	–0.9 ... +10	0 ... +16
Supply pressure 1 [bar]	–	+0.5 ... +10	–
Ambient temperature [°C]	–5 ... +50	–5 ... +50	–20 ... +80
Temperature of medium [°C]	–	–	–20 ... +80


# Standard valves to ISO 5599-1, flow control plate

Accessories

FESTO


## Standard nominal flow rate $q_{nN}$ as a function of the turns $n$ of the regulating screw

VABF-S1-1-F1B1-C




— Flow control screw from 2 → 3  
 - - - Flow control screw from 4 → 5

VABF-S1-2-F1B1-C



— Flow control screw from 2 → 3  
 - - - Flow control screw from 4 → 5

## GRO-ZP-3-ISO




# Standard valves to ISO 5599-1, flow control plate

Accessories

## Dimensions


Download CAD data → [www.festo.com](http://www.festo.com)

VABF-S1-...



- 1 Captive mounting screws
- 2 Port pattern to ISO 5599-1

GRO-ZP-3-ISO



- 1 Regulating screw for flow control valve
- 2 Captive mounting screws

Type	Width	B1	B2	B3	D1	H1	H2	H3	H4	L1	L2	L3	L5	L6	T1
VABF-S1-1-F1B1-C	42 mm	39.9	24.3	16.1	9.3	17.5	9.2	-	28	105.3	-	-	-	32	7.3
VABF-S1-2-F1B1-C	52 mm	52	32.5	22.5	13.4	29.5	13.5	-	45	131	-	-	-	40.9	10
GRO-ZP-3-ISO	65 mm	70	48	-	M8	33	12	16.5	-	132	64	32	7	-	-


## Ordering data

Circuit symbol	Description	Width	Weight [g]	Part No.	Type
	Exhaust air flow control valve	42 mm	220	549102	VABF-S1-1-F1B1-C
		52 mm	565	555788	VABF-S1-2-F1B1-C
		65 mm	850	119674	GRO-ZP-3-ISO

# Standard valves to ISO 5599-1, vertical supply plate

Accessories

Function



Alternative compressed air supply for port 1 of the assembled valve.



General technical data		
Type	VABF-S1-1-P1A3-G38	VABF-S1-2-P1A3-G12
Based on standard	ISO 5599-1	
Pneumatic vertical stacking	Alternative compressed air supply for 1	
Mounting position	Any	
Type of mounting	On individual sub-base, on manifold sub-base	
Standard nominal flow rate [l/min]	1300	2800
Pneumatic port 1	G3/8	G1/2
Degree of protection	IP65 NEMA4	IP65 NEMA4

Materials	
Housing	Die-cast aluminium
Note on materials	RoHS-compliant


Operating and environmental conditions		
Type	VABF-S1-1-P1A3-G38	VABF-S1-2-P1A3-G12
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure [bar]	-0.9 ... +10	-0.9 ... +10
Supply pressure 1 [bar]	-	+0.5 ... +10
Ambient temperature [°C]	-5 ... +50	-5 ... +50

# Standard valves to ISO 5599-1, vertical supply plate

Accessories

## Dimensions

Download CAD data → [www.festo.com/en/engineering](http://www.festo.com/en/engineering)



- 1 Captive screws
- 2 Port pattern to ISO 5599-1

Type	B1	B2	D1	H1	H4	L1	L6	T1
VABF-S1-1-P1A3-G38	42.1	24.2	G3/8	32.7	45.3	117.6	35.8	7.9
VABF-S1-2-P1A3-G12	54	31	G1/2	42.4	58.9	136	38	10


## Ordering data

Circuit symbol	Description	Width	Standard nominal flow rate [l/min]	Weight [g]	Part No.	Type
	Vertical supply plate	42 mm	1300	340	<b>549100</b>	<b>VABF-S1-1-P1A3-G38</b>
		52 mm	2800	605	<b>555785</b>	<b>VABF-S1-2-P1A3-G12</b>

# Standard valves to ISO 5599-1, vertical pressure shut-off plate

Accessories

Function



Vertical pressure shut-off plate for blocking duct 1 and duct 14 upstream of a valve.



General technical data		
Type	VABF-S1-1-L1D1-C	VABF-S1-2-L1D1-C
Based on standard	ISO 5599-1	
Pneumatic vertical stacking	Shut-off for 1	Alternative compressed air supply for 1
Mounting position	Any	
Type of mounting	On individual sub-base, on manifold sub-base	
Standard nominal flow rate [l/min]	1200	1950
Pneumatic port 1	G3/8	G1/2
Degree of protection	IP65	IP65
	NEMA4	NEMA4

Materials	
Housing	Die-cast aluminium
Note on materials	RoHS-compliant

Operating and environmental conditions		
Type	VABF-S1-1-L1D1-C	VABF-S1-2-L1D1-C
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure [bar]	-0.9 ... +10	-0.9 ... +10
Supply pressure 1 [bar]	-	+0.5 ... +10
Ambient temperature [°C]	-5 ... +50	-5 ... +50




# Standard valves to ISO 5599-1, vertical pressure shut-off plate

Accessories

## Dimensions

Download CAD data → [www.festo.com/en/engineering](http://www.festo.com/en/engineering)



- 1 Captive screws
- 2 Port pattern to ISO 5599-1

Type	B1	B2	D1	H1	H2	H4	L1	L6	T1
VABF-S1-1-L1D1-C	42.1	26.7	12.8	15.6	1.6	45.3	173.8	92	7.9
VABF-S1-2-L1D1-C	54	32.6	14	21.3	1.6	58.7	191.2	93.2	10


## Ordering data

Circuit symbol	Description	Width	Standard nominal flow rate [l/min]	Weight [g]	Part No.	Type
	Vertical pressure shut-off plate	42 mm	1200	600	<b>549103</b>	<b>VABF-S1-1-L1D1-C</b>
		52 mm	1950	1030	<b>555790</b>	<b>VABF-S1-2-L1D1-C</b>


# Standard valves to ISO 5599-1, pressure regulator

Accessories

Function



The pressure regulator enables the manual setting of a particular pressure in the regulated port upstream or downstream of the valve.



General technical data			
Type	VABF-S1-1-R...	VABF-S1-2-R...	LR-ZP-...-3
Width [mm]	42	52	65
Based on standard	ISO 5599-1	ISO 5599-1	ISO 5599-1
Pneumatic vertical stacking	Pressure regulator	Pressure regulator	Pressure regulator
Design	-	-	Piston
Regulator function	Output pressure constant	Output pressure constant	-
	With secondary venting	With secondary venting	-
Mounting position	Any	Any	-
Type of mounting	On individual sub-base	On individual sub-base	-
	On manifold sub-base	On manifold sub-base	-
Optional pressure gauge	Possible	Possible	-
Pressure gauge connection	With retaining clamp	With retaining clamp	-
Degree of protection	IP65	IP65	-
	NEMA4	NEMA4	-

Materials			
Type	VABF-S1-1-R...	VABF-S1-2-R...	LR-ZP-...-3
Regulator housing	Die-cast aluminium	Die-cast aluminium	Die-cast aluminium, steel
Control section	PA	PA	-
Seals	-	-	NBR
Note on materials	RoHS-compliant	RoHS-compliant	RoHS-compliant
	PWIS-free	PWIS-free	Contains PWIS (paint-wetting impairment substances)

Operating and environmental conditions			
Type	VABF-S1-1-R...	VABF-S1-2-R...	LR-ZP-...-3
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]		-
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)		-
Supply pressure 1 [bar]	+0.5 ... +10	+0.5 ... +10	Max. 14
Ambient temperature [°C]	-5 ... +50	-5 ... +50	-
Certification	-	-	UL Recognised (OL)

Product weight			
Type	VABF-S1-1-R...	VABF-S1-2-R...	LR-ZP-...-3
Regulated port	1	640 g	1190 g
	2	640 g	1230 g
	4	640 g	1230 g
	2 and 4	920 g	1990 g


# Standard valves to ISO 5599-1, pressure regulator

Accessories

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

VABF-S1-1-..., VABF-S1-2-...



Type	B1	B2	H1	H2	H3	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10	T1
Regulator plate, width 42 mm																
VABF-S1-1-R1...	42.1	23.6	115	112	87.1	-	207.1	-	125.3	-	-	49.4	36	27	9	7.9
VABF-S1-1-R2...						-	-	216.2	125.3	-	-					
VABF-S1-1-R3...						-	-	-	125.3	150.3	216.1					
VABF-S1-1-R4...						311.6	-	-	-	-	-					
VABF-S1-1-R5...						311.6	-	-	-	-	-					
VABF-S1-1-R6...						-	-	216.2	125.3	-	-					
VABF-S1-1-R7...						-	-	-	125.3	150.3	216.1					
Regulator plate, width 52 mm																
VABF-S1-2-R1...	54	23.6	182	167	94.4	-	250.2	-	152.2	-	-	49.4	48	38	12	10
VABF-S1-2-R2...						-	-	264.2	152.2	-	-					
VABF-S1-2-R3...						-	-	-	152.2	180.2	264.2					
VABF-S1-2-R4...						380.4	-	-	-	-	-					
VABF-S1-2-R5...						380.4	-	-	-	-	-					
VABF-S1-2-R6...						-	-	264.2	152.2	-	-					
VABF-S1-2-R7...						-	-	-	152.2	180.2	264.2					

# Standard valves to ISO 5599-1, pressure regulator


Accessories

FESTO

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

LR-ZP-...-3





- 1 Pressure gauge connection G1/8
- 2 Regulating screw
- 3 Port pattern to ISO 5599-1
- 4 Captive mounting screws
- 5 Rotary knob

Type	B	H	H1	H2	L1	L2	L3	L4	L5	L6	L7	L8
Regulator plate, width 65 mm												
LR-ZP-P-D-3	70	63	65	14	201.5	-	274	-	-	-	119	-
LR-ZP-B-D-3					201.5	-	-	-	274	72.5	-	119
LR-ZP-A-D-3					201.5	-	-	403	-	-	119	119
LR-ZP-A/B-D-3					201.5	260	-	-	-	-	119	-

## Flow rate qn as a function of output pressure p2

LR-ZP-A-D-3, LR-ZP-B-D-3, LR-ZP-A/B-D-3

LR-ZP-P-D-3



# Standard valves to ISO 5599-1, pressure regulator

Accessories

Ordering data					
	Regulated port	Regulator	Control range	Part No.	Type
Regulator plate, width 42 mm					
	1	P	0.5 ... 6 bar	546817	VABF-S1-1-R1C2-C-6
			0.5 ... 10 bar	546818	VABF-S1-1-R1C2-C-10
	2	B	1 ... 6 bar	546821	VABF-S1-1-R2C2-C-6
			1 ... 10 bar	546822	VABF-S1-1-R2C2-C-10
	2, reversible	B	0.5 ... 6 bar	546827	VABF-S1-1-R6C2-C-6
			0.5 ... 10 bar	546828	VABF-S1-1-R6C2-C-10
	4	A	1 ... 6 bar	546819	VABF-S1-1-R3C2-C-6
			1 ... 10 bar	546820	VABF-S1-1-R3C2-C-10
	4, reversible	A	0.5 ... 6 bar	546829	VABF-S1-1-R7C2-C-6
			0.5 ... 10 bar	546830	VABF-S1-1-R7C2-C-10
	2 and 4	AB	1 ... 6 bar	546823	VABF-S1-1-R4C2-C-6
			1 ... 10 bar	546824	VABF-S1-1-R4C2-C-10
	2 and 4, reversible	AB	0.5 ... 6 bar	546825	VABF-S1-1-R5C2-C-6
			0.5 ... 10 bar	546826	VABF-S1-1-R5C2-C-10





# Standard valves to ISO 5599-1, pressure regulator

Accessories

Ordering data					
	Regulated port	Regulator	Control range	Part No.	Type
Regulator plate, width 52 mm					
	1	P	0.5 ... 6 bar	555757	VABF-S1-2-R1C2-C-6
			0.5 ... 10 bar	555758	VABF-S1-2-R1C2-C-10
	2	B	1 ... 6 bar	555759	VABF-S1-2-R2C2-C-6
			1 ... 10 bar	555760	VABF-S1-2-R2C2-C-10
	2, reversible	B	0.5 ... 6 bar	555767	VABF-S1-2-R6C2-C-6
			0.5 ... 10 bar	555768	VABF-S1-2-R6C2-C-10
	4	A	1 ... 6 bar	555761	VABF-S1-2-R3C2-C-6
			1 ... 10 bar	555762	VABF-S1-2-R3C2-C-10
	4, reversible	A	0.5 ... 6 bar	555769	VABF-S1-2-R7C2-C-6
			0.5 ... 10 bar	555770	VABF-S1-2-R7C2-C-10
	2 and 4	AB	1 ... 6 bar	555763	VABF-S1-2-R4C2-C-6
			1 ... 10 bar	555764	VABF-S1-2-R4C2-C-10
	2 and 4, reversible	AB	0.5 ... 6 bar	555765	VABF-S1-2-R5C2-C-6
			0.5 ... 10 bar	555766	VABF-S1-2-R5C2-C-10

# Standard valves to ISO 5599-1, pressure regulator

Accessories

Ordering data					
	Regulated port	Regulator	Control range	Part No.	Type
Regulator plate, width 65 mm					
	1	P	0 ... 12 bar	35968	LR-ZP-P-D-3
	2	B	0 ... 12 bar	35426	LR-ZP-B-D-3
	4	A	0 ... 12 bar	35971	LR-ZP-A-D-3
	2, 4	AB	0.5 ... 12 bar	35429	LR-ZP-A/B-D-3





Ordering data – Accessories				
	Width	Weight [g]	Part No.	Type
Pressure gauge for intermediate pressure regulator plates LR-ZP	65 mm	64.5	345395	MA-40-16-1/8

· || · Note: This product conforms to ISO 1179-1 and to ISO 228-1

# Standard valves to ISO 5599-1

Accessories

**FESTO**









Ordering data					
	Description	Voltage	Cable length [m]	Part No.	Type
<b>Solenoid coil MSF</b>					
	Solenoid coil	12 V DC	–	<b>34410</b>	<b>MSFG-12-OD</b>
		24 V DC and 42 V AC, 50 ... 60 Hz	–	<b>34411</b>	<b>MSFG-24/42-50/60-OD</b>
		42 V DC	–	<b>34413</b>	<b>MSFG-42-OD</b>
		24 V AC	–	<b>34415</b>	<b>MSFG-24-50/60-OD</b>
		48 V AC, 50 ... 60 Hz	–	<b>34418</b>	<b>MSFW-48-50/60-OD</b>
		110 V AC, 50 ... 60 Hz and 120 V AC, 60 Hz	–	<b>34420</b>	<b>MSFW-110-50/60-OD</b>
		230 V AC, 50 ... 60 Hz and 240 V AC, 60 Hz	–	<b>34422</b>	<b>MSFW-230-50/60-OD</b>
		240 V AC, 50 ... 60 Hz	–	<b>34424</b>	<b>MSFW-240-50/60-OD</b>
	Solenoid coil with socket MSSD	12 V DC	–	<b>4526</b>	<b>MSFG-12</b>
		24 V DC and 42 V AC, 50 ... 60 Hz	–	<b>4527</b>	<b>MSFG-24/42-50/60</b>
		24 V AC	–	<b>4534</b>	<b>MSFW-24-50/60</b>
		110 V AC, 50 ... 60 Hz and 120 V AC, 60 Hz	–	<b>6720</b>	<b>MSFW-110-50/60</b>
		230 V AC, 50 ... 60 Hz and 240 V AC, 60 Hz	–	<b>4540</b>	<b>MSFW-230-50/60</b>
	Solenoid coil for ATEX environment	24 V DC	1	<b>8059804</b>	<b>VACF-B-K1-1-1-EX4-M</b>
			5	<b>8059805</b>	<b>VACF-B-K1-1-5-EX4-M</b>
		24 V AC, 50 ... 60 Hz	1	<b>8059808</b>	<b>VACF-B-K1-1A-1-EX4-M</b>
			5	<b>8059812</b>	<b>VACF-B-K1-16B-5-EX4-M</b>
		110 V AC, 50 ... 60 Hz	1	<b>8059811</b>	<b>VACF-B-K1-16B-1-EX4-M</b>
			5	<b>8059812</b>	<b>VACF-B-K1-16B-5-EX4-M</b>
		230 V AC, 50 ... 60 Hz	1	<b>8059809</b>	<b>VACF-B-K1-3A-1-EX4-M</b>
5	<b>8059810</b>		<b>VACF-B-K1-3A-5-EX4-M</b>		
<b>Solenoid coil MSN1</b>					
	Solenoid coil	24 V DC	–	<b>123060</b>	<b>MSN1G-24DC-OD</b>
		12 V DC and 24 V AC, 50 ... 60 Hz	–	<b>170152</b>	<b>MSN1W-24AC/12DC</b>
		110 V AC, 50 ... 60 Hz	–	<b>123061</b>	<b>MSN1W-110AC-OD</b>
		230 V AC, 50 ... 60 Hz	–	<b>123062</b>	<b>MSN1W-230AC-OD</b>



# Standard valves to ISO 5599-1

Accessories













FESTO

Ordering data						
	Description			Cable length [m]	Part No.	Type
<b>Electrical accessories for solenoid coil MSF</b>						
	Angled socket	Screw terminal	Cable conduit fitting Pg9	–	<b>34431</b>	<b>MSSD-F</b>
			Cable conduit fitting M16	–	<b>59710</b>	<b>MSSD-F-M16</b>
		Insulation displacement connection	Cable conduit fitting M16	–	<b>192746</b>	<b>MSSD-F-S-M16</b>
	PUR cable coating, connection technology M12x1, A-coded	24 AC/DC	• Signal status display • Protective circuit	0.3	<b>3679773</b>	<b>NEBV-B2W3F-P-K-0.3-N-M12W3</b>
				0.6	<b>3679774</b>	<b>NEBV-B2W3F-P-K-0.6-N-M12W3</b>
		110 AC/DC	–	0.3	<b>3579463</b>	<b>NEBV-B2W3-K-0.3-N-M12W3</b>
				0.6	<b>3579464</b>	<b>NEBV-B2W3-K-0.6-N-M12W3</b>
	PUR cable coating	24 AC/DC	• Signal status display • Protective circuit	0.6	<b>3679778</b>	<b>NEBV-B2W3F-P-K-0.6-N-LE3</b>
				230 AC/DC	–	0.6
	PVC cable coating	24 V DC	Signal status display	2.5	<b>30935</b>	<b>KMF-1-24DC-2,5-LED</b>
				5	<b>30937</b>	<b>KMF-1-24DC-5-LED</b>
				10	<b>193458</b>	<b>KMF-1-24DC-10-LED</b>
				230 V AC	–	2.5
			5	<b>30938</b>	<b>KMF-1-230AC-5</b>	
	Illuminating seal	12 ... 24 V DC	Signal status display	–	<b>19143</b>	<b>MF-LD-12-24DC</b>
		230 V DC/V AC	Signal status display	–	<b>19144</b>	<b>MF-LD-230AC</b>
<b>Electrical accessories for solenoid coil MSN1 and MD</b>						
	Angled socket	Screw terminal	Cable conduit fitting Pg9	–	<b>34583</b>	<b>MSSD-C</b>
			Cable conduit fitting M16	–	<b>539709</b>	<b>MSSD-C-M16</b>
		Insulation displacement connection	Cable conduit fitting M16	–	<b>192748</b>	<b>MSSD-C-S-M16</b>
	PUR cable coating, connection technology M12x1, A-coded	24 AC/DC	• Signal status display • Protective circuit	0.3	<b>3679771</b>	<b>NEBV-A1W3F-P-K-0.3-N-M12W3</b>
				0.6	<b>3679772</b>	<b>NEBV-A1W3F-P-K-0.6-N-M12W3</b>
		110 AC/DC	–	0.3	<b>3579461</b>	<b>NEBV-A1W3-K-0.3-N-M12W3</b>
				0.6	<b>3579462</b>	<b>NEBV-A1W3-K-0.6-N-M12W3</b>
	PUR cable coating	24 AC/DC	• Signal status display • Protective circuit	0.6	<b>3679776</b>	<b>NEBV-A1W3F-P-K-0.6-N-LE3</b>
				230 AC/DC	–	0.6
	PVC cable coating	24 V DC	Signal status display	2.5	<b>30931</b>	<b>KMC-1-24DC-2,5-LED</b>
				5	<b>30933</b>	<b>KMC-1-24DC-5-LED</b>
				10	<b>193459</b>	<b>KMC-1-24DC-10-LED</b>
				230 V AC	–	2.5
			5	<b>30934</b>	<b>KMC-1-230AC-5</b>	
	Illuminating seal	12 ... 24 V DC	Signal status display	–	<b>19145</b>	<b>MC-LD-12-24DC</b>
		230 V DC/V AC	Signal status display	–	<b>19146</b>	<b>MC-LD-230AC</b>

# Standard valves to ISO 5599-1

Accessories

**FESTO**

Ordering data					
	Description		Part No.	Type	PU <sup>1)</sup>
<b>Electrical accessories for valves with central plug</b>					
	Angled socket, M12, 4-pin, type A, screw terminal	–	<b>12956</b>	<b>SIE-WD-TR</b>	<b>1</b>
	Modular system for connecting cables → Internet: nebu	0.1 ... 30 m	–	<b>NEBU-...</b>	–
	Connecting cable, straight socket, M12x1, 5-pin, open cable end, 4-wire	2.5	<b>550326</b>	<b>NEBU-M12G5-K-2,5-LE4</b>	<b>1</b>
		5	<b>541328</b>	<b>NEBU-M12G5-K-5-LE4</b>	<b>1</b>
	Connecting cable, angled socket, M12x1, 5-pin, open cable end, 4-wire	2.5	<b>550325</b>	<b>NEBU-M12W5-K-2,5-LE4</b>	<b>1</b>
		5	<b>541329</b>	<b>NEBU-M12W5-K-5-LE4</b>	<b>1</b>
<b>Pressure gauge</b>					
	With cartridge connection for regulator	10 bar	<b>543487</b>	<b>PAGN-26-16-P10</b>	<b>1</b>
		6 bar	<b>543488</b>	<b>PAGN-26-10-P10</b>	<b>1</b>
<b>Seal</b>					
	Enables the valves with central plug M12, 3-pin, to be assembled on the sub-bases of the valve terminal VTSA/VTSA-F		<b>571343</b>	<b>VABD-S2-1-S-C</b>	<b>2</b>
<b>Inscription label</b>					
	Inscription label for valves		<b>161937</b>	<b>IBS-9x17</b>	<b>24</b>
	Clip-on inscription label holder for valve cap, for valves with central plug M12, 3-pin		<b>540888</b>	<b>ASCF-T-S6</b>	<b>5</b>
<b>Manual override</b>					
	Cover cap for manual override, non-detenting	for valves with central plug M12, 3-pin	<b>541010</b>	<b>VAMC-S6-CH</b>	<b>10</b>
	Cover cap for manual override, covered	for valves with central plug M12, 3-pin	<b>541011</b>	<b>VAMC-S6-CS</b>	<b>10</b>
	Heavy duty cover cap for manual override, non-detenting, detenting via accessory	for valves with central plug M12, 3-pin	<b>4105147</b>	<b>VAMC-B-S6-CTR</b>	<b>10</b>
	Tool for manual override	for valves MN1H/MFH	<b>157651</b>	<b>AHB-MD/MF/MW</b>	<b>1</b>
		for heavy duty cover cap, for detenting position	<b>1662543</b>	<b>AHB-MEB-B</b>	<b>1</b>

1) Packaging unit quantity