

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

HANDLE SHANKS

Glass-fibre reinforced polyamide based (PA) technopolymer, black colour, matte finish.

END CAPS

Glass-fibre reinforced polyamide based (PA) technopolymer, black colour, matte finish.

TUBE

Anodised aluminium black colour.

CABLE

8-pin length 5 m.


IP PROTECTION

IP 65 protection class, according to EN 60529 (see page).



FEATURES AND APPLICATIONS

The RH-FG17 handle perfectly combines ergonomics, functionality and safety.

An LED ring (red/green/yellow/blue) is integrated into the handle which, interfaced with an external logic, indicates the status of the machine.



Electrical features	
Led light voltage	24 Vdc
Uscita cavo	8 poli



Code	
RHFG17-10.300.04	660