



SAFETY DATA SHEET

Zinsser B-I-N® Aerosol

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME Zinsser B-I-N® Aerosol
 PRODUCT NO. ZN70208
 APPLICATION Intended for use as a spray, applied coating
 SUPPLIER William Zinsser (UK) Ltd
 Portobello Industrial Estate
 Birtley
 County Durham
 England
 DH3 2RE
 +44(0)191 4106611
 +44(0)191 4920125
 enquiries@tor-coatings.com
 CONTACT PERSON ian.mccormack@tor-coatings.com
 EMERGENCY TELEPHONE +44(0)1865 407333 (NCEC)

2 HAZARDS IDENTIFICATION

Extremely flammable Repeated exposure may cause skin dryness or cracking. Vapours may cause drowsiness and dizziness. Irritating to eyes.

CLASSIFICATION (1999/45) Xi;R36. F+;R12. R66, R67.

ENVIRONMENT

The product is not expected to be hazardous to the environment.

PHYSICAL AND CHEMICAL HAZARDS

The product is highly flammable, and explosive vapours/air mixtures may be formed even at normal room temperatures.

HUMAN HEALTH

In high concentrations, vapours and spray mists are narcotic and may cause headache, fatigue, dizziness and nausea. Risk of serious damage to eyes. Vapours/aerosol spray may irritate the respiratory system. Repeated exposure may cause skin dryness or cracking.

3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content %	Classification (67/548/EEC)
ACETONE	200-662-2	67-64-1	25-50%	F;R11 Xi;R36 R66 R67
ETHANOL	200-578-6	64-17-5	10-25%	F;R11
METHYLAL	203-714-2	109-87-5	5-10%	Xn;R20/21/22,R68/20/21/22. F;R11.
BUTANE	203-448-7	106-97-8	2.5-5.0%	F+;R12
ISOBUTANE	200-857-2	75-28-5	1.0-2.5%	F+;R12
METHANOL	200-659-6	67-56-1	< 1%	F;R11 T;R23/24/25,R39/23/24/25

The Full Text for all R-Phrases is Displayed in Section 16

4 FIRST-AID MEASURES

GENERAL INFORMATION

General first aid, rest, warmth and fresh air. Do not give victim anything to drink if they are unconscious. Get medical attention if any discomfort continues.

INHALATION

Place unconscious person on the side in the recovery position and ensure breathing can take place. If respiratory problems, artificial respiration/oxygen. Get medical attention if any discomfort continues.

INGESTION

Immediately rinse mouth and drink plenty of water or milk. Keep person under observation. Do not induce vomiting. If vomiting occurs, keep head low. Transport immediately to hospital and bring along these instructions.

Zinsser B-I-N® Aerosol**SKIN CONTACT**

Use appropriate hand lotion to prevent defatting and cracking of skin. Immediately remove contaminated clothing. Wash off promptly and flush contaminated skin with water. Promptly remove clothing if soaked through and flush skin with water.

EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Get medical attention promptly if symptoms occur after washing.

5 FIRE-FIGHTING MEASURES**EXTINGUISHING MEDIA**

Fire can be extinguished using: Water spray, fog or mist. Foam, carbon dioxide or dry powder. Dry chemicals, sand, dolomite etc. Do not use water jet as an extinguisher, as this will spread the fire.

SPECIAL FIRE FIGHTING PROCEDURES

Use pressurised air mask if product is involved in a fire. Cool containers exposed to flames with water until well after the fire is out. Keep run-off water out of sewers and water sources. Dike for water control.

UNUSUAL FIRE & EXPLOSION HAZARDS

Aerosol cans may explode in a fire. If heated, volume and pressure increases strongly, resulting in explosion of container.

PROTECTIVE MEASURES IN FIRE

Self contained breathing apparatus and full protective clothing must be worn in case of fire.

6 ACCIDENTAL RELEASE MEASURES**PERSONAL PRECAUTIONS**

Wear protective clothing as described in Section 8 of this safety data sheet.

ENVIRONMENTAL PRECAUTIONS

Spillages or uncontrolled discharges into watercourses must be IMMEDIATELY alerted to the Environmental Agency or other appropriate regulatory body.

SPILL CLEAN UP METHODS

Keep combustibles away from spilled material. Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Absorb in vermiculite, dry sand or earth and place into containers. Wash thoroughly after dealing with a spillage.

7 HANDLING AND STORAGE**USAGE PRECAUTIONS**

Static electricity and formation of sparks must be prevented. Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level. Vapours are heavier than air and may spread near ground to sources of ignition.

STORAGE PRECAUTIONS

Flammable/combustible - Keep away from oxidisers, heat and flames. Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container. Avoid contact with oxidising agents.

STORAGE CLASS

Flammable compressed gas storage.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
ACETONE	WEL	500 ppm	1210 mg/m ³	1500 ppm	3620 mg/m ³	
BUTANE	WEL	600 ppm	1450 mg/m ³	750 ppm	1810 mg/m ³	
ETHANOL	WEL	1000 ppm	1920 mg/m ³			
ISOBUTANE	WEL	600 ppm		750 ppm		
METHANOL	WEL	200 ppm(Sk)	266 mg/m ³ (Sk)	250 ppm(Sk)	333 mg/m ³ (Sk)	

WEL = Workplace Exposure Limit.

INGREDIENT COMMENTS

WEL = Workplace Exposure Limits

PROTECTIVE EQUIPMENT**PROCESS CONDITIONS**

Provide eyewash station.

Zinsser B-I-N® Aerosol**ENGINEERING MEASURES**

Provide adequate ventilation, including appropriate local extraction, to ensure that the defined occupational exposure limit is not exceeded. All handling to take place in well-ventilated area.

RESPIRATORY EQUIPMENT

Provide adequate ventilation. Observe Occupational Exposure Limits and minimise the risk of inhalation of vapours. At work in confined or poorly ventilated spaces, respiratory protection with air supply must be used. Wear mask supplied with: Gas cartridge suitable for organic substances.

HAND PROTECTION

For prolonged or repeated skin contact use suitable protective gloves. Use protective gloves made of: Neoprene. Nitrile. Rubber (natural, latex).

EYE PROTECTION

Wear splash-proof eye goggles to prevent any possibility of eye contact.

OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of skin contact.

HYGIENE MEASURES

DO NOT SMOKE IN WORK AREA! Wash at the end of each work shift and before eating, smoking and using the toilet. Promptly remove any clothing that becomes contaminated. Use appropriate skin cream to prevent drying of skin. When using do not eat, drink or smoke.

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Aerosol.
COLOUR	White.
ODOUR	Characteristic.
SOLUBILITY	Slightly soluble in water.
RELATIVE DENSITY	0.9 Approx. @20°C.
VAPOUR DENSITY (air=1)	Heavier than air
VAPOUR PRESSURE	4700 mbar 20
FLASH POINT (°C)	-74°C. CC (Closed cup).
FLAMMABILITY LIMIT - LOWER(%)	1.8
FLAMMABILITY LIMIT - UPPER(%)	10.0
VOLATILE ORGANIC COMPOUND (VOC)	EXEMPT

10 STABILITY AND REACTIVITY**STABILITY**

No particular stability concerns.

CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition. Avoid contact with strong oxidisers.

HAZARDOUS DECOMPOSITION PRODUCTS

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

11 TOXICOLOGICAL INFORMATION**GENERAL INFORMATION**

Prolonged and repeated contact with solvents over a long period may lead to permanent health problems.

INHALATION

In high concentrations, vapours may irritate throat and respiratory system and cause coughing. In high concentrations, vapours are narcotic and may cause headache, fatigue, dizziness and nausea.

INGESTION

Gastrointestinal symptoms, including upset stomach.

SKIN CONTACT

Acts as a defatting agent on skin. May cause cracking of skin, and eczema. Irritating to skin.

EYE CONTACT

Irritation of eyes and mucous membranes.

Name	PROPANE
Name	BUTANE
Toxic Conc. - LC 50	658 mg/l/4h (inh-rat)

Zinsser B-I-N® Aerosol

Name	METHANOL
Toxic Dose 1 - LD 50	5600 mg/kg (oral rat)
Toxic Conc. - LC 50	64000 ppm/4h (inh-rat)
Toxicological information	
This material is toxic.	
Other Health Effects	
Carcinogen Category 3.	
Name	ETHANOL
Toxic Dose 1 - LD 50	7060 mg/kg (oral rat)
Toxic Conc. - LC 50	20000 ppm/4h (inh-rat)
Name	ACETONE
Toxic Dose 1 - LD 50	5800 mg/kg (oral rat)
Name	ISOBUTANE
Toxic Conc. - LC 50	658 mg/l/4h (inh-rat)
Name	METHYLAL
Toxic Dose 1 - LD 50	5620 mg/kg (oral rat)
Toxic Dose 2 - LD 50	No data
Toxic Conc. - LC 50	No data

12 ECOLOGICAL INFORMATION**ECOTOXICITY**

The product is not expected to be hazardous to the environment.

Zinsser B-I-N® Aerosol

Name PROPANE

LC 50, 96 Hrs, Fish mg/l >1000

Name BUTANE

Ecotoxicity

Not considered dangerous to aquatic organisms.

LC 50, 96 Hrs, Fish mg/l >1000

Mobility

The product contains organic solvents which will evaporate easily from all surfaces.

Bioaccumulative potential

This material is not expected to significantly bioaccumulate.

Degradability

The product is expected to be biodegradable. The product is degraded completely by photochemical oxidation.

Name METHANOL

Ecotoxicity

Not regarded as dangerous for the environment. The product must not be allowed to enter drains or water courses. Dangerous to aquatic life in high concentrations.

LC 50, 96 Hrs, Fish mg/l >10000

EC 50, 48 Hrs, Daphnia, mg/l >10000

Mobility

The product is soluble in water.

Bioaccumulative potential

The product is not bioaccumulating.

Degradability

The product is readily biodegradable.

Name ETHANOL

Ecotoxicity

Not considered dangerous to aquatic organisms. The product must not be allowed to enter drains or water courses.

LC 50, 96 Hrs, Fish mg/l 13000 - 16000

EC 50, 48 Hrs, Daphnia, mg/l 5680 - 7710

Mobility

The product is soluble in water. The product contains organic solvents which will evaporate easily from all surfaces.

Bioaccumulative potential

The product does not contain any substances expected to be bioaccumulating.

Degradability

The product is readily biodegradable.

Name ACETONE

LC 50, 96 Hrs, Fish mg/l 8300

EC 50, 48 Hrs, Daphnia, mg/l 10

Mobility

The product is soluble in water.

Bioaccumulative potential

The product is not bioaccumulating.

Degradability

The product is readily biodegradable.

Name ISOBUTANE

Ecotoxicity

Not considered dangerous to aquatic organisms.

Mobility

The product contains volatile substances, which may spread in the atmosphere.

Bioaccumulative potential

This material is not expected to significantly bioaccumulate.

Degradability

The product is expected to be biodegradable. The product is degraded completely by photochemical oxidation.

Name METHYLAL

13 DISPOSAL CONSIDERATIONS

GENERAL INFORMATION

Waste to be treated as controlled waste. Disposal to licensed waste disposal site in accordance with local Waste Disposal Authority.

Zinsser B-I-N® Aerosol

DISPOSAL METHODS

Dispose of waste and residues in accordance with local authority requirements. Make sure containers are empty before discarding (explosion risk). Absorb in vermiculite or dry sand and dispose of at a licenced hazardous waste collection point.

14 TRANSPORT INFORMATION

PROPER SHIPPING NAME	AEROSOLS
ENVIRONMENTALLY HAZARDOUS SUBSTANCE/MARINE POLLUTANT	No.
UN NO. ROAD	1950
ADR CLASS NO.	2.1
ADR CLASS	Class 2: Gases
TUNNEL RESTRICTION CODE	(D)
ADR LABEL NO.	2.1
UN NO. SEA	1950
IMDG CLASS	2.1
EMS	F-D, S-U
UN NO. AIR	1950
AIR CLASS	2.1

15 REGULATORY INFORMATION

LABELLING



Irritant



Extremely flammable

RISK PHRASES

R12	Extremely flammable.
R36	Irritating to eyes.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

SAFETY PHRASES

S2	Keep out of the reach of children.
S16	Keep away from sources of ignition - No smoking.
S23	Do not breathe vapour/spray.
S26	In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S37	Wear suitable gloves.
S51	Use only in well-ventilated areas.
A1	Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.
A2	Do not spray on a naked flame or any incandescent material.

UK REGULATORY REFERENCES

The Control of Substances Hazardous to Health Regulations 2002 (S.I 2002 No. 2677) with amendments.

EU DIRECTIVES

System of specific information relating to Dangerous Preparations. 2001/58/EC. Dangerous Preparations Directive 1999/45/EC.

APPROVED CODE OF PRACTICE

Safety Data Sheets for Substances and Preparations. Classification and Labelling of Substances and Preparations Dangerous for Supply.

NATIONAL REGULATIONS

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2002. No. 1689. Workplace Exposure Limits 2005 (EH40)

16 OTHER INFORMATION

Zinsser B-I-N® Aerosol

INFORMATION SOURCES

Croner's Emergency Spillage Guide Croner's Emergency First Aid Guide Croner's Substances Hazardous to Health

REVISION COMMENTS

This is first issue.

ISSUED BY

I McCormack

REVISION DATE 07/01/2005

REV. NO./REPL. SDS GENERATED 1

SDS NO. 17530

SAFETY DATA SHEET STATUS

Approved.

DATE 16/07/2012

RISK PHRASES IN FULL

R12	Extremely flammable.
R20/21/22	Harmful by inhalation, in contact with skin and if swallowed.
R68/20/21/22	Harmful: possible risk of irreversible effects through inhalation, in contact with skin and if swallowed.
R11	Highly flammable
R36	Irritating to eyes.
R66	Repeated exposure may cause skin dryness or cracking.
R23/24/25	Toxic by inhalation, in contact with skin and if swallowed.
R39/23/24/25	Toxic: danger of very serious irreversible effects through inhalation, in contact with skin and if swallowed.
R67	Vapours may cause drowsiness and dizziness.

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.