

Indexable insert countersink, single tooth cutter

for universal use up to 1300 N/mm² with CC..06 and CC..09..

ATORN[®]

Application

180° countersinks with CC.. indexable inserts in the diameter range from 10.00–33.00 mm, in the material groups steel, stainless steel, non-ferrous metals, cast materials and special alloys for use in single part and series production.

Version

- backing material made from high-grade steel with clamping surface in line with DIN 1835B

Advantage

- precisely fitting inserts ensure optimum machining results even under difficult conditions
- universal use in all material groups
- cost-efficient tool in comparison with mono-block solutions



Art. No.	11240 620
Number of cutting edges	1 PCS
Tool holding device	HB parallel shank
Cutting edge diameter	32 mm
Cantilever length	56 mm
Length	120 mm
Min. pilot hole diameter	12 mm
Shaft diameter	20 mm
Suitable for indexable inserts	CC..09

EAN-Code

4050293112382