

## Single-tooth milling cutter HSSE Co 5

1 cutter, uncoated

**ORION**<sup>®</sup>

### Application:

For milling, plunging and contour milling NF metals and plastics.



### Version:

- HSSE Co 5
- Straight shank pursuant to DIN 6535 HA
- Sharp-edged
- Uncoated

Application	Steel (N/mm <sup>2</sup> )			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GJMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
						60	186	30	35	25	32	77	30						

<b>Art. no.</b>	<b>15007 070</b>
<b>Cutting material</b>	HSSE Co5
<b>Surface</b>	Uncoated
<b>Type</b>	W
<b>Number of cutting edges</b>	1 PCS
<b>Twist angle</b>	40°
<b>Tool holding device</b>	HA parallel shank
<b>Overall length</b>	Normal
<b>Cutting edge diameter</b>	7 mm
<b>Cutting edge length</b>	14 mm
<b>Length</b>	60 mm
<b>Shaft diameter</b>	8 mm
<b>fz aluminium</b>	0.015 mm

### EAN-Code

4039247083114