

Fixed centring point

With full tip and thread for draw-off nuts



Application:

For centring workpieces on lathes, grinding machines and radial drilling machines.

Execution:

- Tip angle 60°.
- With thread for draw-off nut.
- Taper fully hardened and precision-ground.
- Carbide-tipped.
- Concentricity tolerance $\leq 0.8 \mu\text{m}$.

Delivery:

1x centring point MK 2.



Art. no.	22121 120
Brand	BRUCKNER
Manufacturer Part Number	2852
Morse taper size	MK 2
Programming size	48 mm
Diameter of flat area	7 mm
Nut for removing spindles	M22 x 1.5
Concentricity tolerance	0.008 mm
DIN	807
Gross Weight	0.158 kg
Product Group	2AA