

## Indexable insert countersink, single tooth cutter

for universal use up to 1300 N/mm<sup>2</sup> with CC..06 and CC..09..

**ATORN**<sup>®</sup>

### Application

180° countersinks with CC.. indexable inserts in the diameter range from 10.00–33.00 mm, in the material groups steel, stainless steel, non-ferrous metals, cast materials and special alloys for use in single part and series production.



### Version

- backing material made from high-grade steel with clamping surface in line with DIN 1835B

### Advantage

- precisely fitting inserts ensure optimum machining results even under difficult conditions
- universal use in all material groups
- cost-efficient tool in comparison with mono-block solutions

<b>Art. No.</b>	<b>11240 630</b>
<b>Number of cutting edges</b>	1 PCS
<b>Tool holding device</b>	HB parallel shank
<b>Cutting edge diameter</b>	33 mm
<b>Cantilever length</b>	56 mm
<b>Length</b>	120 mm
<b>Min. pilot hole diameter</b>	12 mm
<b>Shaft diameter</b>	20 mm
<b>Suitable for indexable inserts</b>	CC..09

### EAN-Code

4050293112399