

## 3-point internal micrometer

IMICRO



### Application:

For high-precision measurement of through-bores, even at high measuring depths.

### Execution:

- Measuring faces made of hardened steel
- Friction coupling for consistent, repeatable measuring force
- Self-centring and self-aligning

### Advantage:

- Ground step taper for high precision
- Insensitive to influence of body heat from the user's hand and fluctuations in ambient temperature
- The only 3-point internal micrometer working on the Abbe principle

### Delivery:

In cardboard box



<b>Art. no.</b>	<b>31695 004</b>
<b>Brand</b>	TESA
<b>Manufacturer Part Number</b>	00813411
<b>Min./max. length measuring range</b>	4-4.5 mm
<b>Measuring depth</b>	20 mm
<b>Error limit</b>	4 µm
<b>Vernier scale</b>	0.001 mm
<b>Measuring spindle increments</b>	0.5 mm
<b>Calibration Group</b>	I
<b>DIN</b>	863
<b>Calibration Group Description</b>	Internal micrometers (3 point)
<b>Gross Weight</b>	0.315 kg
<b>Product Group</b>	362

### EAN

7630041108347