




1D/2D code readers

O2IIRDKG/E1/E4/EF/VF/TB/S



- 1 lens
- 2 illumination unit
- 3 laser spots



Product characteristics

Type of light		infrared light
Image resolution	[px]	1280 x 960
Max. reading rate	[Hz]	40

Electrical data

Operating voltage	[V]	18...30 DC
Current consumption	[mA]	< 300; (24V DC typical)
Max. current consumption	[mA]	650; (18V DC, with switched outputs, memory stick active)
Protection class		III
Reverse polarity protection		yes



1D/2D code readers

O2IIRDKG/E1/E4/EF/VF/TB/S

Type of light	infrared light			
Wave length [nm]	850			
Image sensor	CMOS image sensor black/white			
Inputs / outputs				
Number of inputs and outputs	Number of digital outputs: 2			
Inputs				
Trigger	external; 24 V PNP/NPN (IEC 61131-2 Typ 3); TCP/IP; PROFINET; internal			
Outputs				
Total number of outputs	2			
Electrical design	PNP/NPN; (parameterisable)			
Number of digital outputs	2; (configurable)			
Output function	configurable			
Max. voltage drop switching output DC [V]	1			
Max. current load per output [mA]	100			
Short-circuit protection	yes			
Type of short-circuit protection	pulsed			
Overload protection	yes			
Detection zone				
Field of view size [mm]	Operating distance	field of view		
	85	28 x 21		
	300	92 x 69		
	500	152 x 114		
	1000	302 x 227		
Operating distance [mm]	> 85			
Image resolution [px]	1280 x 960			
Lens type	standard			
Readable codes	Interleaved 2-of-5; Industrial 2-of-5; Code 39; Code 93; Code 128; Pharmacode; Codabar; EAN8; EAN8 Add-On 2; EAN8 Add-On 5; EAN13; EAN13 Add-On 2; EAN13 Add-On 5; UPC-A; UPC-A Add-On 2; UPC-A Add-On 5; UPC-E; UPC-E Add-On 2; UPC-E Add-On 5; GS1 DataBar Omnidirectional; GS1 DataBar Truncated; GS1 DataBar Stacked; GS1 DataBar Stacked Omnidirectional; GS1 DataBar Limited; GS1 DataBar Expanded; GS1 DataBar Expanded Stacked; GS1 - 128; MSI Barcode; ECC200; PDF-417; QR; Micro-QR; Aztec Code; GS1 ECC200; GS1 QR Code; GS1 Aztec Code			
Code quality based on			ISO / IEC 15415	
			ISO / IEC 15416	
			AIM DPM	
			ISO/IEC TR 29158	
			SEMI T10	
Legible fonts	Industrial; Document; OCR-A; OCR-B; Pharma; Semi; Universal; Dot Print			
Text recognition	yes			
Omnidirectional reading	yes			
Max. inclination to the image plane [°]	45			
Max. reading rate [Hz]	40			



1D/2D code readers

O2IIRDKG/E1/E4/EF/VF/TB/S

Software / programming			
Parameter setting options		teach button; via PC with ifm Vision Assistant	
Interfaces			
Communication interface		Ethernet	
Ethernet			
Number of Ethernet interfaces		1	
Transmission standard		10Base-T; 100Base-TX	
Transmission rate		10 MBit/s; 100 MBit/s	
Protocol		TCP/IP; PROFINET	
Factory settings		IP address: 192.168.0.69	
		subnet mask: 255.255.255.0 (Class C)	
		gateway IP address: 192.168.0.201	
		MAC address: see type label	
Usage type		parameter setting; data transmission	
Operating conditions			
Ambient temperature [°C]		-10...50	
Storage temperature [°C]		-40...70	
Max. relative air humidity [%]		90; (non condensing)	
Max. height above sea level [m]		4000	
Protection		IP 65	
Pollution degree		3	
Tests / approvals			
EMC		EN IEC 61000-6-4 radiation of interference	industrial environments
		EN IEC 61000-6-2 immunity	industrial environments
Shock resistance		EN 60068-2-27	50 g 11 ms / not repetitive
		EN 60068-2-27	40 g 6 ms / repetitive
Vibration resistance		EN 60068-2-6	2 g (10 ... 150 Hz)
Laser protection class		1	
Notes on laser protection		Caution:	laser light
		laser class:	1
			EN / IEC60825-1:2007
			EN / IEC60825-1:2014
			Complies with 21 CFR 1040.10 except for compliance with IEC 60825-1 Ed. 3, as described in Laser Notice No. 56 dated 8 May 2019.
Photobiological safety		exempt group; (EN 62471)	
Electrical safety		EN IEC 61010-2-201	electrical supply only via PELV circuits
MTTF [years]		52	
Mechanical data			
Weight [g]		599.6	
Type of mounting		screw mounting; (bore hole M4 x 7 mm)	
Dimensions [mm]		45 x 45 x 96	
Materials		housing: diecast zinc powder-coated; front pane: Gorillaglas; LED window: PC; pushbutton: POM	



1D/2D code readers

O2IIRDKG/E1/E4/EF/VF/TB/S

Sealing material	FKM
Tightening torque [Nm]	2.1

Displays / operating elements

Display	function	2 x LED, green
	function	2 x LED, yellow
	Teach-Funktion	1 x LED, green
	Teach-Funktion	1 x LED, yellow
Operating elements	1 x	Teach-Taste

Accessories

Accessories (optional)	Operating software
	Mounting accessories
	Adapter cable
	protective panes and filter panes

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Electrical connection - Ethernet


Connector: 1 x M12; coding: D; Moulded body: stainless steel; Sealing: FKM



1	TxD+
2	RxD+
3	TxD-
4	RxD-

Electrical connection - supply

Connector: 1 x M12; coding: A; Moulded body: stainless steel



1	U+
2	trigger input
3	0 V
4	switching output 1 configurable
5	switching output 2 configurable / trigger output with external illumination