



Configurable safe small controllers PNOZmulti 2, expansion module, safe monitoring of 2 axes.

Technical details

General data

Approval:	CE, UKCA, cULus Listed, KOSHA, EAC (Eurasian), TÜV
Application range:	Failsafe

Technical data

Electrical data

Purpose of UINT1:	Module supply
Source of internal voltage:	Via base unit
Voltage type of UINT1:	DC

Input incremental encoder

Number of incremental encoder:	2
Connection (increment encoder):	8-pin Mini-IO female connector
Phase pos. diff.sign. inc. enc.:	90° ±30°
Prog. mon. fun. wo hyst. incr.:	0.1 Hz - 500 kHz

Inputs

Potential isolation input:	Yes
----------------------------	-----

Environmental data

Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	0 - 60 °C
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-30, EN 60068-2-78

Condensation permitted?:	Not permitted
Perm. operating height ASL:	2000 m
EMC to standard ...:	EN 61131-2
Vibration to standard ...:	EN 60068-2-6
Acc. shock to standard1:	15g
Clearance & creepage dist. to:	EN 61131-2
Overvoltage category:	II
Pollution degree clear.&creep.:	2
Protection type standard:	EN 60529
Times	
Reaction time over limit value:	1/f_actual + 16ms
Potential separation	
Potential isolation 1 between:	Sensor and system voltage
Type of potential isolation 1:	Functional insulation
Potential isolation 2 between:	Sensor 1 and sensor 2
Type of potential isolation 2:	Functional insulation
Mechanical data	
Mounting position:	horizontal on top hat rail
DIN-rail dimensions:	35 x 7.5 EN 50022
Housing material lower section:	PC
Housing material front plate:	PC
Housing material upper part:	PC
Connection terminal:	Screw terminal, Spring-loaded terminal
Terminal style:	plug-in
Flex. cond. c/s AWG info:	24 - 12 AWG
Height dimension:	101.4 mm
Width dimension:	22.5 mm
Depth dimension:	111 mm
Net weight:	120

Gross weight:

130

Obligatory accessories

793544

Screw terminals PNOZ 2MM 1 set



783544

Spring terminals PNOZ 2MM 1 set



Optional accessories

773871

PNOZ msi S15



773870

PNOZ msi S09



772201

MM A MINI-IO CAB99 2.5m



772200

MM A MINI-IO CAB99 1.5m



773872

PNOZ msi S025



772202

MM A MINI-IO CAB99 5.0m





773845

PNOZ msi b4 Box
