

## Ideal shears D 15 S-BE compact, left-cutting

With double lever action

*Erdi*

### Application:

For short, straight cuts and tight radii in standard sheet metal up to 1.2-mm thickness.

### Execution:

- Ideal for tight radii
- Forged cutting head, sheet metal handles
- Cutting edge length: 20 mm
- Stainless steel blade inductively hardened
- Maximum sheet metal thickness that can be cut: 1 mm (600 N/mm<sup>2</sup>)

### Advantage:

- Extremely flexible and compact shears
- Noticeably reduced force application thanks to double lever ratio
- Practical catch/stopper combination
- With ergonomic two-component handles for a secure hold, even when high force is used



<b>Art. no.</b>	<b>53671 030</b>
<b>Brand</b>	ERDI
<b>Manufacturer Part Number</b>	D15S-BE
<b>Material</b>	Stainless steel
<b>Length</b>	180 mm
<b>Cutting direction</b>	Left-hand cutting
<b>Material of handle</b>	2-component plastic
<b>Gross Weight</b>	0.191 kg
<b>Product Group</b>	552

### EAN

4010220031582