



Section 1. Product and Company Identification.

1.1 Model Number; TM102 v1
1.2 Description; Professional Auto-Ranging Digital Multimeter - 8 Function
Battery: 9 Volts. 35 grams.

1.3 Manufacturer;

Sealey Group.
Kempson Way,
Bury St. Edmunds,
Suffolk.
IP32 7AR

1.4 Emergency telephone number; 44 (0) 1284 757 500 (Office Hours)

Date of source compilation; 10 January 2013

Section 2. Hazards Identification.

Battery is hermetically sealed and does not present a hazard under normal conditions of use.

Ingestion: Swallowing a battery can be harmful. Contents of an open battery can cause serious chemical burns of mouth, oesophagus, and gastrointestinal tract.

Inhalation: Contents of an open battery can cause respiratory irritation.

Skin Contact: Contents of an open battery can cause skin irritation and/or chemical burns.

Eye Contact: Contents of an open battery can cause severe irritation and chemical burns.



Section 3. Substances.

3.1 Chemical Name (substance)	3.1 CAS No.	3.2 Concentration Weight	Classification	
			Hazard Class & Category Code	Hazard Statements
Manganese Dioxide	1313-13-9	28.88%	Acute Tox. 4 Acute Tox. 4 STOT RE 2 Aquatic Chronic 2	H302 H332 H373 H411
Zinc	7440-66-6	8.75%	Aquatic Acute 1 Aquatic Chronic 1	H400 H410
Ammonium Chloride	12125-02-9	8.7%	Acute Tox. 4 Skin Irrit. 2 Eye Irrit. 2 STOT SE 1 Muta. 2	H302 H315 H319 H335 H341
Acetylene Black	74-86-2	5.25%	Flam. Gas 1 Press. Gas. STOT SE 3	H220 H280 H336
Zinc Chloride	7646-85-7	4.16%	Met. Corr. 1 Acute Tox. 4 Skin Corr. 1A Eye Dam. 1 STOT SE 3 Aquatic Acute 1 Aquatic Chronic 1	H290 H302 H314 H318 H335 H400 H410
Lead	7439-92-1	0.025%	Acute Tox. 4 Acute Tox. 4 Muta. 2 Carc. 2 Repr. 1A STOT RE 1 Aquatic Acute 1 Aquatic Chronic 1	H302 H332 H341 H351 H360 H372 H400 H410
Cadmium	7440-43-9	< 0.0005%	Carc. 1B Muta. 2 Repr. 2 Acute Tox. 2 STOT RE 1 Aquatic Acute 1 Aquatic Chronic 1	H350 H341 H361 H330 H372 H400 H410
Mercury	7439-97-6	< 0.0001%	Acute Tox. 2 Skin Sens. 1 Acute Tox. 2 Muta. 2 Repr. 1A STOT SE 1 STOT RE 1 Aquatic Acute 1	H300 H317 H330 H341 H360 H371 H373 H400

For full text of Phrases and Statements, see Section 16.



Section 4. First Aid Measures.

Batteries do not pose a risk to eyes or skin under normal circumstances.
In the case of contact with internal substances;

4.1 Description of first aid measures

- Inhalation** If breathing difficulties develop, remove the person to fresh air.
Loosen close fitting clothing.
Ensure that person is warm.
Get medical attention.
- Skin Contact** Remove contaminated clothing.
Remove affected area(s) with soap and water.
Seek medical attention if chemical burn(s) appear or if symptoms persist.
- Eye Contact** Irrigate eyes with water for at least 15 minutes while raising eyelid(s).
Get medical attention.
- Ingestion** Do not induce vomiting.
Do not give food or drink.
Get medical attention.

4.2. Most important symptoms and effects, both acute and delayed

No information available.

4.3. Indication of any immediate medical attention and special treatment needed

No information available.

Section 5. Fire Fighting Measures.

5.1. Extinguishing media

Any extinguishing media.
Use extinguishing media that is appropriate for the surrounding area.

5.2. Special hazards arising from the substance or mixture

Move batteries away from a fire incident, if safe to do so.
Cool batteries to reduce the risk of rupture.

5.3. Advice for fire-fighters

Fire Fighters should wear self-contained breathing apparatus and appropriate Personal Protective Equipment. Thermal degradation may produce hazardous fumes of zinc and manganese; hydrogen gas, caustic vapours of potassium hydroxide and other toxic by-products.



Section 6. Accidental Release Measures.

6.1. Personal precautions, protective equipment and emergency procedures

Wear appropriate protective clothing, see Section 8.

6.2. Environmental precautions

Ventilate area.

6.3. Methods and material for containment and cleaning up

Collect in a leak proof container.

Place battery in a sealed bag with an absorbent such as sand, silica, chalk, lime powder or vermiculite.

Rinse contamination with water.

Prevent contaminated water from entering sewers or water courses.

6.4. Reference to other sections

See Section 7 for information on Safe Handling

See Section 8 for information of Personal Protective Equipment.

See Section 13 for information on disposal.

Section 7. Handling and Storage.

7.1. Precautions for safe handling

Wear appropriate protective clothing, see Section 8.

7.2. Conditions for safe storage, including any incompatibilities

Store batteries in a well ventilated area.

Do not short circuit a battery. A short circuit causes heating and can lead to ignition of surrounding materials.

To minimize the risk of a short circuit, always store batteries in an appropriate container to prevent contact with conductive materials.

Keep batteries away from children.

7.3. Specific end use(s)

Intended for use as the battery for the Model Number identified in 1.1 with Description stated in 1.2.



Section 8. Exposure Controls/Personal Protection.

8.1. Control parameters

In the event of battery rupture and leakage:

Ventilate the area.

Remove sources of ignition.

8.2. Exposure controls

The use of Personal Protective Equipment (PPE) is not necessary under conditions of normal use.

If handling a leaking or ruptured battery, ensure that the following Personal Protective Equipment (PPE) is used.

Eye/Face Protection

Chemical grade full face shield.

Skin Protection

Acid resistant, natural rubber or neoprene gloves.

Protective rubber apron.

Appropriate Personal Protection with long sleeves and long trousers.

Respiratory Protection

Acid gas filter mask or self-contained breathing apparatus.



Section 9. Physical and Chemical Properties.

9.1. Information on basic physical and chemical properties

The following information is not a technical specification or sales specification.

(a) Appearance:	Acetylene Black: Black powder. Ammonium Chloride: Colourless liquid. Manganese Dioxide: Black powder. Zinc Chloride: Colourless liquid.
(b) Odour:	No information available.
(c) Odour threshold;	No information available.
(d) pH:	No information available.
(e) Melting point;	Ammonium Chloride: -2°C Manganese Dioxide: 535°C Zinc: 420°C Zinc Chloride: -2°C
(f) Initial boiling point and boiling range;	No information available.
(g) Flash point;	No information available.
(h) Evaporation rate;	No information available.
(i) Flammability (solid, gas);	No information available.
(j) Upper/lower flammability or explosive limits;	No information available.
(k) Vapour pressure;	No information available.
(l) Vapour density;	No information available.
(m) Relative density;	No information available.
(n) Solubility (ies):	Ammonium Chloride: Soluble in water. Zinc Chloride: Soluble in water.
(o) Partition coefficient: n-octanol/water;	No information available.
(p) Auto-ignition temperature;	No information available.
(q) Decomposition temperature;	No information available.
(r) Viscosity;	No information available.
(s) Explosive properties;	No information available.
(t) Oxidising properties.	No information available.

9.2 Other information

No information available.



Section 10. Stability and Reactivity.

10.1. Reactivity	No information available.
10.2. Chemical stability	Stable.
10.3. Possibility of hazardous reactions	Hazardous polymerisation will not occur.
10.4. Conditions to avoid	Do not charge. Do not short circuit. Do not subject battery to fire.
10.5. Incompatible materials	No information available.
10.6. Hazardous decomposition products	No information available.

Section 11. Toxicological Information.

11.1. Information on toxicological effects

The materials that comprise this battery are hermetically sealed.

The potential for exposure to materials is negligible when this battery is used as directed. See Section 7.

Inappropriate handling and / or inappropriate use of this battery may result in release of the materials that are sealed within.

Inhalation, skin contact and eye contact are possible when the battery is opened.

Exposure to internal components and corrosive fumes will cause irritation to the eyes skin and mucous membranes.

Section 12. Ecological Information.

When properly used and disposed of correctly, the battery does not present environmental hazard.

Do not release internal components into water ways, wastewater or ground water.

12.1. Toxicity	No data available.
12.2. Persistence and degradability	No data available.
12.3. Bioaccumulative potential	No data available.
12.4. Mobility in soil	No data available.
12.5. Results of PBT and vPvB assessment	No data available.
12.6. Other adverse effects	No data available.

Section 13. Disposal Considerations.

13.1. Waste treatment methods

Disposal of the battery must be in accordance with local authority regulations.

The battery should be completely discharged prior to disposal and the terminals taped or capped to prevent short circuit.

Do not dispose of batteries with household waste.

Do not dispose of batteries at landfill sites.

Do not incinerate batteries.



Section 14. Transport Information.

ADR. International Carriage of Dangerous Goods by Road.

Not subject to ADR.

IATA. International Air Transport Association.

Special Provision A123.

Batteries not otherwise listed as Dangerous Goods concerning transport by air, no UN Code refers.

Examples of such batteries are (but not restricted to) alkali-manganese, zinc-carbon and nickel cadmium batteries.

Any electrical battery or battery powered device, equipment or vehicle having the potential of a dangerous evolution of heat must be prepared for transport so as to prevent:

- (a) a short circuit (e.g. in the case of batteries, by the effective insulation of exposed terminals; or in the case of equipment, by the disconnection of the battery and protection of exposed terminals); and
- (b) accidental activation.

The statement "Not restricted, as per Special Provision A123" must be included in the description of the article on the Air Waybill when required.

IMDG. International Maritime Dangerous Goods.

Not subject to IMDG.



Section 15. Regulatory Information.

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture
No information available.

15.2. Chemical safety assessment
No information available.

Section 16. Additional Information.

Full text of Phrases and Statements used in Section 3;

H220: Extremely flammable gas.
 H280: Contains gas under pressure; may explode if heated.
 H290: May be corrosive to metals.
 H300: Fatal if swallowed.
 H302: Harmful if swallowed.
 H314: Causes severe skin burns and eye damage.
 H315: Causes skin irritation.
 H317: May cause an allergic skin reaction.
 H318: Causes serious eye damage.
 H319: Causes serious eye irritation.
 H330: Fatal if inhaled.
 H332: Harmful if inhaled.
 H335: May cause respiratory irritation.
 H336: May cause drowsiness or dizziness.
 H341: Suspected of causing genetic defects.
 H350: May cause cancer.
 H351: Suspected of causing cancer.
 H360: May damage fertility or the unborn child.
 H361: Suspected of damaging fertility or the unborn child.
 H371: May cause damage to organs.
 H372: Causes damage to organs through prolonged or repeated exposure.
 H373: May cause damage to organs through prolonged or repeated exposure.
 H400: Very toxic to aquatic life.
 H410: Very toxic to aquatic life with long lasting effects.
 H411: Toxic to aquatic life with long lasting effects.

The above information is believed to be accurate and represents the best information currently available.

No warranty is expressed or implied by the above information.

We assume no liability resulting from use of the above information.

The end user should conduct their own investigations to determine the suitability of the above information for their particular purpose.

Issue level	Date	Revisions
1	10/01/13	First issue.
2	22/01/16	Sections 5 and 14
3	15/07/16	Sections 1.2, 3, 8, 12, 14
4	20/09/16	Section 14

End of Safety Data Sheet.