

## Conical washers DIN 6319 type G



### Application:

For transferring clamping forces in cases where clamping elements need to adapt to uneven clamping surfaces.

### Execution:

- Stamped, pressed and tempered

### Advantage:

- Thanks to the large diameter, these are particularly ideal for clamping via the slot in the case of clamps.



<b>Art. no.</b>	<b>26208 714</b>
<b>Brand</b>	AMF
<b>Manufacturer Part Number</b>	81992
<b>Suitable cheese-head screw DIN 912</b>	M10
<b>Internal diameter</b>	12 mm
<b>Outer diameter</b>	30 mm
<b>Height</b>	5 mm
<b>Diameter</b>	18.5 mm
<b>DIN</b>	6319
<b>Gross Weight</b>	0.022 kg
<b>Product Group</b>	260

### EAN

4020772081997