


Temperature transmitter

TU-025CLEM14-A-ZVG/DE



Product characteristics

Number of inputs and outputs	Number of analogue outputs: 1	
Measuring range	-50...150 °C	-58...302 °F
Process connection	threaded connection G 1/4 external thread	
Installation length EL [mm]	25	

Application

Measuring element	1 x Pt 1000; (to DIN EN 60751, class A)	
Media	liquids and gases	
Pressure rating [bar]	400	

Electrical data

Operating voltage [V]	8...32 DC; ("supply class 2" to cULus)	
Current consumption [mA]	< 30	
Protection class	III	
Reverse polarity protection	yes	

Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 1	
------------------------------	-------------------------------	--

Outputs

Total number of outputs	1	
Output signal	analogue signal	
Number of analogue outputs	1	
Analogue voltage output [V]	0.5...4.5	
Min. load resistance [Ω]	2000	
Short-circuit protection	yes	
Overload protection	yes	


Measuring/setting range

Measuring range	-50...150 °C	-58...302 °F
-----------------	--------------	--------------



Temperature transmitter

TU-025CLEM14-A-ZVG/DE


Resolution		
Resolution of analogue output	[K]	0.1
Accuracy / deviations		
Precision analogue output	[K]	± 0,3 + (± 0,1 % MS)
Temperature coefficient [% of the span / 10 K]	0,1; (in case of deviation from the reference condition 25 ± 5 °C)	
Response times		
Dynamic response T05 / T09	[s]	1 / 3; (to DIN EN 60751)
Operating conditions		
Ambient temperature	[°C]	-40...100
Storage temperature	[°C]	-40...100
Protection	IP 68; IP 69K	
Tests / approvals		
EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF	[years]	849
UL approval	UL Approval no.	K009
Mechanical data		
Weight	[g]	92.5
Materials	stainless steel (1.4404 / 316L); PPS; FKM	
Materials (wetted parts)	stainless steel (1.4404 / 316L); FKM	
Process connection	threaded connection G 1/4 external thread	
Probe diameter	[mm]	6
Installation length EL	[mm]	25
Remarks		
Remarks	The values for accuracy apply to flowing water.	
	referring to UL: for use on a low voltage circuit with overcurrent protection	
	in accordance with UL873 tab. 28.1 or I _{max} = 100/U _b (U _b = voltage of the circuit)	
Pack quantity	1 pcs.	
Electrical connection		
Connector: 1 x DEUTSCH connector (DT04-3P)		
		



Temperature transmitter

TU-025CLEM14-A-ZVG/DE

Connection



OUT: analogue output