




Specifications

Impedance	: 50Ω
Frequency Range	: DC - 3GHz
VSWR	: 1.4 : 1 Max.
Insertion Loss	: -1dB Max.
Working Voltage	: 335Vrms Max.
Dielectric Withstanding Voltage	: 750Vrms Min.
Insulator Resistance	: 5,000Ω Min.

**RoHS
Compliant**

Diagram



1. SMA IP67 B/H Jack Crimp type for OD1.37mm Cable
2. Heat Shrink Tube F32 OD2.5mm L=10mm Colour: Black
3. OD1.37mm tin plated cable black jacket
4. SMA ST. Plug Crimp for OD1.37mm Cable

Part Number Table

Description	Part Number
RF Coaxial Cable Assembly, 1.37mm, IP67 SMA B/H JackSMA Plug, 150mm	MC000787

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.