

Drive motor MB 30 E

All-rounder for use in almost all industrial sectors



Application:

Universal tool for milling, grinding, brushing or polishing

Execution:

- Overload protection of the motor thanks to automatic shutdown
- Start-up current limitation prevents current peaks and protects the motor
- Machine can be operated when suspended or standing
- Soft start

Advantage:

- Constant speed even under loads
- Automatic cut-off when carbon brushes become worn
- No pulsing in low speed range
- Fewer mechanical wear parts because there is no gear
- Fully encapsulated sensorless electronics – no clogging with metal chips

Delivery:

With DV 8 flexible shaft, straight handpiece



Art. no.	72120 015
Brand	BIAX DRUCKLUFT
Manufacturer Part Number	010403410
Model	MB 30 E
Manufacturer Article Number	010403410
Power input	1300 W
Min./max. rotation speed	5000-15000 rpm
Sound-pressure level	75 dB
Weight	5.2 kg
IP protection class	IP 20
With overload protection	Yes
Made in	Germany
Connection thread	M10 x 30
Applications	Hanging, Standing
Gross Weight	9.750 kg
Product Group	749