

LED machine lamp ring light

with adjustable magnetic feet



Application:

For use on drilling and milling machines

Execution:

- Attach to the machine by means of adjustable, rubber-coated magnetic feet
- High-performance LED 460 lumens in aluminium housing
- Uniform and low-reflection illumination, glare and flicker-free
- min. 50,000 hours service life
- Internal diameter 100 mm, external 160 mm, height 42 mm

Advantage:

- Simple, trouble-free mounting on the machine without any screws

Delivery:

With power supply



| | |
|---------------------------------|------------------|
| Art. no. | 56879 300 |
| Brand | BAUER & BÖCKER |
| Manufacturer Part Number | 900/83 |
| Power rating | 7.5 W |
| Gross Weight | 2.000 kg |
| Product Group | 5ID |

EAN

4260131238895