

Fixed ball-type tap wrench

For mounting screw taps and hand reamers

ORION®

Application:

For mounting screw taps and reamers with square.

Execution:

- Steel tool holder with screw-off arm and 4 square holes to DIN 10

Advantage:

- High-quality steel with very good wear characteristics and chromium-plated extensions for high corrosion resistance
- User-friendly handling and short retooling times
- Excellent value for money



Art. no.	13545 020
Brand	ORION
Manufacturer Part Number	13545020
Tap wrench size	2
Square size	3.4 mm/4.3 mm/4.9 mm/5.5 mm
Min./max. thread-cutting area, metric	4-10 mm
Min./max. thread-cutting area, imperial	5/32-3/8 in
Length	240 mm
Gross Weight	0.162 kg
Product Group	109

EAN

4039247076574

