

## Thread milling cutter, single-edge cutter, full-profile, 60°

For universal use up to 1500 N/mm<sup>2</sup> in female threads

**ATORN**<sup>®</sup>



### Application

For producing metric right-hand and left-hand threads on CNC machines, in steel, stainless steel, non-ferrous metals, cast iron and special alloy material groups up to a strength of 1500 N/mm<sup>2</sup>.

### Version

- Single-edge cutter in full-profile design

### Advantage

- Innovative cutting geometry for very high dimensional accuracy, process reliability and chip removal.
- High-quality cutting material and cutting edge finish for very high service life requirements
- Low tool costs thanks to high variability in the thread diameter, just one tool required for right-hand thread and left-hand thread

Application	Steel (N/mm <sup>2</sup> )			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	90	70	60	70	60	140	140	135	135	120	120	135	120	50	30	25	25		

<b>Art. no.</b>	<b>13498 700</b>
<b>Hole type</b>	Clearance/blind hole ≤ 3xD
<b>Coolant supply</b>	External
<b>Min./max. pitch internal</b>	0.4-0.4 mm
<b>Cutting edge diameter</b>	1.55 mm
<b>Shaft diameter</b>	3 mm
<b>Effective length of thread milling</b>	7.1 mm
<b>Length</b>	39 mm
<b>Number of grooves</b>	3 PCS
<b>Machining type</b>	Inside
<b>Number of cutting edges</b>	1 PCS

### EAN-Code

4050293658637