

Pneumatic straight grinder G 813 H

**MANNESMANN
DEMAG**

Application:

For fine milling, grinding, engraving and polishing work

Delivery:

Incl. hose unit



| | |
|---|------------------|
| Art. no. | 75061 045 |
| Brand | MANNESMANN DEMAG |
| Manufacturer Part Number | 60019755 |
| Model | G 813 H |
| Valve design | Lever valve |
| Max. idle speed | 70000 rpm |
| Min./max. idle speed | 0-70000 rpm |
| Power input | 70 W |
| Air consumption | 2 l/s |
| Sound-pressure level | 76 dB |
| Length | 120 mm |
| Diameter of housing | 14 mm |
| Collet chuck diameter | 3 mm |
| Suitable for max. sanding block diameter | 6 mm |
| Max. HM rotating milling cutter diameter | 4 mm |
| Weight | 0.11 kg |
| Gross Weight | 0.180 kg |
| Product Group | 7AA |

EAN

4251757301032