

## Safety data sheet according to 1907/2006/EC, Article 31

Printing date 31.01.2018

Version number 46

Revision: 31.01.2018

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** PLASTI-KOTE® T&S SATIN LIME GREEN 22125 6UC 400 ML
- **Article number:** 440.0022125.076
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**  
No further relevant information available.
- **Sector of Use**
  - SU21 Consumer uses: Private households / general public / consumers
  - SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
- **Product category PC9a** Coatings and paints, thinners, paint removers
- **Process category**
  - PROC7 Industrial spraying
  - PROC11 Non industrial spraying
- **Application of the substance / the mixture** Paint
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
MOTIP DUPLI B.V.  
Wolfraamweg 2  
NL-8471 XC Wolvega  
Nederland  
Tel : +31 (0)561 694400  
Fax: +31 (0)561 694411  
e-mail: info@nl.motipdupli.com
- **Further information obtainable from:** Department Product Safety
- **1.4 Emergency telephone number:** +31 (0)561-694400 (09:00h - 17:00h)

### SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS02 flame

Aerosol 1 H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.



GHS07

Eye Irrit. 2 H319 Causes serious eye irritation.  
STOT SE 3 H336 May cause drowsiness or dizziness.

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**  
The product is classified and labelled according to the CLP regulation.
- **Hazard pictograms**



GHS02



GHS07

(Contd. on page 2)

GB

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 31.01.2018

Version number 46

Revision: 31.01.2018

Trade name: **PLASTI-KOTE® T&S SATIN LIME GREEN 22125 6UC 400 ML**

(Contd. of page 1)

· **Signal word** *Danger*· **Hazard-determining components of labelling:***acetone**Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, <2% aromatics*· **Hazard statements***H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.**H319 Causes serious eye irritation.**H336 May cause drowsiness or dizziness.*· **Precautionary statements***P102 Keep out of reach of children.**P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.**P211 Do not spray on an open flame or other ignition source.**P251 Do not pierce or burn, even after use.**P260 Do not breathe spray.**P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.**P501 Dispose of contents / container in accordance with regional regulations.*· **Additional information:***EUH066 Repeated exposure may cause skin dryness or cracking.*· **2.3 Other hazards**· **Results of PBT and vPvB assessment**· **PBT:** Not applicable.· **vPvB:** Not applicable.

### SECTION 3: Composition/information on ingredients

· **3.2 Chemical characterisation: Mixtures**· **Description:** Mixture of substances listed below with nonhazardous additions.· **Dangerous components:**

CAS: 67-64-1 EINECS: 200-662-2 Index number: 606-001-00-8 Reg.nr.: 01-2119471330-49	<i>acetone</i> ----- ☠ Flam. Liq. 2, H225 ☠ Eye Irrit. 2, H319; STOT SE 3, H336	25-<50%
CAS: 74-98-6 EINECS: 200-827-9 Index number: 601-003-00-5 Reg.nr.: 01-2119486944-21	<i>propane</i> ----- ☠ Flam. Gas 1, H220 Press. Gas C, H280	12.5-<20%
EC number: 919-857-5 Reg.nr.: 01-2119463258-33	<i>Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, &lt;2% aromatics</i> ----- ☠ Flam. Liq. 3, H226 ☠ Asp. Tox. 1, H304 ☠ STOT SE 3, H336	12.5-<20%
CAS: 106-97-8 EINECS: 203-448-7 Index number: 601-004-00-0 Reg.nr.: 01-2119474691-32	<i>butane</i> ----- ☠ Flam. Gas 1, H220 Press. Gas C, H280	10-<12.5%
CAS: 75-28-5 EINECS: 200-857-2 Index number: 601-004-00-0 Reg.nr.: 01-2119485395-27	<i>isobutane</i> ----- ☠ Flam. Gas 1, H220 Press. Gas C, H280	10-<12.5%
CAS: 34140-91-5 EINECS: 251-846-4 Reg.nr.: 01-2119974119-29-xxxx	<i>Oleic acid, compound with (Z)-N-octadec-9-enylpropane-1,3-diamine (2:1)</i> ----- ☠ STOT RE 2, H373 ☠ Aquatic Acute 1, H400; Aquatic Chronic 2, H411 ☠ Skin Irrit. 2, H315; Eye Irrit. 2, H319	≤0.5%

(Contd. on page 3)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 31.01.2018

Version number 46

Revision: 31.01.2018

**Trade name: PLASTI-KOTE® T&S SATIN LIME GREEN 22125 6UC 400 ML**

(Contd. of page 2)

· **Additional information:** For the wording of the listed hazard phrases refer to section 16.

#### **SECTION 4: First aid measures**

- **4.1 Description of first aid measures**
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Generally the product does not irritate the skin.
- **After eye contact:**  
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:** Drink plenty of water and provide fresh air. Call for a doctor immediately.
- **4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

#### **SECTION 5: Firefighting measures**

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**  
CO<sub>2</sub>, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **5.2 Special hazards arising from the substance or mixture**  
During heating or in case of fire poisonous gases are produced.
- **5.3 Advice for firefighters -**
- **Protective equipment:** Mouth respiratory protective device.

#### **SECTION 6: Accidental release measures**

- **6.1 Personal precautions, protective equipment and emergency procedures**  
Ensure adequate ventilation  
Keep away from ignition sources.  
Mount respiratory protective device.  
Wear protective equipment. Keep unprotected persons away.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**  
Dispose contaminated material as waste according to item 13.  
Ensure adequate ventilation.
- **6.4 Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

#### **SECTION 7: Handling and storage**

- **7.1 Precautions for safe handling** Ensure good ventilation/exhaustion at the workplace.
- **Information about fire - and explosion protection:**  
Do not spray onto a naked flame or any incandescent material.  
Keep ignition sources away - Do not smoke.  
Keep respiratory protective device available.  
Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C, i.e. electric lights. Do not pierce or burn, even after use.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**  
Observe official regulations on storing packagings with pressurised containers.
- **Information about storage in one common storage facility:** Not required.

(Contd. on page 4)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 31.01.2018

Version number 46

Revision: 31.01.2018

**Trade name: PLASTI-KOTE® T&S SATIN LIME GREEN 22125 6UC 400 ML**

(Contd. of page 3)

- **Further information about storage conditions:** Keep container tightly sealed.
- **Storage class:** 2 B
- **7.3 Specific end use(s)** No further relevant information available.

**SECTION 8: Exposure controls/personal protection**

- **Additional information about design of technical facilities:** No further data; see item 7.
- **8.1 Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:**

**67-64-1 acetone**

WEL	Short-term value: 3620 mg/m <sup>3</sup> , 1500 ppm Long-term value: 1210 mg/m <sup>3</sup> , 500 ppm
-----	--

**106-97-8 butane**

WEL	Short-term value: 1810 mg/m <sup>3</sup> , 750 ppm Long-term value: 1450 mg/m <sup>3</sup> , 600 ppm Carc (if more than 0.1% of buta-1.3-diene)
-----	---

- **Additional information:** The lists valid during the making were used as basis.
- **8.2 Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**  
Keep away from foodstuffs, beverages and feed.  
Immediately remove all soiled and contaminated clothing  
Wash hands before breaks and at the end of work.  
Do not inhale gases / fumes / aerosols.  
Avoid contact with the eyes and skin.  
Avoid contact with the eyes.
- **Respiratory protection:**  
In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.
- **Protection of hands:**  
The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.  
Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.  
Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation
- **Material of gloves**  
The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.
- **Penetration time of glove material**  
Butyl rubber gloves with a thickness of 0.4 mm are resistant to:  
Acetone: 480 min  
Butyl acetate: 60 min  
Ethyl acetate: 170 min  
Xylene: 42 min  
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

(Contd. on page 5)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 31.01.2018

Version number 46

Revision: 31.01.2018

Trade name: **PLASTI-KOTE® T&S SATIN LIME GREEN 22125 6UC 400 ML**

(Contd. of page 4)

· **Eye protection:**

Tightly sealed goggles

### SECTION 9: Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**· **General Information**· **Appearance:**

· <b>Form:</b>	Aerosol
· <b>Colour:</b>	Different according to colouring
· <b>Odour:</b>	Solvent-like
· <b>Odour threshold:</b>	Not determined.

· **pH-value:** Not determined.· **Change in condition**

· <b>Melting point/freezing point:</b>	Undetermined.
· <b>Initial boiling point and boiling range:</b>	Not applicable, as aerosol.

· **Flash point:** <0 °C (<32 °F)  
Not applicable, as aerosol.

· **Flammability (solid, gas):** Not applicable.· **Ignition temperature:** 240 °C (464 °F)· **Decomposition temperature:** Not determined.· **Auto-ignition temperature:** Product is not selfigniting.

· **Explosive properties:** Product is not explosive. However, formation of explosive air/vapour mixtures are possible.

· **Explosion limits:**

· <b>Lower:</b>	0.6 Vol %
· <b>Upper:</b>	13 Vol %

· **Vapour pressure at 20 °C (68 °F):** 8,300 hPa (6 mm Hg)· **Density at 20 °C (68 °F):** 0.82 g/cm<sup>3</sup> (6.84 lbs/gal)· **Relative density** Not determined.· **Vapour density** Not determined.· **Evaporation rate** Not applicable.· **Solubility in / Miscibility with water:**

Not miscible or difficult to mix.

· **Partition coefficient: n-octanol/water:** Not determined.· **Viscosity:**

· <b>Dynamic:</b>	Not determined.
· <b>Kinematic:</b>	Not determined.

· **Solvent content:**

· <b>Organic solvents:</b>	80.7 %
· <b>EU-VOC:</b>	684.0 g/l
· <b>EU-VOC in %:</b>	83.81 %
· <b>VOC (EC)</b>	---
	658.3 g/l
· <b>VOC-EU%</b>	80.66 %

(Contd. on page 6)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 31.01.2018

Version number 46

Revision: 31.01.2018

Trade name: **PLASTI-KOTE® T&S SATIN LIME GREEN 22125 6UC 400 ML**

(Contd. of page 5)

- |                                |  |
|--------------------------------|--|
| · <b>Solids content:</b>       | 19.2 %                                     |
| · <b>9.2 Other information</b> | No further relevant information available. |

### SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

### SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.

· **LD/LC50 values relevant for classification:**

**67-64-1 acetone**

Oral	LD50	5,800 mg/kg (rat)
Dermal	LD50	>15,800 mg/kg (rabbit)
Inhalative	LC50 / 4h	76 mg/l (rat)

- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation**  
Causes serious eye irritation.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure**  
May cause drowsiness or dizziness.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

### SECTION 12: Ecological information

· **12.1 Toxicity**

· **Aquatic toxicity:**

**67-64-1 acetone**

LC50/96h	8,300 mg/l (fish)
EC50/96h	7,200 mg/l (algae)
LC50 / 48 h	8,450 mg/l (crustacean (water flea))

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**

· **General notes:**

Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water  
Do not allow product to reach ground water, water course or sewage system.

(Contd. on page 7)



**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 31.01.2018

Version number 46

Revision: 31.01.2018

**Trade name: PLASTI-KOTE® T&S SATIN LIME GREEN 22125 6UC 400 ML**

(Contd. of page 6)

- *Danger to drinking water if even small quantities leak into the ground.*
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

### SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**  
Must not be disposed together with household garbage. Do not allow product to reach sewage system.

- **European waste catalogue**

08 01 11*	waste paint and varnish containing organic solvents or other hazardous substances
15 01 04	metallic packaging

- **Uncleaned packaging:**
- **Recommendation:** Non contaminated packagings may be recycled.

### SECTION 14: Transport information

- **14.1 UN-Number**  
· **ADR, IMDG, IATA** UN1950
- **14.2 UN proper shipping name**  
· **ADR** 1950 AEROSOLS  
· **IMDG** AEROSOLS  
· **IATA** AEROSOLS, flammable

- **14.3 Transport hazard class(es)**

- **ADR**



- **Class** 2 5F Gases.
- **Label** 2.1

- **IMDG, IATA**



- **Class** 2.1
- **Label** 2.1

- **14.4 Packing group**

- **ADR, IMDG, IATA** not regulated

- **14.5 Environmental hazards:** Not applicable.

- **14.6 Special precautions for user** Warning: Gases.
- **Danger code (Kemler):** -
- **EMS Number:** F-D,S-U
- **Segregation groups** Alkalis
- **Stowage Code** SW1 Protected from sources of heat.  
SW22 For AEROSOLS with a maximum capacity of 1 litre:  
Category A. For AEROSOLS with a capacity above 1 litre:  
Category B. For WASTE AEROSOLS: Category C, Clear

(Contd. on page 8)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 31.01.2018

Version number 46

Revision: 31.01.2018

Trade name: **PLASTI-KOTE® T&S SATIN LIME GREEN 22125 6UC 400 ML**

(Contd. of page 7)

· <b>Segregation Code</b>	of living quarters. SG69 For AEROSOLS with a maximum capacity of 1 litre: Segregation as for class 9. Stow "separated from" class 1 except for division 1.4. For AEROSOLS with a capacity above 1 litre: Segregation as for the appropriate subdivision of class 2. For WASTE AEROSOLS: Segregation as for the appropriate subdivision of class 2.
· <b>14.7 Transport in bulk according to Annex II of Marpol and the IBC Code</b>	Not applicable.
· <b>Transport/Additional information:</b>	
· <b>ADR</b>	
· <b>Limited quantities (LQ)</b>	1L
· <b>Excepted quantities (EQ)</b>	Code: E0 Not permitted as Excepted Quantity
· <b>Transport category</b>	2
· <b>Tunnel restriction code</b>	D
· <b>IMDG</b>	
· <b>Limited quantities (LQ)</b>	1L
· <b>Excepted quantities (EQ)</b>	Code: E0 Not permitted as Excepted Quantity Code: E0 Not permitted as Excepted Quantity
· <b>UN "Model Regulation":</b>	UN 1950 AEROSOLS, 2.1

### SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **Seveso category P3a** FLAMMABLE AEROSOLS
- **Qualifying quantity (tonnes) for the application of lower-tier requirements** 150 t
- **Qualifying quantity (tonnes) for the application of upper-tier requirements** 500 t
- **REGULATION (EC) No 1907/2006 ANNEX XVII** Conditions of restriction: 3, 40
- **National regulations:**
- **Other regulations, limitations and prohibitive regulations**
- **Substances of very high concern (SVHC) according to REACH, Article 57**
- None of the ingredients is listed.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

### SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**
- H220 Extremely flammable gas.
- H225 Highly flammable liquid and vapour.
- H226 Flammable liquid and vapour.
- H280 Contains gas under pressure; may explode if heated.
- H304 May be fatal if swallowed and enters airways.
- H315 Causes skin irritation.
- H319 Causes serious eye irritation.

(Contd. on page 9)

GB



**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 31.01.2018

Version number 46

Revision: 31.01.2018

**Trade name: PLASTI-KOTE® T&S SATIN LIME GREEN 22125 6UC 400 ML**

(Contd. of page 8)

*H336 May cause drowsiness or dizziness.**H373 May cause damage to organs through prolonged or repeated exposure.**H400 Very toxic to aquatic life.**H411 Toxic to aquatic life with long lasting effects.*

· **Abbreviations and acronyms:**

*RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)*

*ICAO: International Civil Aviation Organisation*

*ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)*

*IMDG: International Maritime Code for Dangerous Goods*

*IATA: International Air Transport Association*

*GHS: Globally Harmonised System of Classification and Labelling of Chemicals*

*EINECS: European Inventory of Existing Commercial Chemical Substances*

*ELINCS: European List of Notified Chemical Substances*

*CAS: Chemical Abstracts Service (division of the American Chemical Society)*

*VOC: Volatile Organic Compounds (USA, EU)*

*LC50: Lethal concentration, 50 percent*

*LD50: Lethal dose, 50 percent*

*PBT: Persistent, Bioaccumulative and Toxic*

*SVHC: Substances of Very High Concern*

*vPvB: very Persistent and very Bioaccumulative*

*Flam. Gas 1: Flammable gases – Category 1*

*Aerosol 1: Aerosols – Category 1*

*Press. Gas C: Gases under pressure – Compressed gas*

*Flam. Liq. 2: Flammable liquids – Category 2*

*Flam. Liq. 3: Flammable liquids – Category 3*

*Skin Irrit. 2: Skin corrosion/irritation – Category 2*

*Eye Irrit. 2: Serious eye damage/eye irritation – Category 2*

*STOT SE 3: Specific target organ toxicity (single exposure) – Category 3*

*STOT RE 2: Specific target organ toxicity (repeated exposure) – Category 2*

*Asp. Tox. 1: Aspiration hazard – Category 1*

*Aquatic Acute 1: Hazardous to the aquatic environment - acute aquatic hazard – Category 1*

*Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard – Category 2*

· **\* Data compared to the previous version altered.**