

Printing date 23.02.2023 Version number 301 Revision: 23.02.2023

SECTION 1: Identification of the substance/mixture and of the company/undertaking

· 1.1 Product identifier 600280

· Trade name: Universal Cleaner + Concentrated Car Wash E-COLL

· Article number: 4317784313414, 4317784313421

· 1.2 Relevant identified uses of the substance or mixture and uses advised against

· Sector of Use

SU21 Consumer uses: Private households / general public / consumers

SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)

- · Application of the substance / the mixture Cleaning material/ Detergent
- · 1.3 Details of the supplier of the safety data sheet
- · Manufacturer/Supplier:

E/D/E - Einkaufsbuero Deutscher Eisenhaendler GmbH EDE Platz 1 D-42389 Wuppertal Germany

Tel. +49 202 6096-0 e-mail: sdb@ede.de

- · Further information obtainable from: Product safety department
- 1.4 Emergency telephone number: Giftinformationszentrum Mainz Tel.: +49 (6131) 19240

SECTION 2: Hazards identification

- · 2.1 Classification of the substance or mixture
- · Classification according to Regulation (EC) No 1272/2008

Skin Corr. 1A H314 Causes severe skin burns and eye damage.

Eye Dam. 1 H318 Causes serious eye damage.

- · 2.2 Label elements
- · Labelling according to Regulation (EC) No 1272/2008

The product is classified and labelled according to the CLP regulation.

· Hazard pictograms



GHS05

- · Signal word Danger
- · Hazard-determining components of labelling:

potassium hydroxide Alkoholethoxylat C9-C11 1-Heptanol, 2-propyl-, 7EO



Printing date 23.02.2023 Version number 301 Revision: 23.02.2023

Trade name: Universal Cleaner + Concentrated Car Wash E-COLL

(Contd. of page 1)

Amides, C8-18 (even numbered) and C18-unsatd., N,N-bis(hydroxyethyl)

· Hazard statements

H314 Causes severe skin burns and eye damage.

· Precautionary statements

P101 If medical advice is needed, have product container or label at hand.

P102 Keep out of reach of children. P260 Do not breathe mist/vapours/spray.

Wear protective gloves/protective clothing/eye protection/face protection. P280

P301+P330+P331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.

P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with

P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if

present and easy to do. Continue rinsing.

P310 Immediately call a POISON CENTER/doctor.

P501 Dispose of contents/container in accordance with local/regional/national/international

regulations.

· 2.3 Other hazards

· Results of PBT and vPvB assessment

· PBT: Not applicable. · vPvB: Not applicable.

SECTION 3: Composition/information on ingredients

· 3.2 Mixtures

· Description: Mixture of substances listed below with nonhazardous additions.

· Dangerous components:				
CAS: 1310-58-3 EINECS: 215-181-3 Index number: 019-002-00-8 Reg.nr.: 01-2119487136-33-xxxx	potassium hydroxide Skin Corr. 1A, H314 Acute Tox. 4, H302 Specific concentration limits: Skin Corr. 1A; H314: C ≥ 5 % Skin Corr. 1B; H314: 2 % ≤ C < 5 % Skin Irrit. 2; H315: 0.5 % ≤ C < 2 % Eye Dam. 1; H318: C ≥ 2 % Eye Irrit. 2; H319: 0.5 % ≤ C < 2 %	<1.25%		
CAS: 68439-46-3 Reg.nr.: 01-2119980051-45-xxxx	Alkoholethoxylat C9-C11 Eye Dam. 1, H318 Acute Tox. 4, H302	1-<5%		
CAS: 160875-66-1	1-Heptanol, 2-propyl- , 7EO	1-<5%		
EC number: 931-329-6 Reg.nr.: 01-2119490100-xxxx	Amides, C8-18 (even numbered) and C18-unsatd., N,N-bis(hydroxyethyl) Eye Dam. 1, H318 Aquatic Chronic 2, H411 Skin Irrit. 2, H315	1-<5%		



Printing date 23.02.2023 Version number 301 Revision: 23.02.2023

Trade name: Universal Cleaner + Concentrated Car Wash E-COLL

(Contd. of page 2)

Regulation (EC) No 648/2004 on detergents / Labelling for contents
 5 % or over but less than 15 %
 non-ionic surfactants
 less than 5 %
 cationic surfactants

· Additional information: For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

- · 4.1 Description of first aid measures
- · General information: Immediately remove any clothing soiled by the product.
- · After inhalation:

Supply fresh air.

Seek medical treatment in case of complaints.

· After skin contact:

Immediately wash with water and soap and rinse thoroughly.

If skin irritation continues, consult a doctor.

· After eye contact:

Rinse opened eye for several minutes under running water. Then consult a doctor. Seek medical treatment.

- · After swallowing: Drink plenty of water and provide fresh air. Call for a doctor immediately.
- 4.2 Most important symptoms and effects, both acute and delayed No further relevant information available.
- 4.3 Indication of any immediate medical attention and special treatment needed No further relevant information available.

SECTION 5: Firefighting measures

- 5.1 Extinguishing media
- Suitable extinguishing agents:

CO2, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

- · For safety reasons unsuitable extinguishing agents: Water with full jet
- 5.2 Special hazards arising from the substance or mixture

Formation of toxic gases is possible during heating or in case of fire.

- · 5.3 Advice for firefighters
- **Protective equipment:** Wear self-contained respiratory protective device.

(Contd. on page 4)



Printing date 23.02.2023 Version number 301 Revision: 23.02.2023

Trade name: Universal Cleaner + Concentrated Car Wash E-COLL

(Contd. of page 3)

· Additional information

Dispose of fire debris and contaminated fire fighting water in accordance with official regulations.

SECTION 6: Accidental release measures

· 6.1 Personal precautions, protective equipment and emergency procedures

Wear protective equipment. Keep unprotected persons away.

• **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.

· 6.3 Methods and material for containment and cleaning up:

Ensure adequate ventilation.

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

Use neutralising agent.

Dispose contaminated material as waste according to item 13.

· 6.4 Reference to other sections

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage

· 7.1 Precautions for safe handling

Ensure good ventilation/exhaustion at the workplace.

Prevent formation of aerosols.

- · Information about fire and explosion protection: No special measures required.
- · 7.2 Conditions for safe storage, including any incompatibilities
- · Storage:

· Requirements to be met by storerooms and receptacles:

Provide floor trough without outlet.

Store only in the original receptacle.

Provide alkali-resistant floor.

· Information about storage in one common storage facility:

Do not store together with acids.

Store away from foodstuffs.

· Further information about storage conditions:

Keep container tightly sealed.

Protect from frost.

Protect from heat and direct sunlight.

· 7.3 Specific end use(s) No further relevant information available.



Printing date 23.02.2023 Version number 301 Revision: 23.02.2023

Trade name: Universal Cleaner + Concentrated Car Wash E-COLL

(Contd. of page 4)

SECTION 8: Exposure controls/personal protection

· 8.1 Control parameters

· Ingredients with limit values that require monitoring at the workplace:

The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

· DNELs				
CAS: 1310-58-3 potassium hydroxide				
Inhalative DNEL (worker) 1 mg/m³ (industrial use)				
Amides, C8-18 (even numbered) and C18-unsatd., N,N-bis(hydroxyethyl)				
Dermal	DNEL (worker)	4.16 mg/kg bw/day (industrial use)		
Inhalative	DNEL (worker)	73.4 mg/m³ (industrial use)		

- · Additional information: The lists valid during the making were used as basis.
- · 8.2 Exposure controls
- · Appropriate engineering controls No further data; see item 7.
- · Individual protection measures, such as personal protective equipment
- · General protective and hygienic measures:

Keep away from foodstuffs, beverages and feed. Wash hands before breaks and at the end of work. Do not inhale gases / fumes / aerosols. Avoid contact with the eyes and skin.

· Hand protection



Protective gloves

Only use chemical-protective gloves with CE-labelling of category III.

· Material of gloves

Nitrile rubber, NBR

Recommended thickness of the material: \geq 0.4 mm

· Penetration time of glove material

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· Eye/face protection



Tightly sealed goggles

· Body protection: Alkaline resistant protective clothing



Printing date 23.02.2023 Version number 301 Revision: 23.02.2023

Trade name: Universal Cleaner + Concentrated Car Wash E-COLL

(Contd. of page 5)

SECTION 9: Physical and chemical properties

· 9.1 Information on basic physical and chemical properties

· General Information

Colour:

 Odour:
 Odour threshold:
 Melting point/freezing point:

 Light yellow

 Characteristic
 Not determined.

 Undetermined.

· Boiling point or initial boiling point and boiling

range Undetermined. • Flammability Not applicable.

· Lower and upper explosion limit

Lower: Not determined.
Upper: Not determined.
Flash point: Not applicable.
Decomposition temperature: Not determined.

· pH at 20 °C 12

· Viscosity:

· Kinematic viscosity Not determined.

· Kinematic: 23 °C - 4 mm (ISO 2431)

· **Dynamic:** Not determined.

· Solubility

· water: Not miscible or difficult to mix.

Partition coefficient n-octanol/water (log value)
 Vapour pressure:
 Not determined.
 Not determined.

· Density and/or relative density

Density at 20 °C:
 Relative density
 Vapour density
 Not determined.
 Not determined.

· 9.2 Other information

· Appearance:

· Form: Fluid

· Important information on protection of health and environment, and on safety.

• Auto-ignition temperature: Product is not selfigniting.

• Explosive properties: Product does not present an explosion hazard.

· VOC (EC) q/l

· VOCV (CH) 0.00 %

· Change in condition

· Drip point:

Oxidising propertiesEvaporation rateNot determined.Not determined.

Information with regard to physical hazard classes

Explosives
Flammable gases
Aerosols
Oxidising gases
Gases under pressure
Flammable liquids
Flammable solids

(Contd. on page 7)



Printing date 23.02.2023 Version number 301 Revision: 23.02.2023

Trade name: Universal Cleaner + Concentrated Car Wash E-COLL

6)

		(Contd. of page 6
· Self-reactive substances and mixtures	Void	, , ,
· Pyrophoric liquids	Void	
· Pyrophoric solids	Void	
· Self-heating substances and mixtures	Void	
· Substances and mixtures, which emit flamn	nable	
gases in contact with water	Void	
· Oxidising liquids	Void	
· Oxidising solids	Void	
· Organic peroxides	Void	
· Corrosive to metals	Void	
· Desensitised explosives	Void	

SECTION 10: Stability and reactivity

- 10.1 Reactivity No further relevant information available.
- · 10.2 Chemical stability
- · Thermal decomposition / conditions to be avoided:

No decomposition if used according to specifications.

· 10.3 Possibility of hazardous reactions

Strong exothermic reaction with acids.

Corrosive action on metals.

- 10.4 Conditions to avoid No further relevant information available.
- 10.5 Incompatible materials: No further relevant information available.
- 10.6 Hazardous decomposition products: No dangerous decomposition products known.

SECTION 11: Toxicological information

- · 11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008
- · Acute toxicity Based on available data, the classification criteria are not met.
- · LD/LC50 values relevant for classification:

CAS: 1310-58-3 potassium hydroxide

Oral LD50 273 mg/kg (rat)

· Skin corrosion/irritation

Causes severe skin burns and eye damage.

· Serious eye damage/irritation

Causes serious eye damage.

- · Respiratory or skin sensitisation Based on available data, the classification criteria are not met.
- · Germ cell mutagenicity Based on available data, the classification criteria are not met.
- · Carcinogenicity Based on available data, the classification criteria are not met.

(Contd. on page 8)



Printing date 23.02.2023 Version number 301 Revision: 23.02.2023

Trade name: Universal Cleaner + Concentrated Car Wash E-COLL

(Contd. of page 7)

- · Reproductive toxicity Based on available data, the classification criteria are not met.
- · STOT-single exposure Based on available data, the classification criteria are not met.
- · STOT-repeated exposure Based on available data, the classification criteria are not met.
- · Aspiration hazard Based on available data, the classification criteria are not met.
- · 11.2 Information on other hazards
- · Endocrine disrupting properties

None of the ingredients is listed.

SECTION 12: Ecological information

- · 12.1 Toxicity
- · Aquatic toxicity: No further relevant information available.
- 12.2 Persistence and degradability No further relevant information available.
- 12.3 Bioaccumulative potential No further relevant information available.
- 12.4 Mobility in soil No further relevant information available.
- · 12.5 Results of PBT and vPvB assessment
- · PBT: Not applicable.
- · vPvB: Not applicable.
- · 12.6 Endocrine disrupting properties

The product does not contain substances with endocrine disrupting properties.

- · 12.7 Other adverse effects
- · Additional ecological information:
- · General notes:

The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.

Must not reach sewage water or drainage ditch undiluted or unneutralised.

Rinse off of bigger amounts into drains or the aquatic environment may lead to increased pH-values. A high pH-value harms aquatic organisms. In the dilution of the use-level the pH-value is considerably reduced, so that after the use of the product the aqueous waste, emptied into drains, is only low water-dangerous.

Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water

Do not allow product to reach ground water, water course or sewage system.



Printing date 23.02.2023 Version number 301 Revision: 23.02.2023

Trade name: Universal Cleaner + Concentrated Car Wash E-COLL

(Contd. of page 8)

SECTION 13: Disposal considerations

· 13.1 Waste treatment methods:

Containers can be recycled if completely empty; if not, dispose product/containers as dangerous waste. Observe local regulations.

SECTION 14: Transport information

· 14.1 UN number or ID number

· ADR, IMDG, IATA Void

· 14.2 UN proper shipping name

· ADR, IMDG, IATA Void

· 14.3 Transport hazard class(es)

· ADR, IMDG, IATA

· Class Void

· 14.4 Packing group

· ADR, IMDG, IATA Void

• 14.5 Environmental hazards: Not applicable.

• 14.6 Special precautions for user Not applicable.

· 14.7 Maritime transport in bulk according to IMO

instruments Not applicable.

· UN "Model Regulation": Void

SECTION 15: Regulatory information

- · 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.
- · Labelling according to Regulation (EC) No 1272/2008

The product is classified and labelled according to the CLP regulation.

· Hazard pictograms



GHS05

- · Signal word Danger
- · Hazard-determining components of labelling:

potassium hydroxide Alkoholethoxylat C9-C11

1-Heptanol, 2-propyl-, 7EO

Amides, C8-18 (even numbered) and C18-unsatd., N,N-bis(hydroxyethyl)

· Hazard statements

H314 Causes severe skin burns and eye damage.



Printing date 23.02.2023 Version number 301 Revision: 23.02.2023

Trade name: Universal Cleaner + Concentrated Car Wash E-COLL

(Contd. of page 9)

· Precautionary statements

P101 If medical advice is needed, have product container or label at hand.

P102 Keep out of reach of children.
P260 Do not breathe mist/vapours/spray.

P280 Wear protective gloves/protective clothing/eye protection/face protection.

P301+P330+P331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.

P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with

water.

P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if

present and easy to do. Continue rinsing.

P310 Immediately call a POISON CENTER/doctor.

P501 Dispose of contents/container in accordance with local/regional/national/international

regulations.

· REGULATION (EC) No 1907/2006 ANNEX XVII Conditions of restriction: 3

DIRECTIVE 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment – Annex II

None of the ingredients is listed.

· REGULATION (EU) 2019/1148

· Annex I - RESTRICTED EXPLOSIVES PRECURSORS (Upper limit value for the purpose of licensing under Article 5(3))

None of the ingredients is listed.

· Annex II - REPORTABLE EXPLOSIVES PRECURSORS

None of the ingredients is listed.

· National regulations:

· Information about limitation of use:

Employment restrictions concerning pregnant and lactating women must be observed.

Exposure scenario(s)

Exposure scenario(s) of ingredients (if present) are available on request at: sdb@ede.de

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· Relevant phrases

H302 Harmful if swallowed.

H314 Causes severe skin burns and eye damage.

H315 Causes skin irritation.

H318 Causes serious eye damage.

H411 Toxic to aquatic life with long lasting effects.

· Contact: sdb@ede.de

· Date of previous version: 25.02.2021

· Abbreviations and acronyms:

ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods



Printing date 23.02.2023 Version number 301 Revision: 23.02.2023

Trade name: Universal Cleaner + Concentrated Car Wash E-COLL

(Contd. of page 10)

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOCV: Lenkungsabgabe auf flüchtigen organischen Verbindungen, Schweiz (Swiss Ordinance on volatile organic compounds)

DNEL: Derived No-Effect Level (REACH) LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic vPvB: very Persistent and very Bioaccumulative

Acute Tox. 4: Acute toxicity - Category 4

Skin Corr. 1A: Skin corrosion/irritation – Category 1A Skin Irrit. 2: Skin corrosion/irritation – Category 2

Eye Dam. 1: Serious eye damage/eye irritation – Category 1

Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard - Category 2

· * Data compared to the previous version altered.

EU -