

## T120R0K2



**Article Number:** 112-12060

**Heavy Duty Cable Tie, 15.2" Long, 120lb Tensile Strength, PA66, Black, 50/pkg**



Download drawing



Download spec sheet

### Base Data

**Local Order Number** T120R0K2

**Type** T120R

**Color** Black (BK)

- Features and Benefits**
- Heavy duty design to offer higher tensile strength.
  - Head design provides high tensile strength with very low insertion force.
  - Bent tail ensures a quick and simple installation.

**Product Description** HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

**Short Description** Heavy Duty Cable Tie, 15.2" Long, 120lb Tensile Strength, PA66, Black, 50/pkg

### Product Dimensions

**Minimum Tensile Strength (Imperial)** 120.0 lbs

**Minimum Tensile Strength (Metric)** 535.0 N

**Length L (Imperial)** 15.2 "

**Length L (Metric)** 387.0 mm

**Fixation Method** None

**Identification Plate Position** none

**Releasable Closure** No

**Tie Closure** plastic pawl

**Variant** Inside Serrated

**Width W (Imperial)** 0.3 "

**Width W (Metric)** 7.6 mm

**Bundle Diameter Min. (Imperial)** 0.2 "

**Bundle Diameter Min. (Metric)** 5.0 mm

**Bundle Diameter Max. (Imperial)** 4.1 "

**Bundle Diameter Max. (Metric)** 105.0 mm

### Logistics and Packaging

**Quantity Per** bag

**Package Quantity (Metric)** 50

**Carton Quantity** 1000

**Weight (Metric)** 5.14 kg

## Material and Specifications

---

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL94 V2
<b>Halogenfree</b>	Yes
<b>Operating Temperature</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Compliant</b>	Yes
<b>Certification/Specification</b>	UL-ZODZ2.E64139 MIL 53421
<b>UL Listed (US and Canada)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes