



PBCL22T

▶ PRODUCTS FOR INDUSTRIAL AUTOMATION



Plastic Fiber, Retroreflective

Core Dia.: 0.5 mm & 9 x 0.25 mm; Fiber Length 0.6 m

Coaxial, Lens

T Termination

Part Number: 65944

CERTIFICATIONS



SPECIFICATIONS

Quantity Included	1
Fiber Optic Type	Plastic
Sensing Mode (General)	Diffuse
Sensing Mode (Detailed)	Coaxial
Fiber Sheathing Material (Jacket)	Polyethylene
Fiber Length (m)	.6
Fiber Sensing End Size	M8
Sensing End Segment 1	Coaxial
Sensing End Segment 2	Lens
Reciprocating	No

Flex Relief	No
Core Diameter (mm)	ø0.5 & 9X ø0.25
Minimum Bend Radius (mm)	10
Termination	Terminated
Max Temp (°C)	70
Minimum Repeat Bending Endurance	5000
Integrated Lens	No
Feature: Chemical Resistant	No
Feature: Extended Range	No
Feature: Flat Pack	No
Feature: Small Object Detection	No
Application: Liquid Level	No
Application: Vacuum Feed Through	No



Banner Engineering India | Office No. 1001, 10th Floor, Sai Capital, Opp. ICC

Senapati Bapat Road | Pune, 411016 | Contact Us: 08030695482