



## PUNCH UNIT-CONNECTOR 9 PIN (229)

Cat No: **229** UPC No: **783310344360**



### Description

- "Cut-out and mounting slots are punched in one operation
- Drill only one 7/16" (11.1 mm) pilot hole. (See page 82 for Kwik Stepper step bits.)
- Fast, accurate panel punching with no sawing or filing required
- Universal size punches for front or back mount of TRW Cinch and ITT Cannon-type or equivalent connectors in 9, 15, 25, 37 or 50-pin configurations
- U.S. Patent No. 4,899,447 "

### Specifications

- Capacity :
  - 16 GA (1.500 MM) Mild Steel
  - 10 GA (3.500 MM) Aluminum
- No. Of Pins : 9
- Operation Type :
  - Manual With A Wrench
  - Quick Draw And Quick Draw 90 Hydraulic Drivers, Battery Driver, Ram And Pump Hydraulic Drivers Aluminum
- Replacement Part : 34441 Punch, 35196 Die Unit, 34421 Draw Stud, 04638 Square Counter Nut, 34733 Drive Nut
- Size : 0.787 IN X 0.982 IN X 0.469 IN (20.000 MM X 24.900 MM X 11.900 MM)
- Type : Electronic Connector Panel
- Weight : 1.400 LB (0.640 KG)